



## Remover and Degreaser

**Heavy duty, multi-purpose degreaser with a characteristic citrus odour. A specially formulated, non-toxic, degreaser designed to remove grease, oil, adhesives, labels and general workshop grime rapidly from a wide range of surfaces.**

### Features

- Powerful, fast acting and penetrating citrus based cleaner
- Ideal for removing labels and adhesives
- Safe on metals, most plastics and paints
- Contains only FDA listed ingredients
- NSF C1 registered - 140805

### Directions for Use

- Shake well and spray from a distance of approx. 15-30 cms
- Apply directly to the surface to be cleaned
- Allow time to penetrate then wipe clean
- For heavier contamination, allow to soak for longer periods of time
- As with all products of this type it is recommended that compatibility with painted or coated surfaces, plastics and rubber be tested prior to use

T +44 (0) 113 232 2600  
F +44 (0) 113 232 2740  
E [customer-service@rocol.com](mailto:customer-service@rocol.com)  
[www.rocol.com](http://www.rocol.com)

ROCOL House, Swillington, Leeds LS26 8BS

Registered Company No. 559693 VAT No. 742 0531 67  
Registered Office: Admiral House, St Leonard's Road, Windsor, Berkshire SL4 3BL

ROCOL A division of **ITW** Ltd



BS EN ISO 9001  
Certificate No. FM 12448



BS EN ISO 14001  
Certificate No. EMS 67596



OHSAS 18001  
Certificate No. OHS 78173



INVESTOR IN PEOPLE

The information in this publication is based on our experience and reports from customers. There are many factors outside our control or knowledge which affect the use and performance of our products, for which reason it is given without responsibility.

# Technical Data

**ROCOL®**

Performance you can trust

## Remover and Degreaser

<b>Appearance</b>	Colourless liquid
<b>Propellant</b>	Carbon dioxide (CO <sub>2</sub> )
<b>Solvent</b>	Blend of terpenes and hydrocarbon
<b>Odour</b>	Characteristic citrus
<b>Flash point (PMCC)</b>	-7°C
<b>Density (kg/m<sup>3</sup> @ 20°C)</b>	0.8 (measured as kg/litre)
<b>Storage</b>	Storage temperature should be controlled to between 1°C and 40°C
<b>Pack size – part code</b>	300mL aerosol – p/c 34151

T +44 (0) 113 232 2600  
F +44 (0) 113 232 2740  
E [customer-service@rocol.com](mailto:customer-service@rocol.com)  
[www.rocol.com](http://www.rocol.com)

ROCOL House, Swillington, Leeds LS26 8BS

Registered Company No. 559693 VAT No. 742 0531 67  
Registered Office: Admiral House, St Leonard's Road, Windsor, Berkshire SL4 3BL

ROCOL A division of **ITW** Ltd



BS EN ISO 9001  
Certificate No. FM 12448



BS EN ISO 14001  
Certificate No. EMS 67596



OHSAS 18001  
Certificate No. OHS 78173



INVESTOR IN PEOPLE

The information in this publication is based on our experience and reports from customers.  
There are many factors outside our control or knowledge which affect the use and performance  
of our products, for which reason it is given without responsibility.