

REFERENCE SPECIFICATIONS

-NFC 93425 (in compliance with HE 507)

PHYSICAL CHARACTERISTICS

-INSULATOR MATERIAL: THERMOPLASTIC ,UL94V0

-CONTACT MATERIAL: BRASS

-ACCESSORIES: BRASS

-SHELLS: STEEL

ELECTRICAL CHARACTERISTICS

-NOMINAL CURRENT: 40A

-CONTACT RESISTANCE: <= 7.3 mOhms

-CONTACT/CONTACT : >=1000 V

-CONTACT/GROUND : >=1200 V

-INSULATION RESISTANCE: >=5000 MOhms

- CLIMATIC CATEGORY: 55/125/21

TEMPERATURE RANGE -55°C TO +125°C

DAMP HEAT STEADY STATE 21 DAYS

SALT SPRAY 24 HOURS

- RETENTION AGAINST TORQUE: - Threaded insert: 0.7 N.m minimum

- Female screw : 0.5 N.m minimum

PRESS FIT PERFORMANCES

PRESS FIT CONTACTS	
INSERTION FORCE	<= 200 N
Average insertion 160N	
EXTRACTION FORCE	>= 30 N

NOTE RoHS INFORMATION

- The "LF" products meet european union Directives and other country regulations as described in GS-22-008.
- Termination plating spec:
 - Ni 1.27µm+Sn 0.5 to 1.5µ(pure bright)
- Active area plating spec:
 - Ni + Gold
- Shell plating : 2 to 4µm Cu + Ni + 3 to 10µm Sn(pure bright)
- Accessories: Sn pure bright + nickel
- Packaging spec: See GS-14-920

Series

DBL5W5S80C5M40LF

Shell size: **E A B C**
(see sheet 3)

Front accessory definition
(see sheet 2)

blank :without accessory
L :threaded insert M3
O :threaded insert UNC 4-40
V :female screw UNC 4-40

Layout of contacts (see sheet 3)

Contacts

S :Socket

Termination type

80C Right angle/US foot print

Plating

5 200 matings/unmatings

6 500 matings/unmatings

PCB accessories definition(see sheet 2)

M Metal brackets

A Without accessory

Power contacts

40 :Fitted with power contacts 40 Amp.

See note RoHS


TABLE 1:PCB HOLE DIAMETERS

P.C.B HOLE DEFINITION (NOTE 1 AND 2)	SnPb holes for CONTACTS		Sn holes for CONTACTS		holes ACCESSORIES Ø3.10±0.10
	DRILL DIAMETER	Ø3.22 REF(NOTE 3)	DRILL DIAMETER	Ø3.22 REF(NOTE 3)	
	DRILLED HOLE	Ø3.19-3.25	DRILLED HOLE	Ø3.19-3.25	
	COPPER PLATING	25µ MINI (RECOMMENDED 50µ MAXI)	COPPER PLATING	25µ MINI (RECOMMENDED 50µ MAXI)	
	TIN-LEAD PLATING	15µ MAXI (RECOMMENDED 5µ MINI)	TIN-LEAD PLATING	15µ MAXI (RECOMMENDED 5µ MINI)	
(NOTE 1 AND 2)	TIN PLATING		TIN PLATING	0.8 to 1,2µ	
	FINISH HOLE (AFTER REFLOW)	Ø 3.02-3.20	FINISH HOLE (AFTER REFLOW)	Ø3.08-3.20	


NOTE-1:THESE DIMENSIONS MUST BE RESPECT TO SECURE PRESS-FIT PIN PERFORMANCES.

NOTE-2: ACCORDING TO IEC-352-5 SPEC.


NOTE-3: MAJOR REQUIREMENT FOR PRESS FIT PIN PERFORMANCE




5W5 FOR EXAMPLE



PERFORMANCE				www.fciconnect.com		surface - ☒ tolerance std ISO 1302 ISO 406 ISO 1101		projection 		mm 	
						TOLERANCES UNLESS OTHERWISE SPECIFIED					
rev		ecn no		dr		date		size		Scale	
B		LS06-0208		LGO		2006/11/27/13		A2		2:1	
C		LS07-0273		MPE		2007/11/05		ECN		LS07-0273	



www.fciconnect.com		surface - ISO 1302	tolerance std ISO 406 ISO 1101	projection	mm	
		TOLERANCES UNLESS OTHERWISE SPECIFIED				
Dr	M PESSON	11/10/05	ANGULAR	0.X	±0.3	size A2
Eng	11/10/05	P LEGARE	LINEAR	0.XX	±0.1	Scale 2:1
Chr			0° ±2°	0.XXX	±0.05	ECN LS07-0273
Appr			Product family	- Spec ref		
FCI		SUB FEMALE DW US foot print		deg no	C01-8639-2317	
		full power right angled solder			C	
		catalog no	-	Y	sheet 2 of 5	



PART NUMBER	AMPS	MATINGS/ UNMATINGS	FRONT ACCESSORY	PCB ACCESSORIES
D*xWxS80C5A40LF	40	200	without	without
D*LxWxS80C5A40LF	40	200	insert M3	without
D*OxWxS80C5A40LF	40	200	insert UNC 4.40	without
D*VxWxS80C5A40LF	40	200	female screw UNC 4.40	without
D*xWxS80C5M40LF	40	200	without	metal bracket
D*LxWxS80C5M40LF	40	200	insert M3	metal bracket
D*OxWxS80C5M40LF	40	200	insert UNC 4.40	metal bracket
D*VxWxS80C5M40LF	40	200	female screw UNC 4.40	metal bracket

shell size	LAYOUTS
*	xWx
E	2V2
A	3V3
A	3W3
B	5W5
C	8W8

PART NUMBER	AMPS	MATINGS/ UNMATINGS	FRONT ACCESSORY	PCB ACCESSORIES
D*xWxS80C6A40LF	40	500	without	without
D*LxWxS80C6A40LF	40	500	insert M3	without
D*OxWxS80C6A40LF	40	500	insert UNC 4.40	without
D*VxWxS80C6A40LF	40	500	female screw UNC 4.40	without
D*xWxS80C6M40LF	40	500	without	metal bracket
D*LxWxS80C6M40LF	40	500	insert M3	metal bracket
D*OxWxS80C6M40LF	40	500	insert UNC 4.40	metal bracket
D*VxWxS80C6M40LF	40	500	female screw UNC 4.40	metal bracket

www.fciconnect.com		surface - ISO 1302		tolerance std ISO 406 ISO 1101		projection		mm	
		TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	M PESSON	11/10/05	ANGULAR	0.X	±0.3	size	A2	Scale	2:1
Eng	11/10/05	P LEGARE	LINEAR	0.XX	±0.1	ECN	LS07-0273		
Chr			0° ±2°	0.XXX	±0.05				
Appr			Product family			Spec ref			
FCI		SUB FEMALE DW US foot print		deg no		C01-8639-2317		Rev.	
		full power right angled solder						C	
		catalog no				Y		sheet 3 of 5	

