

Electronic housing - EFG 45-LG/BS GY - 2757474

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid
(<http://download.phoenixcontact.com>)

Electronics housing, for insertion of two PCBs, without screw connection terminal blocks



Key commercial data

Packing unit	1 pc
GTIN	 4 017918 063566
Weight per Piece (excluding packing)	149.96 GRM
Custom tariff number	85472000
Country of origin	Germany

Technical data

General

Housing type	Complete housing
Housing material	polycarbonate
Color	gray

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

Dimensions

Length	118 mm
Constructional height	137.5 mm
Width	45 mm

Technical data

Inflammability class according to UL 94	V0
---	----

Electronic housing - EFG 45-LG/BS GY - 2757474

Technical data

Technical data

Power dissipation at 20°C in the horizontal mounting position	9.5 W 11.5 W
---	--------------

Classifications

eCl@ss

eCl@ss 4.0	27180401
eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 5.1	27180506
eCl@ss 6.0	27180802
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702

ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC001031

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

Approvals

Approvals

Approvals

UL Recognized

Ex Approvals

Approvals submitted

Electronic housing - EFG 45-LG/BS GY - 2757474

Approvals

Approval details

UL Recognized 

Accessories

Accessories

Printed circuit board terminal


PCB terminal block - FRONT 2,5-H/SA 5 - 1700008



PCB terminal block, Nominal current: 24 A, Nom. voltage: 400 V, Pitch: 5 mm, Number of positions: 1, Connection method: Screw connection, Mounting: Soldering, Conductor/PCB connection direction: 0 °, Color: green, The article can be aligned to create different nos. of positions!


Drawings

Dimensioned drawing



Side element (front and back)


Dimensioned drawing




Cover element

Electronic housing - EFG 45-LG/BS GY - 2757474

Dimensioned drawing



Dimensioned drawing



1 = Diameter 3.2 mm for M3