

LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	OWN	APVD
			P	REVISED PER ECO-11-004820	11MAR11	RK	HMR

- NOTES:
- 1

INSULATOR MATERIAL: THERMOPLASTIC POLYESTER, BLACK, UL94V-0.
- 2


MACHINED CONTACT: BECU, PLATED WITH 20μ” MIN. GOLD THK. OVER 30-100μ” THK. NICKEL.
- 3

SLEEVE: COPPER, PLATED WITH 180-340μ” THK. TIN (LEAD FREE) OVER 75-125μ” THK. NICKEL.
- 4

PARTS ARE END-TO-END STACKABLE AND BREAKABLE TO CREATE VARIOUS POSITION SIZES.
- 5

PRELIMINARY PART-NOT RELEASED FOR PRODUCTION.
- 6



OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



RECOMMENDED HOLE LAYOUT

TOLERANCE ±.002 UNLESS OTHERWISE NOTED

6 OBSOLETE	2.000	20	2-1571994-0
	1.900	19	1-1571994-9
	1.800	18	1-1571994-8
	1.700	17	1-1571994-7
	1.600	16	1-1571994-6
	1.500	15	1-1571994-5
	1.400	14	1-1571994-4
	1.300	13	1-1571994-3
6 OBSOLETE	1.200	12	1-1571994-2
	1.100	11	1-1571994-1
	1.000	10	1-1571994-0
	0.900	9	-1571994-9-
	0.800	8	1571994-8
	0.700	7	-1571994-7-
	0.600	6	-1571994-6-
	0.500	5	-1571994-5-
6 OBSOLETE	0.400	4	-1571994-4-
	0.300	3	1571994-3
	0.200	2	1571994-2
	0.100	1	-1571994-1-
	DIM "A"	POSITION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN B S VISVESWARA CHK K.WRIGHT APVD — PRODUCT SPEC — APPLICATION SPEC — WEIGHT —		26APR05 — — — — — — —		 TE Connectivity								
DIMENSIONS: INCHES			TOLERANCES UNLESS OTHERWISE SPECIFIED:			NAME			ASSEMBLY SOCKET (.510 SERIES. S.I.P)						
			0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —			SIZE			CAGE CODE		DRAWING NO		RESTRICTED TO		
MATERIAL 			FINISH 			A2			00779		C=1571994		—		
CUSTOMER DRAWING						SCALE		4:1		SHEET		1 of 1		REV P	