

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION



.19

(C) COPYRIGHT 19


BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
CM	53	P	LTR	DESCRIPTION	DATE	DWN	APVD
			D	REV & REDWN PER EC 0G1B-0217-98	29OCT98	TB	R5




1. WIRE RANGE: 0.5 - 2 mm² (20 - 14 AWG)
2. INSULATION RANGE: 2.54 - 4.57
- △3 FRICTION FIT ON A 3.56 DIAMETER PIN.




SECTION A-A



SECTION C-C



SECTION B-B



SECTION D-D

1.52	.060	3.43	.135	4.57	.180	20.19	.795
0.51	.020	3.05	.120	3.81	.150	6.05	.238
0.35	.014	2.54	.100	3.61	.142	5.46	.215
0.13	.005	2.03	.080	3.56	.140	5.08	.200
MM	IN	MM	IN	MM	IN	MM	IN

CONVERSION TABLE

METRIC

350388-1
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	29OCT1998	AMP AMP Incorporated Harrisburg, PA 17105-3608			
DIMENSIONS: mm		CHK	29OCT1998				
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	16NOV1998	NAME	
		0 PLC ±- 1 PLC ±- 2 PLC ±0.13 3 PLC ±- 4 PLC ±- ANGLES ±- FINISH PRE-TIN		C. MARTIN		SOCKET, LOOSE PIECE, .140 PIN & SOCKET CONNECTOR	
MATERIAL 0.35 BRASS		APPLICATION SPEC		WEIGHT -		SIZE	RESTRICTED TO
		CUSTOMER DRAWING		SCALE 5:1		CAGE CODE	REV
				SHEET 1 OF 1		DRAWING NO	
						A200779C- 350388	