



(2.54 mm) .100"

SSM-115-L-SH

SSM-120-S-DV

SSM-116-S-SV

SSM SERIES

TIGER CLAW™ SURFACE MOUNT SOCKET

Mates with:

TSW, MTSW, TST,
TSS, ZST, ZSS, DW,
EW, ZW, TSM, HMTSW,
HTSW, TSSH, BST,
HTSS, TLW, MTLW

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?SSM

Insulator Material:

Black Liquid Crystal Polymer

Contact Material:

Phosphor Bronze

Plating:

Au or Sn over

50 μ" (1.27 μm) Ni

Current Rating (SSM/TSW):

5.2 A per pin

(2 pins powered)

Voltage Rating:

405 VAC / 572 VDC

Operating Temp Range:

-55 °C to +125 °C with Gold

-55 °C to +105 °C with Tin

Insertion Depth:

SV/DV is (4.34 mm) .171" to

(7.24 mm) .285" or pass-through

from top; (5.56 mm) .219" plus

board thickness minimum from

bottom; SH/DH is (4.34 mm)

.171" to (6.35 mm) .250"

Normal Force:

125 grams (1.21 N) average

RoHS Compliant:

Yes

PROCESSING

Lead-Free Solderable:

Yes

-DH Coplanarity:

Less than 28 positions

(0.15 mm) .006" max*

More than 27 positions

(0.20 mm) .008" max*

-SH, -SV, -DV Coplanarity:

(0.15 mm) .006" max*

* (.004" stencil solution

may be available; contact

IPG@samtec.com)

RECOGNITIONS

For complete scope



of recognitions see

www.samtec.com/quality



Note:

Some lengths, styles and options are non-standard, non-returnable.



Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

All parts within this catalog are built to Samtec's specifications.

Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.