




LOC	DIST	REVISIONS				
G	86	P	LTR	DESCRIPTION	DATE	DWN
		F		REVISED PER 0L20-0217-97	02DEC97	MJS

1 0.76[.030] MAX ALUMINUM FOIL THK



53264-2
AMP
PART NUMBER

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS				THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK SCHRUM 02DEC97 CHK MJ SPICER 03DEC97 APVD JL MECKLEY 03DEC97 PRODUCT SPEC — APPLICATION SPEC — WEIGHT —		AMP Incorporated Harrisburg, PA 17105-3608 NAME W/ BARREL, TAP, DOUBLE FACE, TERMI-FOIL™, WIRE SIZE: 18-12 AWG SIZE A2 CAGE CODE 00779 DRAWING NO C- 53264 RESTRICTED TO —						
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		RECOMMENDED OPERATING TEMPERATURE: 150°C MAX		DIMENSIONS: mm [INCHES]		0 PLC ±— 1 PLC ±— 2 PLC ±0.20 [.008] 3 PLC ±— 4 PLC ±— ANGLES ±—		FINISH TIN PLATE 0.00254 [.000100] MIN THK PER ASTM B-545				
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		VOLTAGE RATING: NOT APPLICABLE										
FOR ORDER ENTRY		1-800-526-5142		WIRE CROSS SECTIONAL AREA RANGE: 1.65-2.62mm² [3,260-5,180] CIR MILS SOLID OR STRANDED		MATERIAL COPPER PER ASTM B-152 ANNEALED		CUSTOMER DRAWING				SCALE 5:1	SHEET 1 OF 1	REV F