




- VDC: 5, 12
- RPM: 2600~5000
- CFM: 7.67~15.12
- Impeller: 7 blades

- Rotational direction CCW view from front face
- PBT94V-0 frame and impeller
- AWG 26; UL 1007 lead wires
- Mass: 24g




DC FAN 60x60x11.5mm

Specification

	Bearing	Voltage	Current	Speed	Input Power	Air Flow	Static Pressure	Noise	Weight
MODEL NO	○ Sleeve ● One ball and one sleeve ○ Hydraulic	(Vdc)	(Amp)	(Rpm)	(Watts)	(CFM)	(mm/H ₂ O)	dB(A)	Gram
B6010B12L	●	12	0.07	3300	0.84	9.44	1.59	28.0	24
B6010B12M	●	12	0.08	3900	0.96	11.18	2.28	32.6	24
B6010B12H	●	12	0.13	4500	1.56	13.11	2.77	36.4	24
C6010B05M	●	5	0.19	3900	0.95	11.18	2.28	32.6	24
C6010B12E	●	12	0.05	2600	0.60	7.67	1.06	23.7	24
C6010B12L	●	12	0.07	3300	0.84	9.44	1.59	28.0	24
C6010B12M	●	12	0.10	3900	1.20	11.18	2.28	32.6	24
C6010B12H	●	12	0.10	4500	1.20	13.11	2.77	36.4	24
C6010B12U	●	12	0.16	5000	1.92	15.12	3.55	40.0	24
D6010B05M	●	5	0.19	3900	0.95	11.18	2.28	32.6	24
D6010B12L	●	12	0.07	3300	0.84	9.44	1.59	28.0	24
D6010B12M	●	12	0.08	3900	0.96	11.18	2.28	32.6	24
D6010B12H	●	12	0.10	4500	1.20	13.11	2.77	36.4	24
F6010B12E	●	12	0.05	2600	0.60	7.67	1.06	23.7	24
F6010B12L	●	12	0.06	3300	0.72	9.44	1.59	28.0	24
F6010B12M	●	12	0.10	3900	1.20	11.18	2.28	32.6	24
F6010B12H	●	12	0.13	4500	1.56	13.11	2.77	36.4	24

Design specifics subject to change without notice.



STATIC PRESSURE

