





NOTES:

1. MATERIAL: SEE TABLE
2. FINISHES: SEE TABLE
3. PRODUCT SPECIFICATION: NOT REQUIRED
4. PACKAGING: NOT REQUIRED
5. MATES WITH: 86 SERIES PLUGGABLE TERMINAL BLOCK
6. INCH DIMS ARE SHOWN IN BRACKETS (XXX)
7. "XX" REFERS TO THE NUMBER OF CIRCUITS
8. REFER TO SD-38120-003 FOR IMPRINTING OPTIONS (10AV AND 11AV)

3	XX	HEADER PIN (-G30 OPTION)	BRASS	GOLD PLATE
2	XX	HEADER PIN (STANDARD)	BRASS	TIN PLATE
1	I	INSULATOR	NYLON	SEE CHART ON SHEET 2
ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH

ECN NO. 3898 DRWN: JF 10-26-04 CH'K: C APPR: C	DESCRIPTION MAJOR CRITICAL SPC S	QUALITY SYMBOLS	GENERAL TOLERANCES: (UNLESS SPECIFIED)		SCALE 3:1	DESIGN UNITS ☐ mm ☒ INCH	THIRD ANGLE PROJECTION	☒ mm ☐ INCH ☐ mm ONLY	REVISION ON CAD ONLY
			mm	INCH	DRAWN BY & DATE R. KEMP 12-5-01		TITLE: HEADER ST, CLOSED ENDS, ASSEMBLY (5.08 [1.200] CENTERS)		
		4 PLACES		±.0015	CHECKED BY & DATE P. WALTZ 12-6-01				
		3 PLACES	±.038	±.005	APPROVED BY & DATE L. ROTHBAUS 12-6-01		MOLEX INCORPORATED		
2 PLACES	±.13	±.01	CAD FILENAME 8616XX		MATERIAL NO. SEE CHART	DRAWING NO. SD-39860-003			
				ANGULAR: ±2°	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.			SIZE B	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS									

