


TOSHIBA Transistor Silicon NPN Epitaxial Type (PCT Process)

RN1114,RN1115,RN1116,RN1117,RN1118


Switching, Inverter Circuit, Interface Circuit
And Driver Circuit Applications

Unit: mm

- With built-in bias resistors.
- Simplify circuit design
- Reduce a quantity of parts and manufacturing process
- Complementary to RN2114~2118

Equivalent Circuit and Bias Resistor Values

Type No.	R ₁ (kΩ)	R ₂ (kΩ)
RN1114	1	10
RN1115	2.2	10
RN1116	4.7	10
RN1117	10	4.7
RN1118	47	10






**Maximum Ratings (Ta = 25°C)**






Characteristic		Symbol	Rating	Unit
Collector-base voltage	RN1114~1118	V _{CBO}	50	V
Collector-emitter voltage		V _{CEO}	50	V
Emitter-base voltage	RN1114 RN1115 RN1116 RN1117 RN1118	V _{EBO}	5	V
			6	
			7	
			15	
			25	
Collector current	RN1114~1118	I _C	100	mA
Collector power dissipation		P _C	100	mW
Junction temperature		T _j	150	°C
Storage temperature range		T _{stg}	-55~150	°C






Weight: 2.4mg






Electrical Characteristics (Ta = 25°C)






Characteristic		Symbol	Test Circuit	Test Condition	Min	Typ.	Max	Unit
Collector cut-off current	RN1114~1118	I _{CBO}	—	V _{CB} = 50V, I _E = 0	—	—	100	nA
	RN1114~1118	I _{CEO}	—	V _{CE} = 50V, I _B = 0	—	—	500	nA
Emitter cut-off current	RN1114	I _{EBO}	—	V _{EB} = 5V, I _C = 0	0.35	—	0.65	mA
	RN1115		—	V _{EB} = 6V, I _C = 0	0.37	—	0.71	
	RN1116		—	V _{EB} = 7V, I _C = 0	0.36	—	0.68	
	RN1117		—	V _{EB} = 15V, I _C = 0	0.78	—	1.46	
	RN1118		—	V _{EB} = 25V, I _C = 0	0.33	—	0.63	
DC current gain	RN1114~16, 18	h _{FE}	—	V _{CE} = 5V, I _C = 10mA	50	—	—	—
	RN1117		—		30	—	—	
Collector-emitter saturation voltage	RN1114~1118	V _{CE} (sat)	—	I _C = 5mA, I _B = 0.25mA	—	0.1	0.3	V
Input voltage (ON)	RN1114	V _I (ON)	—	V _{CE} = 0.2V, I _C = 5mA	0.6	—	2.0	V
	RN1115		—		0.7	—	2.5	
	RN1116		—		0.8	—	2.5	
	RN1117		—		1.5	—	3.5	
	RN1118		—		2.5	—	10.0	
Input voltage (OFF)	RN1114	V _I (OFF)	—	V _{CE} = 5V, I _C = 0.1mA	0.3	—	0.9	V
	RN1115		—		0.3	—	1.0	
	RN1116		—		0.3	—	1.1	
	RN1117		—		0.3	—	2.3	
	RN1118		—		0.5	—	5.7	
Translation Frequency	RN1114~1118	f _T	—	V _{CE} = 10V, I _C = 5mA	—	250	—	MHz
Collector output capacitance	RN1114~1118	C _{ob}	—	V _{CB} = 10V, I _E = 0, f = 1MHz	—	3.0	6.0	pF
Input Resistor	RN1114	R ₁	—	—	0.7	1.0	1.3	kΩ
	RN1115		—		1.54	2.2	2.86	
	RN1116		—		3.29	4.7	6.11	
	RN1117		—		7.0	10.0	13.0	
	RN1118		—		32.9	47.0	61.1	
Resistor Ratio	RN1114	R ₁ /R ₂	—	—	—	0.1	—	—
	RN1115		—		—	0.22	—	
	RN1116		—		—	0.47	—	
	RN1117		—		—	2.13	—	
	RN1118		—		—	4.7	—	









Type Name	Marking
RN1114	
RN1115	
RN1116	
RN1117	
RN1118	

RESTRICTIONS ON PRODUCT USE

000707EAA

- TOSHIBA is continually working to improve the quality and reliability of its products. Nevertheless, semiconductor devices in general can malfunction or fail due to their inherent electrical sensitivity and vulnerability to physical stress. It is the responsibility of the buyer, when utilizing TOSHIBA products, to comply with the standards of safety in making a safe design for the entire system, and to avoid situations in which a malfunction or failure of such TOSHIBA products could cause loss of human life, bodily injury or damage to property.
In developing your designs, please ensure that TOSHIBA products are used within specified operating ranges as set forth in the most recent TOSHIBA products specifications. Also, please keep in mind the precautions and conditions set forth in the "Handling Guide for Semiconductor Devices," or "TOSHIBA Semiconductor Reliability Handbook" etc..
- The TOSHIBA products listed in this document are intended for usage in general electronics applications (computer, personal equipment, office equipment, measuring equipment, industrial robotics, domestic appliances, etc.). These TOSHIBA products are neither intended nor warranted for usage in equipment that requires extraordinarily high quality and/or reliability or a malfunction or failure of which may cause loss of human life or bodily injury ("Unintended Usage"). Unintended Usage include atomic energy control instruments, airplane or spaceship instruments, transportation instruments, traffic signal instruments, combustion control instruments, medical instruments, all types of safety devices, etc.. Unintended Usage of TOSHIBA products listed in this document shall be made at the customer's own risk.
- The information contained herein is presented only as a guide for the applications of our products. No responsibility is assumed by TOSHIBA CORPORATION for any infringements of intellectual property or other rights of the third parties which may result from its use. No license is granted by implication or otherwise under any intellectual property or other rights of TOSHIBA CORPORATION or others.
- The information contained herein is subject to change without notice.