





								1	
LOC	DIST	REVISIONS							
—	—	P	LTR	DESCRIPTION			DATE	DWN	APVD
			C	REVISED PER ECO 13-001843.			08FEB2013	MGM	CT





SINGLE POLARIZATION



DOUBLE POLARIZATION



PANEL CUTOUT



CAVITY IDENTIFICATION WHEN VIEWED FROM MATING FACE OF CONNECTOR

1. UNLESS OTHERWISE SPECIFIED DIMENSIONS TOLERANCE ARE ± 0.2
2. DWV RATING: 875VAC @ SEA LEVEL
3. WORKING TEMPERATURE: $-55^{\circ}\text{C} \sim +125^{\circ}\text{C}$

4 MATERIAL:
CONTACT : COPPER ALLOY
SHELL : COPPER ALLOY
INSULATOR : PEEK
O RING : SILICONE RUBBER

5 FINISH
CONTACT: GOLD OVER NICKEL
SHELL : BLACK CHROMIUM

6. WATER PROOF: 1M IMMERSION
7. WIRE SIZE: 22 AWG MAX.

8 THE PART IS MARKED WITH THE TE PART NUMBER, CHINA, DATE CODE AND LOT I.D.

9 ALL TOLERANCES TO BE ± 0.20 MM UNLESS NOTED.

1	CHROMIUM-BLACK	DOUBLE	SOLDERING	2157738-2
1	CHROMIUM-BLACK	SINGLE	SOLDERING	2157738-1
SHELL SIZE	FINISH	POLARIZATION	TERMINATION	TE CONNECTIVITY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C THOMAS 20AUG2011	TE Connectivity		
DIMENSIONS: mm		CHK R. GROSS 20AUG2011			
		APVD R. GROSS 20AUG2011	NAME		
		PRODUCT SPEC 108-127005	CIRCULAR HD RECEPTACLE WITH SOLDER CUP SOCKETS CONTACTS - 3 POS		
MATERIAL		APPLICATION SPEC	SIZE A2	CAGE CODE 00779	DRAWING NO C-2157738
FINISH		WEIGHT -	RESTRICTED TO		
CUSTOMER DRAWING		SCALE NTS	SHEET 1 OF 1	REV C	