


MATERIALS

BODY	PASSIVATED STAINLESS STEEL
CONTACT	GOLD PLATED
INSULATOR	PTFE



SPECIFICATIONS

FREQUENCY RANGE: 6.0–18.0 GHz
INSERTION LOSS(MEASURED AT -10dBm): 2.2 dB MAX
VSWR (MEASURED AT -10 dBm): 2.0:1
LEAKAGE @ 1W CW INPUT: $+16.0\text{ dBm}$ MAX

PASSIVE PIN DIODE LIMITERS

1 WATT CW & 100 WATT PEAK ($1\mu\text{SEC}$) POWER HANDLING
0.1% DUTY CYCLE, DERATED TO 20% AT $+125^\circ\text{C}$
INTERNAL DC RETURN
LIMITING THRESHOLD ABOVE $+9\text{ dBm}$ TYPICAL
OPERATING TEMPERATURE RANGE= -55°C TO $+125^\circ\text{C}$

*SMA MALE INPUT / SMA FEMALE OUTPUT



PASTERNAK ENTERPRISES, INC.

P.O BOX 16759, IRVINE, CA 92623
PHONE (949) 261-1920 FAX (949) 261-7451

WEB ADDRESS: www.pasternack.com
E-MAIL ADDRESS: sales@pasternack.com

COAXIAL & FIBER OPTICS

DWG TITLE

PE8024

DES.

SMA PIN-PIN DIODE LIMITERS FREQUENCY
RANGE: 6.0-18.0 GHz

SIZE A

FSCM NO. 53919

CAD FILE 080902

SCALE N/A

127

NOTES:

1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.