

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

FT

0

P

LTR

DESCRIPTION

DATE

DWN

APVD

P3

REVISED PER ECO-11-004587

11MAR11

RK

HMR

1

PARTS PACKAGED UNASSEMBLED.

2

CABLE CLAMPING AREA ADJUSTABLE FROM .100 TO .410 SQ IN BY REVERSING CLAMPING INSERTS.
(2 INSERTS SUPPLIED, -1 AND -2 ONLY)

3

CABLE CLAMPING AREA ADJUSTABLE FROM .100 TO .410 SQ IN BY CHANGING CLAMPING INSERTS. (4 INSERTS SUPPLIED, -4 ONLY)

4

.703 MAXIMUM CABLE OUTSIDE DIAMETER.

5

BULK PACKAGED KITS TO BE ORDERED IN MULTIPLES OF 100 ONLY.

6

NON-HEXAVALENT CHROMATE FINISH.

7

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

2

3

CLAMPING INSERT

(2) #5-20 SELF-TAPPING SCREWS,
SOLID OR SLOTTED SHANK.
MATERIAL: ZINC PLATED STEEL
LENGTH: .62±.00 EXCEPT -6, .50±.05

1.131±.025

DIA

1.655±.030

2

3

CLAMPING AREA SHADED

6

INDIVIDUAL

1-206322-1

6

5

BULK

1-206322-0

6

INDIVIDUAL

206322-9

6

7

OBSOLETE

SMALL PACK

206322-8

6

7

OBSOLETE

INDIVIDUAL

206322-7

6

5

BULK

206322-6

7

6

OBSOLETE

SMALL PACK

206322-5

6

OBSOLETE

INDIVIDUAL

206322-4

6

SUPERSEDED BY 1-206322-0

5

BULK

206322-2

6

SUPERSEDED BY 206322-9

INDIVIDUAL

206322-1

PACKAGING

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

A GRAFF

4/23/91

CHK

W.G.LENKER

7-22-92

APVD

-

-

PRODUCT SPEC

108-10024

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

DIMENSIONS:

INCHES

0 PLC

± -

1 PLC

± -

2 PLC

± -

3 PLC

± -

4 PLC

± -

ANGLES

± -

FINISH

-

MATERIAL

THERMOPLASTIC

STE

TE Connectivity

CABLE CLAMP KIT, LARGE,
SHELL SIZE 17, CPC

SIZE

A3

CAGE CODE

00779

DRAWING NO

C-206322

RESTRICTED TO

-

SCALE

NTS

SHEET

1 OF 1

REV

P3

1470-19

(3/11)