








13		12		11		10		9		8		7		6		5		4		3		2		1	
CKT. SIZE	PART NUMBER	ENG. NUMBER SDA-70204-	DIM. "A"		DIM. "B"		DIM. "C"		CKT. SIZE	PART NUMBER	ENG. NUMBER SDA-70204-	DIM. "A"		DIM. "B"		DIM. "C"		3° MAX. ROTATION PERMISSIBLE  DETAIL "V" SCALE = 20:1  DETAIL "S"							
			MM	IN.	MM	IN.	MM	IN.				MM	IN.	MM	IN.	MM	IN.							MM	IN.
08	25-02-6008	0259	7,62	.300	17,78	.700	20,32	.800	42	25-02-6042	0276	50,80	2.000	60,96	2.400	63,50	2.500	3° MAX. ROTATION PERMISSIBLE  DETAIL "V" SCALE = 20:1  DETAIL "S"							
10	25-02-6010	0260	10,16	.400	20,32	.800	22,86	.900	44	25-02-6044	0277	53,34	2.100	63,50	2.500	66,04	2.600								
12	25-02-6012	0261	12,70	.500	22,86	.900	25,40	1.000	46	25-02-6046	0278	55,88	2.200	66,04	2.600	68,58	2.700								
14	25-02-6014	0262	15,24	.600	25,40	1.000	27,94	1.100	48	25-02-6048	0279	58,42	2.300	68,58	2.700	71,12	2.800								
16	25-02-6016	0263	17,78	.700	27,94	1.100	30,48	1.200	50	25-02-6050	0280	60,96	2.400	71,12	2.800	73,66	2.900								
18	25-02-6018	0264	20,32	.800	30,48	1.200	33,02	1.300	52	25-02-6052	0281	63,50	2.500	73,66	2.900	76,20	3.000								
20	25-02-6020	0265	22,86	.900	33,02	1.300	35,56	1.400	54	25-02-6054	0282	66,04	2.600	76,20	3.000	78,74	3.100								
22	25-02-6022	0266	25,40	1.000	35,56	1.400	38,10	1.500	56	25-02-6056	0283	68,58	2.700	78,74	3.100	81,28	3.200								
24	25-02-6024	0267	27,94	1.100	38,10	1.500	40,64	1.600	58	25-02-6058	0284	71,12	2.800	81,28	3.200	83,82	3.300								
26	25-02-6026	0268	30,48	1.200	40,64	1.600	43,10	1.700	60	25-02-6060	0285	73,66	2.900	83,82	3.300	86,36	3.400								
28	25-02-6028	0269	33,02	1.300	43,10	1.700	45,72	1.800	62	25-02-6062	0286	76,20	3.000	86,36	3.400	88,90	3.500								
30	25-02-6030	0270	35,56	1.400	45,72	1.800	48,26	1.900	64	25-02-6064	0287	78,74	3.100	88,90	3.500	91,44	3.600								
32	25-02-6032	0271	38,10	1.500	48,26	1.900	50,80	2.000	66	25-02-6066	0288	81,28	3.200	91,44	3.600	93,98	3.700								
34	25-02-6034	0272	40,64	1.600	50,80	2.000	53,34	2.100	68	25-02-6068	0289	83,82	3.300	93,98	3.700	96,52	3.800								
36	25-02-6036	0273	43,10	1.700	53,34	2.100	55,88	2.200	70	25-02-6070	0290	86,36	3.400	96,52	3.800	99,06	3.900								
38	25-02-6038	0274	45,72	1.800	55,88	2.200	58,42	2.300	72	25-02-6072	0291	88,90	3.500	99,06	3.900	101,60	4.000								
40	25-02-6040	0275	48,26	1.900	58,42	2.300	60,96	2.400																	




DETAIL "V"
SCALE = 20:1



DETAIL "S"



SECTION W-W



- NOTES:
1. WAFER MATERIAL: GLASS FILLED NYLON; COLOR: BLACK
2. PIN MATERIAL: COPPER ALLOY
3. PIN PLATING:
TIP: 15 MICROINCHES MINIMUM GOLD IN SELECTED AREA
TAIL: 75 MICROINCHES MINIMUM TIN IN SELECTED AREA
OVER NICKEL UNDERPLATE OVER-ALL
4. PINS MUST MEET SOLDERABILITY SPEC. NO. 152
5. PIN PUSH-OUT FORCE (1.81 KG)/4 LBS MINIMUM
6. REFER TO P.S. NO. 70204
7. STANDARD PACKAGING PER: PK-70873-0070

CORRECT DIMENSION EC NO: UCP2011-3892 DRWN:MS BARRA 2011/06/09 CHKD: APPR: MILLER 2011/07/07 REV: H	QUALITY SYMBOLS ▽ = 0 ▽ = 0 ▽ = 0	GENERAL TOLERANCES (UNLESS SPECIFIED) <table border="1"> <tr> <th></th> <th>mm</th> <th>INCH</th> </tr> <tr> <td>4 PLACES</td> <td>± .---</td> <td>± .---</td> </tr> <tr> <td>3 PLACES</td> <td>± .---</td> <td>± .010</td> </tr> <tr> <td>2 PLACES</td> <td>± 0.25</td> <td>± .---</td> </tr> <tr> <td>1 PLACE</td> <td>± .---</td> <td>± .---</td> </tr> </table>		mm	INCH	4 PLACES	± .---	± .---	3 PLACES	± .---	± .010	2 PLACES	± 0.25	± .---	1 PLACE	± .---	± .---	DIMENSION STYLE MM/IN	SCALE 4:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION
	mm	INCH																			
4 PLACES	± .---	± .---																			
3 PLACES	± .---	± .010																			
2 PLACES	± 0.25	± .---																			
1 PLACE	± .---	± .---																			
DRAWN BY JAS 1986/05/20		TITLE SHROUDED HEADER DUAL ROW W/PCB SLOTS & GUIDE EARS .100 GRID .025 SQ PIN																			
CHECKED BY EIK 1986/05/20		MOLEX INCORPORATED																			
APPROVED BY WAZ 1986/05/20		MATERIAL NO. SEE TABLE		DOCUMENT NO. SDA-70204-0257-0320																	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE C				THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															