



0291




0291-0-15-XX-16-XX-10-0
Hex press-fit in 1,7 plated thru hole

0293




0293-0-15-XX-16-XX-10-0
Press-fit in 1,7 mounting hole

0287




0287-0-15-XX-16-XX-10-0
Solder mount in 1,65 min. mounting hole
Also available on 8mm wide carrier tape: 3,250 parts per 330mm reel.
Order as: 0287-0-57-XX-16-XX-10-0

0285




0285-0-15-XX-16-XX-10-0
Solder mount in 1,65 min. mounting hole

0284




0284-0-15-XX-16-XX-10-0
Solder mount in 1,78 min. mounting hole

8114




8114-0-15-XX-16-XX-04-0
Press-fit from underside of pc board into 1,65 mounting hole

0407




0407-0-15-XX-16-XX-04-0
Press-fit in 1,68 mounting hole

0415




0415-0-15-XX-16-XX-10-0
Solder mount in 1,6 min. mounting hole
Also available on 24mm wide carrier tape: 1,500 parts per 330mm reel.
Order as: 0415-0-57-XX-16-XX-10-0

0303




0303-0-19-XX-16-XX-10-0
Wire Termination
Press-fit in 1,70 mounting hole

0306




0306-0-19-XX-16-XX-10-0
Wire Termination
#18 gage crimp barrel

0273



0273-0-15-XX-16-XX-10-0
Press-fit in 1,98 mounting hole

7520



7520-0-15-XX-16-XX-10-0
Press-fit in 1,68 mounting hole

SPECIFICATIONS

SHELL MATERIAL:
Brass Alloy 360, 1/2 Hard

CONTACT MATERIAL:
Beryllium Copper Alloy 172, HT

DIMENSION IN INCHES
TOLERANCES ON:
LENGTHS: $\pm 0,13$
DIAMETERS: $\pm 0,05$
ANGLES: $\pm 2^\circ$

ORDER CODE: XXXX - X - 1X - XX - 16 - XX - XX - 0

BASIC PART #

SPECIFY SHELL FINISH:
01 5,08 μ m TIN/LEAD OVER NICKEL
80 5,08 μ m TIN OVER NICKEL $\diamond$
15 0,25 μ m GOLD OVER NICKEL $\diamond$



CONTACT

#16 CONTACT (DATA ON PAGE 221)

SPECIFY CONTACT FINISH:
01 5,08 μ m TIN/LEAD OVER NICKEL
80 5,08 μ m TIN OVER NICKEL $\diamond$
27 0,76 μ m GOLD OVER NICKEL $\diamond$