

E1M2BBB8-73.225M

Lead Free



COMPLIANT



ITEM DESCRIPTION

73.225MHz ±10ppm 8pF Parallel Resonant

ELECTRICAL SPECIFICATIONS


Nominal Frequency	73.225MHz
Frequency Tolerance	±10ppm
Frequency Stability	±10ppm
Aging at 25°C	±1ppm/year Maximum
Operating Temperature Range	-20°C to +70°C
Load Capacitance	8pF Parallel Resonant
Shunt Capacitance (C0)	7pF Maximum
Equivalent Series Resistance	70 Ohms Maximum
Mode of Operation	Third Overtone
Drive Level	100µWatts Maximum
Crystal Cut	AT-Cut
Storage Temperature Range	-55°C to +125°C
Insulation Resistance	500 Megaohms Minimum (Measured at 100Vdc)

ENVIRONMENTAL & MECHANICAL SPECIFICATIONS

ESD Susceptibility	MIL-STD-883, Method 3015, Class 1, HBM: 1500V
Fine Leak Test	MIL-STD-883, Method 1014, Condition A
Flammability	UL94-V0
Gross Leak Test	MIL-STD-883, Method 1014, Condition C
Lead Integrity	MIL-STD-883, Method 2004
Mechanical Shock	MIL-STD-202, Method 213, Condition C
Moisture Resistance	MIL-STD-883, Method 1004
Moisture Sensitivity	J-STD-020, MSL 1
Resistance to Soldering Heat	MIL-STD-202, Method 210, Condition K
Resistance to Solvents	MIL-STD-202, Method 215
Solderability	MIL-STD-883, Method 2003
Temperature Cycling	MIL-STD-883, Method 1010, Condition B
Vibration	MIL-STD-883, Method 2007, Condition A

E1M2BBB8-73.225M

MECHANICAL DIMENSIONS (all dimensions in millimeters)



LINE	MARKING
1	E73.22 <i>E=Ecliptek Designator</i>
2	XXXXXX <i>XXXXXX=Ecliptek Manufacturing Identifier</i>