




PART NO.

13-60-4 DGZ

REVISIONS

ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
-	A	RELEASED	SID	29/9/12	AMU	29/5/12		12/6/12



Dimensions : Millimetres (Inches)

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.

TOLERANCES:

UNLESS OTHERWISE
SPECIFIED,
DIMENSIONS ARE
FOR REFERENCE
PURPOSES ONLY.

DRAWN BY:

SID

CHECKED BY:

AMU

APPROVED BY:

DATE:

29/05/12

DATE:

29/05/12

DATE:

12/06/12

DRAWING TITLE:

BNC Socket - Low Profile, PCB, Right AngleSIZE
A

DWG NO.

M10002230

ELECTRONIC FILE
1712352-TDS_DWGREV
A

SCALE: NTS

U.O.M.: mm (Inches)

SHEET: 1 OF 2



PART NO.

13-60-4 DGZ

REVISIONS

ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
-	A	RELEASED	SID	29/9/12	AMU	29/5/12		12/6/12

Specifications:

Mechanical Characteristics

Mating / Unmating : 500 cycles

Electrical Characteristics

Normal Impedance : 50 Ω
Frequency Range : 0 to 1 GHz
Testing Voltage : 500 V_{rms}
Dielectric Withstanding Voltage : 1,500 V_{rms}
Minimum Insulation Resistance : 5,000 M Ω

Environmental Characteristics

Temperature Range : -40°C to +60°C
Thermal Shock : MIL-STD-202, method 107, condition B
Physical Shock : MIL-STD-202, method 204, condition B

Specification Table

Item	Description	Material	Finish	Part Number
1	Mounting Post	Brass	Tin	13-60-4 DGZ
2	Housing	PBT +15% G.F	White	
3	Body	Zinc Alloy	Nickel	
4	Solder Pin	Copper Wire	Tin	
5	Insulation	Polypropylene	None	
6	Centre Contact	Phosphorous Bronze with Gold Plating at Contact Area Tin Plating at Tail	Gold Tin	
7	Nut	Brass	Nickel	
8	Lock Washer	S50C		

www.element14.com
www.farnell.com
www.newark.com

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:

SID

CHECKED BY:

AMU

APPROVED BY:

DATE:

29/05/12

DATE:

29/05/12

DATE:

12/06/12

DRAWING TITLE:

BNC Socket - Low Profile, PCB, Right Angle

SIZE	DWG NO.	ELECTRONIC FILE	REV
A	M10002230	1712352-TDS_DWG	A
SCALE: NTS		U.O.M.: mm (Inches)	SHEET: 2 OF 2