

7	6	5	4	3	2	1																																																																																										
NOTE:																																																																																																
1.MOLDED OVC RESIN,CABLE P/N & COLOR AS TABLE																																																																																																
<table><tr><td>COOL GREY</td><td>887800079</td><td>887808421</td><td>COOL GREY</td></tr><tr><td>BLACK</td><td>887800019</td><td>887808239</td><td>BLACK</td></tr><tr><td>FROST WITHE</td><td>887800043</td><td>887808249</td><td>FROST WITHE</td></tr><tr><td>RESIN COLOR</td><td>RESIN P/N</td><td>CABLE P/N</td><td>CABLE COLOR</td></tr></table>							COOL GREY	887800079	887808421	COOL GREY	BLACK	887800019	887808239	BLACK	FROST WITHE	887800043	887808249	FROST WITHE	RESIN COLOR	RESIN P/N	CABLE P/N	CABLE COLOR																																																																										
COOL GREY	887800079	887808421	COOL GREY																																																																																													
BLACK	887800019	887808239	BLACK																																																																																													
FROST WITHE	887800043	887808249	FROST WITHE																																																																																													
RESIN COLOR	RESIN P/N	CABLE P/N	CABLE COLOR																																																																																													
2.STICK UL LABEL ON EACH CARON.																																																																																																
ELECTRICAL PERFORMANCE																																																																																																
ALL TEST DUABILITY:0.01 SEC																																																																																																
1. DIELECTRONIC STRENGTH:500V DC																																																																																																
2. INSULATION RESISTANCE:100M OHMS MIN.																																																																																																
3. CONDUCTIVE RESISTANCE: 3 OHMS MAX.																																																																																																
4. ALL COMPOUENT MUST MEET RoHS COMPLIANCE.																																																																																																
<table><tr><td>88732-8816</td><td>1800±30</td><td>USB_A TO MINI_B 1.1 VER</td><td>88780-8239</td><td>88780-9091</td><td>88780-9090</td></tr><tr><td>88732-8713</td><td>1500±30</td><td>USB_A TO MINI_B 1.1 VER</td><td>88780-8421</td><td>88780-9091</td><td>88780-9090</td></tr><tr><td>88732-8912</td><td>2000±30</td><td>USB_A TO MINI_B 1.1 VER</td><td>88780-8239</td><td>88780-9091</td><td>88780-9090</td></tr><tr><td>88732-8812</td><td>1800±30</td><td>USB_A TO MINI_B 1.1 VER</td><td>88780-8239</td><td>88780-9091</td><td>88780-9090</td></tr><tr><td>88732-8712</td><td>1500±30</td><td>USB_A TO MINI_B 1.1 VER</td><td>88780-8239</td><td>88780-9091</td><td>88780-9090</td></tr><tr><td>88732-8612</td><td>1000±30</td><td>USB_A TO MINI_B 1.1 VER</td><td>88780-8239</td><td>88794-1218</td><td>88794-1217</td></tr><tr><td>88732-8512</td><td>800±30</td><td>USB_A TO MINI_B 1.1 VER</td><td>88780-8239</td><td>88794-1218</td><td>88794-1217</td></tr><tr><td>88732-8412</td><td>1200±30</td><td>USB_A TO MINI_B 1.1 VER</td><td>88780-8239</td><td>88780-9091</td><td>88780-9090</td></tr><tr><td>88732-8910</td><td>2000±30</td><td>USB_A TO MINI_B 1.1 VER</td><td>88780-8249</td><td>88780-9091</td><td>88780-9090</td></tr><tr><td>88732-8810</td><td>1800±30</td><td>USB_A TO MINI_B 1.1 VER</td><td>88780-8249</td><td>88780-9091</td><td>88780-9090</td></tr><tr><td>88732-8710</td><td>1500±30</td><td>USB_A TO MINI_B 1.1 VER</td><td>88780-8249</td><td>88780-9091</td><td>88780-9090</td></tr><tr><td>88732-8610</td><td>1000±30</td><td>USB_A TO MINI_B 1.1 VER</td><td>88780-8249</td><td>88794-1218</td><td>88794-1217</td></tr><tr><td>88732-8510</td><td>800±30</td><td>USB_A TO MINI_B 1.1 VER</td><td>88780-8249</td><td>88794-1218</td><td>88794-1217</td></tr><tr><td>88732-8410</td><td>1200±30</td><td>USB_A TO MINI_B 1.1 VER</td><td>88780-8249</td><td>88780-9091</td><td>88780-9090</td></tr><tr><td>MX P/N</td><td>CABLE LENGTH</td><td>DESCRIPTION</td><td>CABLE P/N</td><td>TERM. E</td><td>TERM. F</td></tr></table>							88732-8816	1800±30	USB_A TO MINI_B 1.1 VER	88780-8239	88780-9091	88780-9090	88732-8713	1500±30	USB_A TO MINI_B 1.1 VER	88780-8421	88780-9091	88780-9090	88732-8912	2000±30	USB_A TO MINI_B 1.1 VER	88780-8239	88780-9091	88780-9090	88732-8812	1800±30	USB_A TO MINI_B 1.1 VER	88780-8239	88780-9091	88780-9090	88732-8712	1500±30	USB_A TO MINI_B 1.1 VER	88780-8239	88780-9091	88780-9090	88732-8612	1000±30	USB_A TO MINI_B 1.1 VER	88780-8239	88794-1218	88794-1217	88732-8512	800±30	USB_A TO MINI_B 1.1 VER	88780-8239	88794-1218	88794-1217	88732-8412	1200±30	USB_A TO MINI_B 1.1 VER	88780-8239	88780-9091	88780-9090	88732-8910	2000±30	USB_A TO MINI_B 1.1 VER	88780-8249	88780-9091	88780-9090	88732-8810	1800±30	USB_A TO MINI_B 1.1 VER	88780-8249	88780-9091	88780-9090	88732-8710	1500±30	USB_A TO MINI_B 1.1 VER	88780-8249	88780-9091	88780-9090	88732-8610	1000±30	USB_A TO MINI_B 1.1 VER	88780-8249	88794-1218	88794-1217	88732-8510	800±30	USB_A TO MINI_B 1.1 VER	88780-8249	88794-1218	88794-1217	88732-8410	1200±30	USB_A TO MINI_B 1.1 VER	88780-8249	88780-9091	88780-9090	MX P/N	CABLE LENGTH	DESCRIPTION	CABLE P/N	TERM. E	TERM. F
88732-8816	1800±30	USB_A TO MINI_B 1.1 VER	88780-8239	88780-9091	88780-9090																																																																																											
88732-8713	1500±30	USB_A TO MINI_B 1.1 VER	88780-8421	88780-9091	88780-9090																																																																																											
88732-8912	2000±30	USB_A TO MINI_B 1.1 VER	88780-8239	88780-9091	88780-9090																																																																																											
88732-8812	1800±30	USB_A TO MINI_B 1.1 VER	88780-8239	88780-9091	88780-9090																																																																																											
88732-8712	1500±30	USB_A TO MINI_B 1.1 VER	88780-8239	88780-9091	88780-9090																																																																																											
88732-8612	1000±30	USB_A TO MINI_B 1.1 VER	88780-8239	88794-1218	88794-1217																																																																																											
88732-8512	800±30	USB_A TO MINI_B 1.1 VER	88780-8239	88794-1218	88794-1217																																																																																											
88732-8412	1200±30	USB_A TO MINI_B 1.1 VER	88780-8239	88780-9091	88780-9090																																																																																											
88732-8910	2000±30	USB_A TO MINI_B 1.1 VER	88780-8249	88780-9091	88780-9090																																																																																											
88732-8810	1800±30	USB_A TO MINI_B 1.1 VER	88780-8249	88780-9091	88780-9090																																																																																											
88732-8710	1500±30	USB_A TO MINI_B 1.1 VER	88780-8249	88780-9091	88780-9090																																																																																											
88732-8610	1000±30	USB_A TO MINI_B 1.1 VER	88780-8249	88794-1218	88794-1217																																																																																											
88732-8510	800±30	USB_A TO MINI_B 1.1 VER	88780-8249	88794-1218	88794-1217																																																																																											
88732-8410	1200±30	USB_A TO MINI_B 1.1 VER	88780-8249	88780-9091	88780-9090																																																																																											
MX P/N	CABLE LENGTH	DESCRIPTION	CABLE P/N	TERM. E	TERM. F																																																																																											
<table><tr><td rowspan="5">ENTER DESCRIPTION EC NO: DG2006-0150 DRWN:JFZHENG CHKD: APPR:DQLUO A</td><td rowspan="5">QUALITY SYMBOLS =0 =3</td><td colspan="2">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">DIMENSION STYLE MM ONLY</td><td>SCALE ---</td><td>DESIGN UNITS METRIC</td><td colspan="2">THIRD ANGLE PROJECTION</td></tr><tr><td></td><td>mm</td><td>INCH</td><td>DRAWN BY JFZHENG</td><td>DATE 2006/01/07</td><td colspan="4" rowspan="2">TITLE USB1.1, A TO MINIB CABLE ASS'Y(WHITE)</td></tr><tr><td>4 PLACES</td><td>± ---</td><td>± ---</td><td>CHECKED BY</td><td>DATE</td></tr><tr><td>3 PLACES</td><td>± ---</td><td>± ---</td><td>JFZHENG</td><td>2006/01/07</td><td colspan="4" rowspan="2">MOLEX INCORPORATED</td></tr><tr><td>2 PLACES</td><td>± ---</td><td>± ---</td><td>APPROVED BY</td><td>DATE</td></tr><tr><td>1 PLACE</td><td>± ---</td><td>± ---</td><td>DQLUO</td><td>2006/01/07</td><td colspan="4" rowspan="2">DOCUMENT NO. SD-887328510</td></tr><tr><td colspan="5">ANGULAR ±1/2°</td><td colspan="4" rowspan="2">SHEET NO. 2 OF 2</td></tr><tr><td colspan="5">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td></tr></table>							ENTER DESCRIPTION EC NO: DG2006-0150 DRWN:JFZHENG CHKD: APPR:DQLUO A	QUALITY SYMBOLS =0 =3	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			mm	INCH	DRAWN BY JFZHENG	DATE 2006/01/07	TITLE USB1.1, A TO MINIB CABLE ASS'Y(WHITE)				4 PLACES	± ---	± ---	CHECKED BY	DATE	3 PLACES	± ---	± ---	JFZHENG	2006/01/07	MOLEX INCORPORATED				2 PLACES	± ---	± ---	APPROVED BY	DATE	1 PLACE	± ---	± ---	DQLUO	2006/01/07	DOCUMENT NO. SD-887328510				ANGULAR ±1/2°					SHEET NO. 2 OF 2				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS																																	
ENTER DESCRIPTION EC NO: DG2006-0150 DRWN:JFZHENG CHKD: APPR:DQLUO A	QUALITY SYMBOLS =0 =3	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---			DESIGN UNITS METRIC	THIRD ANGLE PROJECTION																																																																																						
			mm	INCH	DRAWN BY JFZHENG	DATE 2006/01/07			TITLE USB1.1, A TO MINIB CABLE ASS'Y(WHITE)																																																																																							
		4 PLACES	± ---	± ---	CHECKED BY	DATE																																																																																										
		3 PLACES	± ---	± ---	JFZHENG	2006/01/07			MOLEX INCORPORATED																																																																																							
		2 PLACES	± ---	± ---	APPROVED BY	DATE																																																																																										
1 PLACE	± ---	± ---	DQLUO	2006/01/07	DOCUMENT NO. SD-887328510																																																																																											
ANGULAR ±1/2°									SHEET NO. 2 OF 2																																																																																							
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS																																																																																																
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																																																																
6	5	4	3	2	1																																																																																											