

TYPICAL INDICATOR ORDERING EXAMPLE

P01 — 12 — C — 1 — A

Lamps	
Incandescent	
06	6-volt
12	12-volt
18	18-volt
24	24-volt
28	28-volt
Neon	
N	110-volt

Cap Colors	
B	White
C	Red
D	Orange
E	Yellow
*F	Green
*G	Blue
*F & G not suitable with neon.	

Bezels	
1	.787" (20.0mm) Wide
2	.937" (23.8mm) Wide

Bezel Colors	
A	Black
B	White
C	Red
D	Orange
E	Yellow
F	Green
G	Blue
H	Gray

DESCRIPTION FOR TYPICAL ORDERING EXAMPLE

P01-12-C-1A



Note: Wire harness & cable assemblies offered only in Americas

LAMP CODES & SPECIFICATIONS

Incandescent & Neon Lamps for Solid & Design Caps

AT602 Incandescent  T- 1½ Pilot Slide Base	AT602N Neon 	L(+)  L(-)	06	12	18	24	28	N		
		Voltage	V	6V	12V	18V	24V	28V	110V	
		Current	I	80mA	50mA	35mA	25mA	22mA	1.5mA	
		MSCP	.159	.215	.398	.215	.247	NA		
		Endurance	Hours	2,000 Average						15,000 Avg.
		Ambient Temperature Range	-10° ~ +50°C							
		Recommended Resistor for Neon: 33K ohms for 110V AC & 100K ohms for 220V AC								


Electrical specifications are determined at a basic temperature of 25°C.
For dimension drawings of lamps, see Accessories & Hardware Index.
If the source voltage is greater than rated voltage, a ballast resistor is required.
The ballast resistor calculation and more lamp detail are shown in the Supplement section.

CAP COLORS


B	White	D	Orange	F	Green
C	Red	E	Yellow	G	Blue

Material: Polycarbonate Finish: Glossy F & G not suitable for neon


AT429




OPTIONAL BEZELS & COLORS



AT204
.787" (20.0mm) Wide Bezel



AT9201
.937" (23.8mm) Wide Bezel







Material: Polycarbonate

Standard Finish: Glossy

Color Codes: A Black B White C Red D Orange E Yellow F Green G Blue H Gray

TYPICAL INDICATOR DIMENSIONS





Without Bezel



P01-12-C

Panel Thickness:
 .039" ~ .157"
 (1.0mm ~ 4.0mm)





With Bezel



P01-12-C-1A

Panel Thickness:
 .039" ~ .157"
 (1.0mm ~ 4.0mm)

With Large Bezel



P01-12-C-2A

Panel Thickness:
 .039" ~ .157"
 (1.0mm ~ 4.0mm)