



Dimensions (mm)

tolerances according to DIN ISO 2768-m
Toleranzen gem. DIN ISO 2768-m



Isometric

Scale 1:2
Massstab 1:2



Cable

silicone high voltage wire AWG20
UL-Style 3239

colour white

Silikon Hochspannungslitze AWG20

UL-Style 3239

Farbe weiss


Terminals

ends tinned

Enden verzinkt

Layout

Top View
Draufsicht



Marking

according to EN60062/factory code
gem. EN60062/Fertigungsstätte



Coil Data at 20 °C	Conditions	Min	Typ	Max	Unit
Coil resistance		94	105	116	Ohm
Coil voltage			6		VDC
Rated power			342		mW
Thermal resistance	max. Relay temperature = operating temperature + self heating		20		K/W
Inductance			60,6		mH
Pull-In voltage				4,5	VDC
Drop-Out voltage		0,8			VDC

Contact data 83	Conditions	Min	Typ	Max	Unit
Contact rating	Any DC combination of V & A not to exceed their individual max.'s			50	W
Switching voltage	DC or Peak AC			7.500	V
Switching current	DC or Peak AC			3	A
Carry current	DC or Peak AC			5	A
Contact resistance static	Measured with 40% overdrive Start Value			150	mOhm
Insulation resistance	RH <45 %, 100 V test voltage	10			TOhm
Breakdown voltage	according to EN 60255-5	10			kV DC
Operate time incl. bounce	measured with 40% overdrive			3,2	ms
Release time	measured with no coil excitation			1,5	ms
Capacitance	@ 10 kHz across open switch		2,3		pF

Special Product Data	Conditions	Min	Typ	Max	Unit
Number of contacts			1		
Contact - form			B - NC		
Dielectric Strength Coil/Contact	according to EN 60255-5	7,5			kV DC
Insulation resistance Coil/Contact	RH <45%, 200 VDC test voltage	1			TOhm
Capacity Coil/Contact	@ 10 kHz		4,8		pF
Case colour			grey		
Housing material			Polycarbonat		
Sealing compound			Polyurethan		
Connection pins			Copper alloy tin plated		
Reach / RoHS conformity			yes		



Products for
tomorrow...

Europe: +49 / 7731 8399 0 | Email: info@meder.com
USA: +1 / 508 295 0771 | Email: salesusa@meder.com
Asia: +852 / 2955 1682 | Email: salesasia@meder.com

Item No.:

8506183152

Item:

HE06-1B83-150

Environmental data	Conditions	Min	Typ	Max	Unit
Shock	1/2 sine wave duration 11ms			50	g
Vibration	from 10 - 2000 Hz			20	g
Operating temperature		-20		70	°C
Storage temperature		-35		105	°C
Soldering temperature	wave soldering max. 5 sec.			260	°C

General data	Conditions	Min	Typ	Max	Unit
Total weight			57,2		g
Packaging			Cardboard Box 10pcs/each		

Modifications in the sense of technical progress are reserved

Designed at: 17.08.09 Designed by: WKOVACS
Last Change at: 22.05.12 Last Change by: WKOVACS

Approval at: 18.08.09 Approval by: KOLBRICH
Approval at: 23.05.12 Approval by: CRUF

Version: 04