


# MALE PCB PINS

## PRINTED CIRCUIT PINS

### 3116

3116-X-00-XX-00-00-08-0

Swage mount in .052 hole




| Basic Part Number | Board Thickness | Length V | Depth D |
|-------------------|-----------------|----------|---------|
| 3116-1            | .031            | .051     | .035    |
| 3116-2            | .062            | .082     | .062    |
| 3116-3            | .094            | .113     | .062    |
| 3116-4            | .125            | .145     | .062    |

### X435

X435-X-05-XX-00-00-03-0

Square press-fit in .022 plated through-hole




| Basic Part Number | Length L |
|-------------------|----------|
| 5435-0            | .303     |
| 5435-1            | .200     |
| 5435-2            | .413     |
| 6435-0            | .280     |

### 3135

3135-1-00-XX-00-00-08-0


Swage mount in .040 hole  
For .031 thick board



### 3210

3210-2-00-XX-00-00-08-0


Swage mount in .031 hole  
For .062 thick board



### 3129

3129-1-00-XX-00-00-08-0


Swage mount in .035 hole  
For .031 thick board



### 3147

3147-3-00-XX-00-00-08-0


Swage mount in .043 hole  
For .094 thick board



### 4366

4366-0-00-XX-00-00-03-0


Hex press-fit in .034 plated through-hole



### 1267

1267-0-00-XX-00-00-03-0


Press-fit in .035 mounting hole



### 7827

7827-0-00-XX-00-00-03-0


Press-fit in .035 mounting hole



### 1130

1130-0-00-XX-00-00-03-0

Press-fit in .057 mounting hole  
Pin material is Phosphor Bronze 544 (B2)



#### SPECIFICATIONS:

**Pin Material:** Brass Alloy 360, 1/2 Hard  
(Except where noted)

**Dimensions:** Inches

**Tolerances On:** Lengths:  $\pm .005$   
Diameters:  $\pm .002$   
Angles:  $\pm 2^\circ$



**ORDER CODE:** XXXX - X - 0X - XX - 00 - 00 - XX - 0

**BASIC PART #**

**SPECIFY PIN FINISH:**

- 01 200  $\mu$ " TIN/LEAD OVER NICKEL
- ◆ 80 200  $\mu$ " TIN OVER NICKEL (RoHS)
- ◆ 15 10  $\mu$ " GOLD OVER NICKEL (RoHS)
- ◆ 21 20  $\mu$ " GOLD OVER NICKEL (RoHS)
- ◆ 34 50  $\mu$ " GOLD OVER NICKEL (RoHS)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com