







RETENTION BARB TYPE SHOWN ON ALL SHEET UNLESS OTHERWISE NOTED

- △ MATERIALS:
- | | |
|-----------------|----------------------------------|
| HOUSING: | HIGH TEMPERATURE NYLON, UL94 V-0 |
| EXTRACTOR: | HIGH TEMPERATURE NYLON, UL94 V-0 |
| CONTACTS: | COPPER ALLOY |
| RETENTION BARB: | BRASS, TIN PLATED |
- △ INTERFACE FINISH:
- (1) 0.00038 MIN THK GOLD OVER 0.00127 MIN THK NICKEL.
 - (2) 0.00008 MIN THK GOLD OVER 0.00127 MIN THK NICKEL.
 - (3) 0.00076 MIN THK GOLD OVER 0.00127 MIN THK NICKEL.
- △ FINISHED HOLE SIZE. 0.15 MAXIMUM ANNULAR RING.
- △ KEEP OUT ZONE.
- △ KEEP OUT AREA RESERVED FOR SOCKET EXTRACTORS, BOTH ENDS.
- △ SOLDER TAIL FINISH:
- 0.00300 MIN THK MATTE TIN OVER 0.00127 MIN THK NICKEL.
- △ LED LOCATION AS APPLICABLE PER CUSTOMER.
- △ DATUM -G- IS CONNECTOR SIDE SURFACE OF PCB.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: 28FB2007 LEO ZHOU CHK: 28FB2007 STEVEN YAO		 TE Connectivity	
DIMENSIONS: mm		APVD: 28FB2007 STEVEN YAO			
TOLERANCES UNLESS OTHERWISE SPECIFIED: 		PRODUCT SPEC 108-2256 APPLICATION SPEC 114-13154		NAME SOCKET ASSEMBLY, VERTICAL DDR3 DIMM, SOLDER TAIL, 240 POSITION	
MATERIAL 		FINISH 		SIZE A1	CAGE CODE 00779
		WEIGHT -		DRAWING NO C-1932000	
		CUSTOMER DRAWING		SCALE 4:1 SHEET 1 of 4 REV H-7	



