






NOTES:

1. MAIN BODY, ZINC DIECAST, BRIGHT TIN PLATED
2. GASKET, STAMPED, PHOSPHOR BRONZE, BRIGHT TIN PLATED
3. DOOR, ZINC DIECAST, BRIGHT NICKEL PLATED
4. EMI COVER, STAMPED BRASS ALLOY, BRIGHT TIN PLATED
5. TORSION SPRING, STAINLESS STEEL
6. BACK SIDE OF FRONT PANEL TO BE CONDUCTIVE.
7. MAXIMUM GASKET HEIGHT AND WIDTH WHEN INSERTED INTO FRONT PANEL, .682 AND 1.488 RESPECTIVELY.
8. -1001 VERSION DOES NOT HAVE THE MOLEX LOGO ON THE DOOR
9. DOOR IS BRIGHT TIN PLATED

ENTER DESCRIPTION		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
EC NO: USY2007-0073		2006/09/05		mm		MM/IN		DATE		METRIC		DATE	
DRAWN: JERWIN		2006/09/05		4 PLACES ± --- ± ---		DRAWN BY		JERWIN		2006/08/28		DATE	
CHKD: JERWIN		2006/09/05		3 PLACES ± --- ± .005		CHECKED BY		DDOYE		2006/08/28		DATE	
APPR: DDOYE		2006/09/05		2 PLACES ± 0.13 ± ---		APPROVED BY		DDOYE		2006/08/28		DATE	
				1 PLACE ± --- ± ---		MATERIAL NO.							
				ANGULAR ± --- °		SIZE		SEE CHART		SD-73847-001		SHEET NO.	
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS								1 OF 2	

PCB THICKNESS	"B"	PART NUMBER
.062 (1.57)	.123 (3.12)	73847-1007
.093 (2.36)	.154 (3.91)	73847-0004
.100 (2.54)	.161 (4.09)	73847-0003
.085 (2.16)	.146 (3.71)	73847-0002
.062 (1.57)	.123 (3.12)	73847-0001
.062 (1.57)	.123 (3.12)	73847-1001



—FRONT PANEL

— PCB

tb_frame_C_P_AM_T
Rev. D 2004/06/28