



## Optocoupler, Phototriac Output, High dV/dt, Low Input Current



### DESCRIPTION

The IL4216, IL4217, IL4218 consists of an AlGaAs IRLED optically coupled to a pair of photosensitive non-zero crossing SCR chips and are connected inversely parallel to form a TRIAC. These three semiconductors are assembled in a six pin 0.3 inch dual in-line package.

High input sensitivity is achieved by using an emitter follower phototransistor and a cascaded SCR predriver resulting in an LED trigger current of less than 1.3 mA (DC). The use of a proprietary dV/dt clamp results in a static dV/dt of greater than 10 kV/μs. This clamp circuit has a MOSFET that is enhanced when high dV/dt spikes occur between MT1 and MT2 of the TRIAC. The FET clamps the base of the phototransistor when conducting, disabling the internal SCR predriver.

The blocking voltage of up to 800 V permits control of off-line voltages up to 240 V<sub>AC</sub>, with a safety factor more than two, and is sufficient for as much as 380 V<sub>AC</sub>. Current handling capability is up to 300 mA RMS, continuous at 25 °C.

The IL4216, IL4217, IL4218 isolates low-voltage logic from 120, 240, and 380 VAC lines to control resistive inductive, or capacitive loads including motors solenoids, high current thyristors or TRIAC and relays.

### FEATURES

- High input sensitivity  $I_{FT} = 1.3$  mA
- 300 mA on-state current
- High static dV/dt 10000 V/μs, typical
- Very low leakage  $< 10$  μA
- Isolation test voltage 5300 V<sub>RMS</sub>
- Compliant to RoHS Directive 2002/95/EC and in accordance to WEEE 2002/96/EC



**RoHS**  
COMPLIANT

### APPLICATIONS

- Solid state relay
- Industrial controls
- Office equipment
- Consumer appliances

### AGENCY APPROVALS

- UL1577, file no. E52744 system code J
- CSA 93751
- DIN EN 60747-5-5 (VDE 0884) available with option 1
- BSI IEC60950; IEC60065
- FIMKO

### ORDERING INFORMATION

<input type="text"/> I	<input type="text"/> L	<input type="text"/> 4	<input type="text"/> 2	<input type="text"/> 1	<input type="text"/> #	<input type="text"/> -	<input type="text"/> X	<input type="text"/> 0	<input type="text"/> #	<input type="text"/> #	<input type="text"/> T	DIP	Option 6				
PART NUMBER						PACKAGE OPTION				TAPE AND REEL							
										7.62 mm							
										10.16 mm							
										Option 7		Option 9					
										> 0.7 mm		> 0.1 mm					

#### AGENCY CERTIFIED/PACKAGE

#### UL, cUL, BSI, FIMKO

	600	700	800
DIP-6	IL4216	IL4217	IL4218
DIP-6, 400 mil, option 6	IL4216-X006	-	IL4218-X006
SMD-6, option 7	IL4216-X007T	IL4217-X007	-
SMD-6, option 9	IL4216-X009T <sup>(1)</sup>	IL4217-X009	-

#### VDE, UL, cUL, BSI, FIMKO

	600	700	800
DIP-6	IL4216-X001	-	IL4218-X001
DIP-6, 400 mil, option 6	IL4216-X016	-	IL4218-X016
SMD-6, option 7	-	-	IL4218-X017T <sup>(1)</sup>
SMD-6, option 9	-	-	IL4218-X019T <sup>(1)</sup>

#### Note

<sup>(1)</sup> Also available in tubes, do not put T on the end.

# IL4216, IL4217, IL4218

Vishay Semiconductors

Optocoupler, Phototriac Output,  
High dV/dt, Low Input Current



## ABSOLUTE MAXIMUM RATINGS <sup>(1)</sup> ( $T_{amb} = 25^{\circ}C$ , unless otherwise specified)

PARAMETER	TEST CONDITION	PART	SYMBOL	VALUE	UNIT
<b>INPUT</b>					
Reverse voltage			$V_R$	6	V
Forward current			$I_F$	60	mA
Surge current			$I_{FSM}$	2.5	A
Power dissipation			$P_{diss}$	100	mW
Derate linearly from $25^{\circ}C$				1.33	mW/ $^{\circ}C$
Thermal resistance			$R_{th}$	750	$^{\circ}C/W$
<b>OUTPUT</b>					
Peak off-state voltage		IL4216	$V_{DRM}$	600	V
		IL4217	$V_{DRM}$	700	V
		IL4218	$V_{DRM}$	800	V
RMS on-state current			$I_{DRM}$	300	mA
Single cycle surge			$I_{TSM}$	3	A
Power dissipation			$P_{diss}$	300	mW
Derate linearly from $25^{\circ}C$				6.6	mW/ $^{\circ}C$
Thermal resistance			$R_{th}$	150	$^{\circ}C/W$
<b>COUPLER</b>					
Creepage distance				$\geq 7$	mm
Clearance				$\geq 7$	mm
Storage temperature			$T_{stg}$	- 55 to + 150	$^{\circ}C$
Ambient temperature			$T_{amb}$	- 55 to + 100	$^{\circ}C$
Isolation test voltage			$V_{ISO}$	5300	$V_{RMS}$
Isolation resistance	$V_{IO} = 500 V, T_{amb} = 25^{\circ}C$		$R_{IO}$	$\geq 10^{12}$	$\Omega$
	$V_{IO} = 500 V, T_{amb} = 100^{\circ}C$		$R_{IO}$	$\geq 10^{11}$	$\Omega$
Lead soldering temperature <sup>(2)</sup>	5 s		$T_{sld}$	260	$^{\circ}C$

### Notes

<sup>(1)</sup> Stresses in excess of the absolute maximum ratings can cause permanent damage to the device. Functional operation of the device is not implied at these or any other conditions in excess of those given in the operational sections of this document. Exposure to absolute maximum ratings for extended periods of the time can adversely affect reliability.

<sup>(2)</sup> Refer to reflow profile for soldering conditions for surface mounted devices (SMD). Refer to wave profile for soldering conditions for through hole devices (DIP).

<b>ELECTRICAL CHARACTERISTICS</b> ( $T_{amb} = 25^\circ C$ , unless otherwise specified)							
PARAMETER	TEST CONDITION	PART	SYMBOL	MIN.	TYP.	MAX.	UNIT
<b>INPUT</b>							
Forward voltage	$I_F = 20 \text{ mA}$		$V_F$		1.3	1.5	V
Breakdown voltage	$I_R = 10 \mu\text{A}$		$V_{BR}$	6	30		V
Reverse current	$V_R = 6 \text{ V}$		$I_R$		0.1	10	$\mu\text{A}$
Input capacitance	$V_F = 0 \text{ V}, f = 1 \text{ MHz}$		$C_{IN}$		40		$\text{pF}$
Thermal resistance, junction to lead			$R_{thjl}$		750		$^\circ\text{C}/\text{W}$
<b>OUTPUT</b>							
Repetitive peak off-state voltage	$I_{DRM} = 100 \mu\text{A}$	IL4216	$V_{DRM}$	600	650		V
		IL4217	$V_{DRM}$	700	750		V
		IL4218	$V_{DRM}$	800	850		V
Off-state voltage	$I_{D(RMS)} = 70 \mu\text{A}$	IL4216	$V_{D(RMS)}$	424	460		V
		IL4217	$V_{D(RMS)}$	484	536		V
		IL4218	$V_{D(RMS)}$	565	613		V
Off-state current	$V_D = 600 \text{ V}, T_{amb} = 100^\circ C$		$I_{D(RMS)}$		10	100	$\mu\text{A}$
Reverse current	$V_R = 600 \text{ V}, T_{amb} = 25^\circ C$		$I_{RMS}$		10	100	$\mu\text{A}$
On-state voltage	$I_T = 300 \text{ mA}$		$V_{TM}$		1.7	3	V
On-state current	$PF = 1, V_{T(RMS)} = 1.7 \text{ V}$		$I_{TM}$			300	$\text{mA}$
Surge (non-repetitive, on-state current)	$f = 50 \text{ Hz}$		$I_{TSM}$			3	A
Holding current	$V_T = 3 \text{ V}$		$I_H$		65	200	$\mu\text{A}$
Latching current	$V_T = 2.2 \text{ V}$		$I_L$			500	$\mu\text{A}$
LED trigger current	$V_{AK} = 5 \text{ V}$		$I_{FT}$		0.7		$\text{mA}$
Critical rate of rise of off-state voltage	$V_D = 0.67 V_{DRM}, T_{amb} = 25^\circ C$		$dV/dt_{cr}$	10 000			$\text{V}/\mu\text{s}$
	$V_D = 0.67 V_{DRM}, T_{amb} = 80^\circ C$		$dV/dt_{cr}$	5000			$\text{V}/\mu\text{s}$
Critical rate of rise of voltage at current commutation	$V_D = 230 V_{RMS}, I_D = 300 \text{ mA}_{RMS}, T_J = 25^\circ C$		$dV/dt_{crq}$		8		$\text{V}/\mu\text{s}$
	$V_D = 230 V_{RMS}, I_D = 300 \text{ mA}_{RMS}, T_J = 85^\circ C$		$dV/dt_{crq}$		7		$\text{V}/\mu\text{s}$
Critical rate of rise of on-state current commutation	$V_D = 230 V_{RMS}, I_D = 300 \text{ mA}_{RMS}, T_J = 25^\circ C$		$dI/dt_{crq}$		12		$\text{A}/\mu\text{s}$
Thermal resistance, junction to lead			$R_{thjl}$		150		$^\circ\text{C}/\text{W}$
<b>COUPLER</b>							
Capacitance (input to output)	$f = 1 \text{ MHz}, V_{IO} = 0 \text{ V}$		$C_{IO}$		0.8		$\text{pF}$
Critical rate of rise of coupled input to output voltage	$I_T = 0, V_{RM} = V_{DM} = 300 \text{ VAC}$		$dV_{(IO)}/dt$	5000	1		$\text{mA}$

**Note**

- Minimum and maximum values are testing requirements. Typical values are characteristics of the device and are the result of engineering evaluation. Typical values are for information only and are not part of the testing requirements.

**POWER FACTOR CONSIDERATIONS**

A snubber is not needed to eliminate false operation of the TRIAC driver because of the IL4216, IL4217, IL4218 high static and commutating dV/dt with loads between 1 and 0.8 power factors. When inductive loads with power factors less than 0.8 are being driven, include a RC snubber or a single capacitor directly across the device to damp the peak commutating dV/dt spike. Normally a commutating dV/dt causes a turning-off device to stay on due to the stored energy remaining in the turning-off device.




Fig. 1 - Shunt Capacitance vs. Load Current vs. Power Factor

### TYPICAL CHARACTERISTICS (T<sub>amb</sub> = 25 °C, unless otherwise specified)




Fig. 2 - LED Forward Current vs. Forward Voltage




Fig. 5 - Maximum LED Power Dissipation




Fig. 3 - Forward Voltage vs. Forward Current




Fig. 6 - On-State Terminal Voltage vs. Terminal Current




Fig. 4 - Peak LED Current vs. Duty Factor,  $\tau$






Fig. 7 - Maximum Output Power Dissipation

**PACKAGE DIMENSIONS** in millimeters


## **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.