




NOTES:  
# PLATING: 0,5µm MIN. TIN OVER NICKEL.  
2 PLATING:

| PARTNUMBER | PERFORMANCE LEVEL                                                                                                                                                       |
|------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 2042162-1  | PERFORMANCE LEVEL 1: CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE QUALITY LEVEL III: UNCONTROLLED ENVIRONMENT APPLICATIONS. SEE PRODUCT SPEC 108-19353 |
| 2042162-2  | PERFORMANCE LEVEL 2: CONFORMS TO ALL TESTING ACCORDING PRODUCT SPEC 108-19320, -250 MATING CYCLES, 4 DAYS MIXED GAS TEST PER IEC 60068-2-60 METHOD I                    |

3 CONSULT APPLICATION SPEC OR CONTACT TE CONNECTIVITY FOR PERMISSIBLE CONTACT ASSIGNMENTS.  
4 CONNECTOR MARKED WITH PARTNUMBER AND DATE CODE.  
5 FOR PC-BOARD ROUTING RECOMMENDATIONS SEE SPEC 114-19140

THIS DRAWING IS A CONTROLLED DOCUMENT.  
DIMENSIONS: mm  
TOLERANCES UNLESS OTHERWISE SPECIFIED:  
0 PLC ±  
1 PLC ±  
2 PLC ±  
3 PLC ±  
4 PLC ±  
ANGLES ±  
FINISH  
MATERIAL -

DWN RA 21-Jan-09  
CHK RA 21-Jan-09  
APVD MW 21-Jan-09  
PRODUCT SPEC SEE NOTE  
APPLICATION SPEC 114-19106  
WEIGHT -  
CUSTOMER DRAWING

| ITEM NO. | DESCRIPTION | MATERIAL           |
|----------|-------------|--------------------|
| 3        | OVERMOLD    | LCP 30% GF NATURAL |
| 2        | HOUSING     | LCP 30% GF NATURAL |
| 1        | CONTACT     | COPPER ALLOY       |

TE Connectivity  
NAME RIGHT ANGLE MALE CONNECTOR Z-PACK Slim UHD High Speed  
SIZE A2 CAGE CODE 00779 DRAWING NO C-2042162 RESTRICTED TO -  
SCALE 5:1 SHEET 1 OF 1 REV A