


Sealed Snap Action Switch

D2VW

Watertight Miniature Snap Action Switch

- High-quality watertight, high-precision miniature Snap Action switch. Switch Body meets IP67 requirements
- Use of epoxy resin assures high sealing capability and is ideal for dusty places or where water is sprayed
- V-series internal mechanism assures high precision and long life
- General-load (5 A at 250 VAC) models and micro-load models are available
- RoHS Compliant



Ordering Information

Actuator		Terminal	Model	
			Model 0.1 A	Model 5 A
Pin plunger		With solder and #187 tab terminals	D2VW-01-1HS	D2VW-5-1HS
		With lead wires	D2VW-01-1MS	D2VW-5-1MS
Short hinge lever		With solder and #187 tab terminals	D2VW-01L1A-1HS	D2VW-5L1A-1HS
		With lead wires	D2VW-01L1A-1MS	D2VW-5L1A-1MS
Hinge lever		With solder and #187 tab terminals	D2VW-01L1-1HS	D2VW-5L1-1HS
		With lead wires	D2VW-01L1-1MS	D2VW-5L1-1MS
Long hinge lever		With solder and #187 tab terminals	D2VW-01L1B-1HS	D2VW-5L1B-1HS
		With lead wires	D2VW-01L1B-1MS	D2VW-5L1B-1MS
Simulated roller lever		With solder and #187 tab terminals	D2VW-01L3-1HS	D2VW-5L3-1HS
		With lead wires	D2VW-01L3-1MS	D2VW-5L3-1MS
Short hinge roller lever		With solder and #187 tab terminals	D2VW-01L2A-1HS	D2VW-5L2A-1HS
		With lead wires	D2VW-01L2A-1MS	D2VW-5L2A-1MS
Hinge roller lever		With solder and #187 tab terminals	D2VW-01L2-1HS	D2VW-5L2-1HS
		With lead wires	D2VW-01L2-1MS	D2VW-5L2-1MS

- Note:** 1. The standard lengths of the lead wires (UL1015 AWG20 for UL/CSA models, AW0.75f otherwise) of models incorporating them are 300 mm. Add "-0" to the end of the part number to obtain 1,000 mm long wires. (e.g.: D2VW-5L2A-1MS-0)
2. Remove "-HS" from the end of solder/quick-connect models to obtain non-UL/CSA versions. (e.g.: D2VW-01-1HS → D2VW-01-1)
3. Remove "S" from the end of lead wire models to obtain non-UL/CSA versions with AW0.75f wire. (e.g.: D2VW-5L3-1MS → D2VW-5L3-1M)

Model Number Legend

D2VW- - -

1 2 3 4 5

- | | | | |
|---|--|---|--|
| 1. Ratings
5: 5 A at 250 VAC
01: 0.1 A at 30 VDC | 2. Actuator
None: Pin plunger
L1A: Short hinge lever
L1: Hinge lever
L1B: Long hinge lever
L3: Simulated roller lever
L2A: Short hinge roller lever
L2: Hinge roller lever | 3. Contact Form
1: SPDT
2: SPST-NC
3: SPST-NO | 4. Terminals
None, HS: Solder terminals
(HS for UL and CSA approval.)
M, MS: Molded lead wires
(MS for UL and CSA approval.)

5. Length of the molded lead wire
None: 300 mm
0: 1,000 mm |
|---|--|---|--|

Specifications

■ Characteristics

Model		D2VW-01	D2VW-5
Operating speed		0.1 mm to 1 m/s (at pin plunger)	
Operating frequency		Mechanical: 300 operations/minute max. Electrical: 60 operations/minute max.	
Insulation resistance		100 MΩ min. (at 500 VDC)	
Contact resistance		50 mΩ max. for solder terminal models 100 mΩ max. for 300 mm molded lead wire models 200 mΩ max. for 1,000 mm molded lead wire models	
Dielectric strength (See note 2)		1,000 VAC, 50/60 Hz for 1 min. between terminals of the same polarity 1,500 VAC, 50/60 Hz for 1 min. between each current-carrying metal parts and ground, and between each terminal and non-current-carrying metal parts.	
Vibration resistance (See note 3)		Malfunction: 10 to 55 Hz, 1.5 mm double amplitude	
Shock resistance (See note 3)		Destruction: 1,000 m/s ² (approx. 100G) max. Malfunction: 300 m/s ² (approx. 30G) max.	
Degree of protection		IEC IP67 (excluding the terminals on terminal models).	
Degree of protection against electric shock		Class I	
Proof tracking index (PTI)		175	
Ambient operating temperature		-40° to 85°C (at 60% RH max.) with no icing	
Ambient operating humidity		95% max. (for 5°C to 35°C)	
Life expectancy	Mechanical	10,000,000 operations min. at 60 operations per minute	
	Electrical	1,000,000 operations min. at 30 ops. per minute.	100,000 operations min. at 30 ops. per minute
Weight		Approx. 7g (pin plunger models without wires)	

Note: 1. Data shown are of initial value.

2. The dielectric strength shown is measured using a separator between the switch and metal mounting plate.

3. For the pin plunger models, the above values apply for use at the free position and total travel position. For the lever models, the values apply at the total travel position.

4. The operating temperature of the lead wire (AV0.75f) for non-UL/CSA molded lead wire models is between -40 to 85°C.

■ Ratings (reference values)

D2VW-5

Rated Voltage	Non-inductive load				Inductive load			
	Resistive load		Lamp load		Inductive load		Motor load	
	NC	NO	NC	NO	NC	NO	NC	NO
125 VAC	5 A		0.5 A		4 A		—	
250 VAC	5 A		0.5 A		4 A		—	
30 VDC	5 A		3 A		4 A		—	
125 VDC	0.4 A		0.1 A		0.4 A		—	

D2VW-01

Rated Voltage	Non-inductive load				Inductive load			
	Resistive load		Lamp load		Inductive load		Motor load	
	NC	NO	NC	NO	NC	NO	NC	NO
125 VAC	0.1 A		—		—		—	
30 VDC	0.1 A		—		—		—	

Note: 1. The resistive load ratings apply under the following test conditions:

Ambient Temperature = 20±2°C, Ambient Humidity = 65±5%, Operating frequency = 30 operations/min.

2. The above current ratings are the values of the steady-state current.

3. Inductive load has a power factor of 0.7 min. (AC) and a time constant of 7 ms max. (DC).

4. Lamp load has an inrush current of 10 times the steady-state current.

5. Rating for UL/CSA approval is as follows (See "Approved Standards" section):

D2VW-01 0.1A @ 125 VAC

0.1A @ 30 VDC

D2VW-5 3A @ 125 VAC, 250 VAC

Approved Standards

Consult your OMRON sales representative for specific models with standard approvals.

UL Recognized, CSA Certified

Rated Voltage	D2VW-5	D2VW-01
125 VAC	3 A	0.1 A
250 VAC	3 A	---
30 VDC	---	0.1 A

EN 61058-1 (VDE Approval)

Rated Voltage	D2VW-5	D2VW-01
125 VAC	---	0.1 A
250 VAC	3 A	---

Testing conditions:

25E3 (25,000 operations), T55 (0°C to 55°C) for D2VW-5
1E5 (100,000 operations), T85 (0°C to 85°C) for D2VW-01

Contact Specifications


Item	D2VW-5	D2VW-01
Specification	Rivet	Crossbar
Material	Silver alloy	Gold alloy
Gap (standard value)	0.5 mm	
Inrush current	NC: 15 A max. NO: 15 A max.	---
Minimum applicable load (see note)	160 mA at 5 VDC	1 mA at 5 VDC

Note: Minimum applicable loads are indicated by N standard reference values. This value represents the failure rate at a 60% (λ_{60}) reliability level (JIS C5003).
The equation $\lambda_{60}=0.5 \times 10^{-6}$ / operations indicates that a failure rate of less than 1/2,000,000 operations can be expected at a reliability level of 60%


Engineering Data

Structure


SPDT



SPST-NC




SPST-NO



Note: Colors in parentheses indicate lead wire colors.

Mounting

All switches may be panel mounted using M3 mounting screws with plane washers or spring washers to securely mount the switch. Tighten the screws to a torque of 0.39 to 0.59 N·m.




Dimensions

■ Terminals


Note: 1. Unless otherwise specified, all units are in millimeters and a tolerance of ± 0.4 mm applies to all dimensions

2. The pin plunger model is shown here as a typical example for both the solder/quick connect terminals and the molded lead wire versions.

Solder/Quick Connect Terminals



Molded Lead Wires



* UL/CSA approved models have AWG20 UL1015 approved wiring.

	300 mm type	1,000 mm type
L	300 ± 10 mm	1,000 ± 30 mm

■ Dimensions and Operating Characteristics



Note: 1. Unless otherwise specified, all units are in millimeters and a tolerance of ± 0.4 mm applies to all dimensions

2. Omitted dimensions are the same as pin plunger type.

3. The operating characteristics are for operation in the A direction(▼)

Pin Plunger Models



D2VW-01-1HS
D2VW-5-1HS



OF max	200 gf
RF min.	30 gf
PT max.	1.2 mm
OT min.	1.0 mm
MD max.	0.4 mm
OP	14.7 ± 0.4 mm

Short Hinge Lever Models



D2VW-01L1A-1MS
D2VW-5L1A-1MS



OF max	200 gf
RF min.	20 gf
PT max.	1.6 mm
OT min.	0.8 mm
MD max.	0.5 mm
OP	15.2 ± 0.5 mm

Hinge Lever Models

D2VW-01L1-1MS
D2VW-5L1-1MS




OF max	120 gf
RF min.	15 gf
PT max.	4.0 mm
OT min.	1.6 mm
MD max.	0.8 mm
OP	15.2 ± 1.2 mm

- Note:** 1. Unless otherwise specified, all units are in millimeters and a tolerance of ± 0.4 mm applies to all dimensions
 2. Omitted dimensions are the same as pin plunger type.
 3. The operating characteristics are for operation in the A direction(↓)

Long Hinge Lever Models


D2VW-01L1B-1MS
 D2VW-5L1B-1MS



OF max	60 gf
RF min.	5 gf
PT max.	9.0 mm
OT min.	3.2 mm
MD max.	2.0 mm
OP	15.2 ± 2.6 mm

Simulated Roller Lever Models


D2VW-01L3-1MS
 D2VW-5L3-1MS



OF max	120 gf
RF min.	15 gf
PT max.	4.0 mm
OT min.	1.6 mm
MD max.	0.8 mm
OP	18.7 ± 1.2 mm

Short Hinge Roller Lever Models


D2VW-01L2A-1MS
 D2VW-5L2A-1MS



OF max	230 gf
RF min.	20 gf
PT max.	1.6 mm
OT min.	0.8 mm
MD max.	0.5 mm
OP	20.7 ± 0.6 mm

Hinge Roller Lever Models

D2VW-01L2-1MS
 D2VW-5L2-1MS



OF max	120 gf
RF min.	15 gf
PT max.	4.0 mm
OT min.	1.6 mm
MD max.	0.8 mm
OP	20.7 ± 1.2 mm

Precautions

Be sure to read the precautions and information common to all Snap Action and Detection Switches, contained in the Technical User's Guide, "Snap Action Switches, Technical Information" for correct use.


■ Correct Use

Operations

Make sure that the switching object is perfectly separated from the actuator when the switch is not operated and the actuator is pressed appropriately by the switching object when the switch is operated.

The switch should be set so that its stroke will be within the rated OT when the switch is operated.

With the pin plunger models, set the switch so that the plunger can be actuated from directly above. Since the plunger is covered with a rubber cap, applying a force from lateral directions may cause damage to the plunger or reduction in the sealing capability.




Handling

Handle the switch carefully so as not to break the sealing rubber of the plunger.

Using Microloads

Using a model for ordinary loads to switch microloads may result in faulty operation. Instead, use the models that are designed for microloads and that operate in the following range;



However, even when using microload models within the operating range shown above, if inrush current or inductive voltage spikes occur when the contact is opened or closed, then contact wear may increase and so decrease the service life. Therefore, insert a contact protection circuit where necessary.

Soldering - Connecting to Solder Terminals

When soldering the lead wire to the terminal, first insert the lead wire conductor through the terminal hole and then conduct soldering.

Complete the soldering at the iron tip temperature between 350 to 400 C within 3 seconds, and do not apply any external force for 1 minute after soldering. Soldering at an excessively high temperature or soldering for more than 3 seconds may deteriorate the characteristics of the switch.

Mounting

Use M3 mounting screws with plane washers or spring washers to securely mount the switch.

Tighten the screws to a torque of 0.39 to 0.59 N·m (4 to 6 kgf·cm)

■ Cautions

Degree of Protection

Do not use the Switch underwater.

The switch was tested and found to satisfy the conditions necessary to meet the following standards. However, the test only checks for water intrusion after immersion for a specified time period, not for switching and operation underwater.

The switch is tested and conforms to JIS C0920 (Degrees of protection provided by enclosures of electrical apparatus) and IEC60529 (Degrees of protection provided by enclosures).

Note: The object to be tested is submerged at a depth of 1 meter for 30 minutes, then checked for water intrusion.

Protection Against Chemicals

Prevent the switch from coming into contact with oil and chemicals. Otherwise, damage to or deterioration of the switch materials may occur.

All sales are subject to Omron Electronic Components LLC standard terms and conditions of sale, which can be found at http://www.components.omron.com/components/web/webfiles.nsf/sales_terms.html

ALL DIMENSIONS SHOWN ARE IN MILLIMETERS.

To convert millimeters into inches, multiply by 0.03937. To convert grams into ounces, multiply by 0.03527.

OMRON[®]
**OMRON ELECTRONIC
COMPONENTS LLC**
847-882-2288

OMRON ON-LINE

Global - <http://www.omron.com>

USA - <http://www.components.omron.com>

Cat. No. C095-E-05

09/14 (11/10)

Specifications subject to change without notice

Printed in USA