


USBR-B-S-F-O-TH



USB-B-S-S-B-SM



USB-B, USBR-B SERIES

STANDARD & RUGGED USB 2.0

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?USB-B or www.samtec.com?USBR-B

Insulator Material:

High Temperature

Thermoplastic

Contact Material:

Phosphor Bronze

Plating:

Gold on Contacts, Nickel on Shell, Tin on Tails

Operating Temp Range:

-50 °C to +85 °C

Voltage Rating:

30 VAC

Cycles:

1500 (maximum number of cycles tested)

Packaging:

Packaged and shipped in Bulk Packaging Trays; Trays suitable for automation are available upon request.

RoHS Compliant:

Yes

Lead-Free Solderable:

USB-SM=Yes

USB-TH= Yes

(Wave Solder only)

USBR=Yes (Wave Solder only)

TID Number:

USB-B-S-X-X-TH (61001155)

RUGGEDIZED
BY SAMTEC

- High retention option

Minimum 15N withdrawal force

Increased retention option

Through-hole option

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



FILE NO. E111594

(USB only)

FILE NO. E225096

(USBR only)

TYPE

B

S

PLATING

COLOR

TERMINATION

OTHER OPTION

USB

= Standard Connector

USBR

= Increased Retention Connector (Complies with Class 1, DIV II minimum withdrawal requirement of 15N)

-F

= Gold Flash on Mating Area, Tin on Tails

-S

= 30 μ" (0.76 μm) Gold on Mating Area, Tin on Tails

-B

= Black (USB only)

-W

= White (USB only)

-O

= Orange (USBR only)

-TH

= Through-hole

-SM




= Surface Mount (USB only)

-VT




= Vertical Top Entry

-TR

= Tape and Reel Packaging (-SM only)



MATING / UNMATING FORCE (100 CYCLES)		
SERIES	MATING	UNMATING
USB	5.3 (23.59 N)	6.1 (27.15 N)
USBR	11.8 (52.51 N)	11.5 (51.18 N)



Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

All parts within this catalog are built to Samtec's specifications.

Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.