


### Applications

- High frequency DC-DC converters

| $V_{DSS}$ | $R_{DS(on)}$ max | $I_D$ |
|-----------|------------------|-------|
| 150V      | 95m $\Omega$     | 24A   |

### Benefits

- Low Gate-to-Drain Charge to Reduce Switching Losses
- Fully Characterized Capacitance Including Effective  $C_{OSS}$  to Simplify Design, (See App. Note AN1001)
- Fully Characterized Avalanche Voltage and Current



### Absolute Maximum Ratings

|                                   | Parameter                                | Max.         | Units               |
|-----------------------------------|------------------------------------------|--------------|---------------------|
| $I_D$ @ $T_C = 25^\circ\text{C}$  | Continuous Drain Current, $V_{GS}$ @ 10V | 24           | A                   |
| $I_D$ @ $T_C = 100^\circ\text{C}$ | Continuous Drain Current, $V_{GS}$ @ 10V | 17           |                     |
| $I_{DM}$                          | Pulsed Drain Current ①                   | 96           |                     |
| $P_D$ @ $T_C = 25^\circ\text{C}$  | Power Dissipation                        | 140          | W                   |
|                                   | Linear Derating Factor                   | 0.92         | W/ $^\circ\text{C}$ |
| $V_{GS}$                          | Gate-to-Source Voltage                   | $\pm 30$     | V                   |
| $dv/dt$                           | Peak Diode Recovery $dv/dt$ ③            | 4.9          | V/ns                |
| $T_J$                             | Operating Junction and                   | -55 to + 175 | $^\circ\text{C}$    |
| $T_{STG}$                         | Storage Temperature Range                |              |                     |
|                                   | Soldering Temperature, for 10 seconds    |              |                     |

### Thermal Resistance

|                 | Parameter                        | Typ. | Max. | Units                     |
|-----------------|----------------------------------|------|------|---------------------------|
| $R_{\theta JC}$ | Junction-to-Case                 | —    | 1.1  | $^\circ\text{C}/\text{W}$ |
| $R_{\theta JA}$ | Junction-to-Ambient (PCB mount)* | —    | 50   |                           |
| $R_{\theta JA}$ | Junction-to-Ambient              | —    | 110  |                           |

Notes ① through ⑤ are on page 10

www.irf.com

# IRFR24N15D/IRFU24N15D

International  
**IR** Rectifier

## Static @ $T_J = 25^\circ\text{C}$ (unless otherwise specified)

|                                 | Parameter                            | Min. | Typ. | Max. | Units               | Conditions                                            |
|---------------------------------|--------------------------------------|------|------|------|---------------------|-------------------------------------------------------|
| $V_{(BR)DSS}$                   | Drain-to-Source Breakdown Voltage    | 150  | —    | —    | V                   | $V_{GS} = 0V, I_D = 250\mu A$                         |
| $\Delta V_{(BR)DSS}/\Delta T_J$ | Breakdown Voltage Temp. Coefficient  | —    | 0.18 | —    | V/ $^\circ\text{C}$ | Reference to $25^\circ\text{C}$ , $I_D = 1mA$ ⑥       |
| $R_{DS(on)}$                    | Static Drain-to-Source On-Resistance | —    | 82   | 95   | m $\Omega$          | $V_{GS} = 10V, I_D = 14A$ ④                           |
| $V_{GS(th)}$                    | Gate Threshold Voltage               | 3.0  | —    | 5.0  | V                   | $V_{DS} = V_{GS}, I_D = 250\mu A$                     |
| $I_{DSS}$                       | Drain-to-Source Leakage Current      | —    | —    | 25   | $\mu A$             | $V_{DS} = 150V, V_{GS} = 0V$                          |
|                                 |                                      | —    | —    | 250  |                     | $V_{DS} = 120V, V_{GS} = 0V, T_J = 150^\circ\text{C}$ |
| $I_{GSS}$                       | Gate-to-Source Forward Leakage       | —    | —    | 100  | nA                  | $V_{GS} = 30V$                                        |
|                                 | Gate-to-Source Reverse Leakage       | —    | —    | -100 |                     | $V_{GS} = -30V$                                       |


## Dynamic @ $T_J = 25^\circ\text{C}$ (unless otherwise specified)


|                        | Parameter                       | Min. | Typ. | Max. | Units | Conditions                                            |
|------------------------|---------------------------------|------|------|------|-------|-------------------------------------------------------|
| $g_{fs}$               | Forward Transconductance        | 8.2  | —    | —    | S     | $V_{DS} = 25V, I_D = 14A$                             |
| $Q_g$                  | Total Gate Charge               | —    | 30   | 45   | nC    | $I_D = 14A$                                           |
| $Q_{gs}$               | Gate-to-Source Charge           | —    | 7.4  | 11   |       | $V_{DS} = 120V$                                       |
| $Q_{gd}$               | Gate-to-Drain ("Miller") Charge | —    | 17   | 26   |       | $V_{GS} = 10V, \text{ ④}$                             |
| $t_{d(on)}$            | Turn-On Delay Time              | —    | 11   | —    | ns    | $V_{DD} = 75V$                                        |
| $t_r$                  | Rise Time                       | —    | 53   | —    |       | $I_D = 14A$                                           |
| $t_{d(off)}$           | Turn-Off Delay Time             | —    | 19   | —    |       | $R_G = 6.8\Omega$                                     |
| $t_f$                  | Fall Time                       | —    | 15   | —    |       | $V_{GS} = 10V, \text{ ④}$                             |
| $C_{iss}$              | Input Capacitance               | —    | 890  | —    | pF    | $V_{GS} = 0V$                                         |
| $C_{oss}$              | Output Capacitance              | —    | 220  | —    |       | $V_{DS} = 25V$                                        |
| $C_{rss}$              | Reverse Transfer Capacitance    | —    | 46   | —    |       | $f = 1.0MHz$                                          |
| $C_{oss}$              | Output Capacitance              | —    | 1460 | —    |       | $V_{GS} = 0V, V_{DS} = 1.0V, f = 1.0MHz$              |
| $C_{oss}$              | Output Capacitance              | —    | 95   | —    |       | $V_{GS} = 0V, V_{DS} = 120V, f = 1.0MHz$              |
| $C_{oss \text{ eff.}}$ | Effective Output Capacitance    | —    | 200  | —    |       | $V_{GS} = 0V, V_{DS} = 0V \text{ to } 120V \text{ ⑤}$ |

## Avalanche Characteristics


|          | Parameter                      | Typ. | Max. | Units |
|----------|--------------------------------|------|------|-------|
| $E_{AS}$ | Single Pulse Avalanche Energy② | —    | 170  | mJ    |
| $I_{AR}$ | Avalanche Current①             | —    | 14   | A     |
| $E_{AR}$ | Repetitive Avalanche Energy①   | —    | 14   | mJ    |

## Diode Characteristics


|          | Parameter                              | Min.                                                                        | Typ. | Max. | Units | Conditions                                                                                                                                           |
|----------|----------------------------------------|-----------------------------------------------------------------------------|------|------|-------|------------------------------------------------------------------------------------------------------------------------------------------------------|
| $I_S$    | Continuous Source Current (Body Diode) | —                                                                           | —    | 24   | A     | MOSFET symbol showing the integral reverse p-n junction diode.  |
| $I_{SM}$ | Pulsed Source Current (Body Diode) ①   | —                                                                           | —    | 96   |       |                                                                                                                                                      |
| $V_{SD}$ | Diode Forward Voltage                  | —                                                                           | —    | 1.5  | V     | $T_J = 25^\circ\text{C}, I_S = 14A, V_{GS} = 0V, \text{ ④}$                                                                                          |
| $t_{rr}$ | Reverse Recovery Time                  | —                                                                           | 110  | —    | ns    | $T_J = 25^\circ\text{C}, I_F = 14A$                                                                                                                  |
| $Q_{rr}$ | Reverse Recovery Charge                | —                                                                           | 450  | —    | nC    | $di/dt = 100A/\mu s, \text{ ④}$                                                                                                                      |
| $t_{on}$ | Forward Turn-On Time                   | Intrinsic turn-on time is negligible (turn-on is dominated by $L_S + L_D$ ) |      |      |       |                                                                                                                                                      |




**Fig 1.** Typical Output Characteristics



**Fig 2.** Typical Output Characteristics







**Fig 3.** Typical Transfer Characteristics




**Fig 4.** Normalized On-Resistance Vs. Temperature


# IRFR24N15D/IRFU24N15D

International  
**IR** Rectifier







**Fig 9.** Maximum Drain Current Vs. Case Temperature



**Fig 10a.** Switching Time Test Circuit




**Fig 10b.** Switching Time Waveforms




**Fig 11.** Maximum Effective Transient Thermal Impedance, Junction-to-Case

# IRFR24N15D/IRFU24N15D


International  
**IR** Rectifier




**Fig 12a.** Unclamped Inductive Test Circuit




**Fig 12b.** Unclamped Inductive Waveforms



**Fig 12c.** Maximum Avalanche Energy Vs. Drain Current





**Fig 13a.** Basic Gate Charge Waveform



**Fig 13b.** Gate Charge Test Circuit

## Peak Diode Recovery dv/dt Test Circuit



\*  $V_{GS} = 5V$  for Logic Level Devices


**Fig 14.** For N-Channel HEXFET® Power MOSFETs

# IRFR24N15D/IRFU24N15D

International  
**IR** Rectifier


## D-Pak (TO-252AA) Package Outline

Dimensions are shown in millimeters (inches)



## D-Pak (TO-252AA) Part Marking Information


EXAMPLE: THIS IS AN IRFR120  
WITH ASSEMBLY  
LOT CODE 1234  
ASSEMBLED ON WW 16, 1999  
IN THE ASSEMBLY LINE "A"






## I-Pak (TO-251AA) Package Outline

Dimensions are shown in millimeters (inches)



## I-Pak (TO-251AA) Part Marking Information

EXAMPLE: THIS IS AN IRFR120  
WITH ASSEMBLY  
LOT CODE 5678  
ASSEMBLED ON WW 19, 1999  
IN THE ASSEMBLY LINE "A"




# IRFR24N15D/IRFU24N15D

International  
**IR** Rectifier


## D-Pak (TO-252AA) Tape & Reel Information

Dimensions are shown in millimeters (inches)



### NOTES :

1. CONTROLLING DIMENSION : MILLIMETER.
2. ALL DIMENSIONS ARE SHOWN IN MILLIMETERS ( INCHES ).
3. OUTLINE CONFORMS TO EIA-481 & EIA-541.



### NOTES :

1. OUTLINE CONFORMS TO EIA-481.

### Notes:

- ① Repetitive rating; pulse width limited by max. junction temperature.
  - ② Starting  $T_J = 25^\circ\text{C}$ ,  $L = 1.7\text{mH}$   
 $R_G = 25\Omega$ ,  $I_{AS} = 14\text{A}$ .
  - ③  $I_{SD} \leq 14\text{A}$ ,  $di/dt \leq 380\text{A}/\mu\text{s}$ ,  $V_{DD} \leq V_{(BR)DSS}$ ,  
 $T_J \leq 175^\circ\text{C}$ .
  - ④ Pulse width  $\leq 300\mu\text{s}$ ; duty cycle  $\leq 2\%$ .
  - ⑤  $C_{OSS}$  eff. is a fixed capacitance that gives the same charging time as  $C_{OSS}$  while  $V_{DS}$  is rising from 0 to 80%  $V_{DSS}$ .
- \* When mounted on 1" square PCB (FR-4 or G-10 Material).  
For recommended footprint and soldering techniques refer to application note #AN-994.

Data and specifications subject to change without notice.  
This product has been designed and qualified for the Automotive [Q101] market.  
Qualification Standards can be found on IR's Web site.

International  
**IR** Rectifier

**IR WORLD HEADQUARTERS:** 233 Kansas St., El Segundo, California 90245, USA Tel: (310) 252-7105  
TAC Fax: (310) 252-7903

Visit us at [www.irf.com](http://www.irf.com) for sales contact information.03/02

[www.irf.com](http://www.irf.com)

Note: For the most current drawings please refer to the IR website at:  
<http://www.irf.com/package/>