


OA938 Series



AC Fan - 115V, 230V, Dual Voltage
92 x 38mm(3.62" x 1.5")



Frame	Diecast Aluminum	<u>Operating Temperature</u> Ball Bearing -20C ~ +80C Sleeve Bearing -10C ~ +50C
Impeller	PBT, UL94V-O plastic	
Connection	2x Lead Wires 22 AWG or terminals	
Motor	Shaded pole, impedance protected	<u>Life Expectancy</u> Ball Bearing 60,000 hours (L10 at 40C) Sleeve Bearing 30,000 hours (L10 at 40C)
Bearing System	Dual ball or Sleeve	
Insulation Resistance	>100M ohm between lead-wire and frame (500VDC)	<u>Dual Voltage</u> Connection via 4x leads. Fans can be configured for 115V or 230V operation.
Dielectric Strength	1 min at 1500 VAC, 50/60Hz	

Airflow (CFM)	Static Pressure (inches H2O) at 3100 RPM	Static Pressure (inches H2O) at 2400 RPM	Static Pressure (inches H2O) at 1800 RPM
0	0.22	0.17	0.09
10	0.18	0.12	0.06
20	0.14	0.09	0.03
30	0.12	0.05	0.00
40	0.06	0.00	-
50	0.00	-	-

Model Number	Speed (RPM)	Airflow (CFM)	Noise (dB)	Volts AC	Voltage Range	Watts	Max. Static Pressure ("H2O)
OA938AP-11-1*	3100	50	32	115	80~130	9	.22
OA938AP-11-2*	2400	39	23	115	80~130	5	.17
OA938AP-11-3*	1800	26	19	115	80~130	3	.10
OA938AP-22-1*	3100	50	32	230	160~260	9	.22
OA938AP-22-2*	2400	39	23	230	160~260	5	.17
OA938AP-22-3*	1800	26	19	230	160~260	3	.10
OA938AP-11/22-1W**	3100	50	32	115/230	80~260	9	.22
OA938AP-11/22-2W**	2400	39	23	115/230	80~260	5	.17
OA938AP-11/22-3W**	1800	26	19	115/230	80~260	3	.10

* Indicate "TB" (Terminal Ball Bearing), "WB" (12" Wire Leads, Ball Bearing), "TS" (Terminal, Sleeve Bearing), "WS" (12" Wire Leads, Sleeve Bearing)
** Indicate "B" (Ball Bearing) or "S" (Sleeve Bearing)