




CLAMPING SCREW

0.5

INTERLOCKING FEATURE

12.5

WIRE ENTRY

2.5 REF

1.00±0.01 TYP

5.00±0.05 TYP

5.0

RECOMMENDED PC BOARD LAYOUT

5.0

1.4^{+0.1}₋₀

Ø 0.1

15.0

35°

0.80±0.05 TYP

6.25 TYP

3.80±0.30 TYP

120.0

24

2-796689-4

115.0

23

2-796689-3

110.0

22

2-796689-2

105.0

21

2-796689-1

100.0

20

2-796689-0

95.0

19

1-796689-9

90.0

18

1-796689-8

85.0

17

1-796689-7

80.0

16

1-796689-6

75.0

15

1-796689-5

70.0

14

1-796689-4

65.0

13

1-796689-3

60.0

12

1-796689-2

55.0

11

1-796689-1

50.0

10

1-796689-0

45.0

9

796689-9

40.0

8

796689-8

35.0

7

796689-7

30.0

6

796689-6

25.0

5

796689-5

20.0

4

796689-4

15.0

3

796689-3

10.0

2

796689-2

L

NO OF POSN

PART NUMBER

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	3
1 PLC	±	3
2 PLC	±	25
3 PLC	±	25
4 PLC	±	25
ANGLES	±	2
FINISH		

MATERIAL

-

DWN

S. WELDON

02SEP2003

CHK

C. RICHARD

02SEP2003

APVD

C. RICHARD

02SEP2003

PRODUCT SPEC

108-20166

APPLICATION SPEC

114-20079

WEIGHT

-

CUSTOMER DRAWING

SCALE 3.1

SHEET 1

OF 1

REV A1

NAME

TERMINAL BLOCK, PCB MOUNT
ANGLED WIRE ENTRY, STACKING
W/INTERLOCK, 5.00mm PITCH

SIZE

A2

CAGE CODE

00779

DRAWING NO

796689

RESTRICTED TO

-