




3M™ TEXTTOOL™ OPEN-TOP SOCKETS FOR QFN APPLICATIONS



NOTES:

1. MATERIALS:

SPRINGS	SS	PLATING : Au
CONTACTS	Be Cu	COLOR : BLACK
IC GUIDES	PES	COLOR : BLACK
PRESSURE PAD	PES	COLOR : BLACK
COVER	PPS or equiv.	COLOR : BLACK
BASE	PES	COLOR : BLACK



2. SEE THE REGULATORY INFORMATION APPENDIX (RIA) IN THE "RoHS COMPLIANCE" SECTION WWW.3MCONNECTOR.COM FOR COMPLIANCE INFORMATION (RIA E1 & C1 APPLY).


3. FOR PRODUCT SPECIFICATIONS AND WARRANTY INFORMATION SEE:

WWW.3MCONNECTOR.COM PN 248-5205-01

DESIGN REFERENCE		NEXT ASSEMBLY		A 37213 INITIAL RELEASE		ARM	
DISTRIBUTION CODES		SCALE 5/1		TOLERANCES EXCEPT AS NOTED		3M 3M Center St. Paul, MN 55144	
DIVISION		DIVISION CODE		INCHES .0 ± .1 .00 ± .02 .000 ± .005 .0000 ± .0002		MILLIMETERS 0 ± .0 .00 ± .000 ± .0000	
THIRD ANGLE PROJECTION		INTERPRET PER ASME Y14.5 - 1994		MAX SURFACE ROUGHNESS 125 ✓		CAGE NUMBER C	
ALL SURFACES		MARKED ONLY		ANGLES ± 1°		TITLE QFN TEST SOCKET, 0.5mm 48 pos, EVEN ROW, 7x7 PKG WITH TP	
REV ECO		ISSUE DATE AND DESCRIPTION		DRFT		CHKD	
DATE		MFG		DATE		DATE	
CHKD		DATE		APPVL		DATE	
CAGE NUMBER		SIZE		DRAWING NO. 78-5100-2473-6		REV. A	
MODEL		TEXTTOOL - QFN		DET. LISTS		SHT 1 OF 2	

3M™ TEXTTOOL™ OPEN-TOP SOCKETS FOR QFN APPLICATIONS



DESIGN REFERENCE				NEXT ASSEMBLY				REV	ECO	ISSUE DATE AND DESCRIPTION				DRFT	CHKD
DISTRIBUTION CODES								DRFT		DATE		MFG		DATE	
								CHKD		DATE		APPVL		DATE	
DIVISION				DIVISION CODE				3M 3M Center St. Paul, MN 55144 © 3M COPYRIGHT 2012 This document is the copyrighted property of the 3M Company and may not be reproduced without 3M written permission or used for other than 3M authorized purposes.							
DO NOT SCALE DRAWING		SCALE 5 1		TOLERANCES EXCEPT AS NOTED											
				INCHES				TITLE QFN TEST SOCKET, 0.5mm 48 pos, EVEN ROW, 7x7 PKG WITH TP							
				.0 ± .1 .00 ± .02 .000 ± .005 .0000 ± .0002											
THIRD ANGLE PROJECTION				MILLIMETERS				CAGE NUMBER 78-5100-2473-6							
INTERPRET PER ASME Y14.5 - 1994				0 ± .1 .0 ± .005 .00 ± .0002											
MAX SURFACE ROUGHNESS 125 ✓ ☒ MARKED ONLY								CAGE NUMBER C		DRAWING NO.		REV.			
				ANGLES ± 1°				MODEL TEXTTOOL - QFN		DET. LISTS ☐ YES ☒ NO		SHT 2 OF 2			