




FIGURE A




FIGURE B




FIGURE D

44.93 [1.769]	- N/A	35.10 [1.382]	1.73 [.068]	55.88 [2.200]	53.6 [2.11]	36.19 [1.425]	47.62 [1.875]	140.5 [5.53]	A	35mm	1000 MCM	1-193673-9	3
44.93 [1.769]	- N/A	35.10 [1.382]	1.73 [.068]	55.88 [2.200]	45 [1.77]	30.43 [1.198]	47.62 [1.875]	129.5 [5.10]	A	35mm	700 MCM	1-193673-8	3
40.36 [1.589]	- N/A	30.12 [1.186]	1.73 [.068]	55.88 [2.200]	53.6 [2.11]	36.19 [1.425]	42.80 [1.685]	139.4 [5.49]	B	30mm	1000 MCM	1-193673-7	3
40.36 [1.589]	- N/A	30.12 [1.186]	1.73 [.068]	55.88 [2.200]	45 [1.77]	30.43 [1.198]	42.80 [1.685]	127.2 [5.01]	A	30mm	700 MCM	1-193673-6	3
37.29 [1.468]	- N/A	25.09 [.988]	1.73 [.068]	55.88 [2.200]	50.8 [2.00]	34.98 [1.377]	40.66 [1.601]	135.4 [5.33]	B	25mm	900 MCM	1-193673-5	3
37.29 [1.468]	- N/A	25.09 [.988]	1.73 [.068]	55.88 [2.200]	41.7 [1.64]	27.94 [1.100]	40.66 [1.601]	123.4 [4.86]	A	25mm	600 MCM	1-193673-4	3
25.35 [.998]	- N/A	20.09 [.791]	1.42 [.056]	35.56 [1.400]	32.5 [1.28]	23.11 [.910]	27.23 [1.072]	89.9 [3.54]	B	20mm	400 MCM	1-193673-3	3
25.35 [.998]	- N/A	20.09 [.791]	1.42 [.056]	35.56 [1.400]	25.9 [1.02]	18.31 [.721]	27.23 [1.072]	80.5 [3.17]	A	20mm	250 MCM	1-193673-2	
22.40 [.882]	- N/A	16.10 [.634]	1.17 [.046]	33.02 [1.300]	28.4 [1.12]	20.04 [.789]	23.57 [.928]	80 [3.15]	B	16mm	300 MCM	1-193673-1	3
22.40 [.882]	- N/A	16.10 [.634]	1.17 [.046]	33.02 [1.300]	24.1 [.95]	16.94 [.677]	23.57 [.928]	73.9 [2.91]	A	16mm	4/0	1-193673-0	3
18.62 [.733]	- N/A	12.09 [.476]	1.17 [.046]	30.48 [1.200]	24.1 [.95]	17.22 [.678]	20.19 [.795]	70.1 [2.76]	B	12mm	4/0	1-193673-9	3
18.62 [.733]	- N/A	12.09 [.476]	1.17 [.046]	30.48 [1.200]	19.6 [.77]	13.74 [.541]	20.19 [.795]	63.7 [2.51]	A	12mm	2/0	193673-8	
SEE SHEET 2										8mm	1/0	193673-7	
- N/A	13.51 [.532]	8.10 [.319]	- N/A	5.2 [.21]	14.2 [.56]	9.91 [.390]	14.45 [.569]	57.4 [2.26]	D	8mm	2	193673-6	
- N/A	9.45 [.372]	6.04 [.238]	- N/A	5.2 [.21]	11.4 [.45]	7.36 [.290]	10.41 [.410]	37.6 [1.48]	D	6mm	4	193673-5	
- N/A	9.45 [.372]	6.04 [.238]	- N/A	5.2 [.21]	9.4 [.37]	5.97 [.235]	10.41 [.410]	36.1 [1.42]	D	6mm	6	193673-4	
- N/A	6.65 [.262]	4.09 [.161]	- N/A	6.2 [.25]	9.1 [.36]	4.60 [.181]	7.62 [.300]	33.3 [1.31]	D	4mm	8	193673-3	
- N/A	6.65 [.262]	4.09 [.161]	- N/A	6.2 [.25]	9.1 [.36]	3.68 [.145]	7.62 [.300]	33.3 [1.31]	D	4mm	10	193673-2	
- N/A	4.75 [.187]	2.23 [.088]	- N/A	5.2 [.21]	9.1 [.36]	2.54 [.105]	5.89 [.232]	28.7 [1.13]	D	2mm	12/14	193673-1	
ØS	ØR	ØN	M	K	F	ØC	ØB	A	FIGURE	MATING Ø PIN	WIRE AWG	PART NUMBER	

- 3 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
2. ALL DIMENSIONS ARE REFERENCE ONLY.
- 1 GROOVE PROVIDED FOR USE WITH COMMERCIALY AVAILABLE RETAINING RINGS, i.e. MS-16624 TYPE.

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
J.TURNER
09-10-93

CHK
A.L.G.
09-10-93

APVD
S.R.S.
09-10-93

DIMENSIONS:
MM[INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± -
1 PLC ± -
2 PLC ± 0.40[.015]
3 PLC ± 0.25[.010]
4 PLC ± ± -
ANGLES ± ± -

MATERIAL
BODY: COPPER ALLOY
RETENTION SPRING:
STAINLESS STEEL
CONTACT BAND: BeCu

FINISH
BODY AND BAND:
SILVER OVER NICKEL
SPRING: NONE

WEIGHT
-

TE Connectivity

NAME
SOCKET ASSY, 2-35mm, CRIMP

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-193673

RESTRICTED TO
-

CUSTOMER DRAWING


SCALE
NTS

SHEET
1 OF 2

REV
D2

1471-9 (3/11)

LOC	DIST	REVISIONS			
CH	11	P	LTR	DESCRIPTION	DATE
		-	-	SEE SHEET 1	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	17/OCT/97	TE Connectivity	
		CHK	-		
DIMENSIONS:		APVD	-	NAME	
mm[in]		PRODUCT SPEC	-		
	0 PLC	± -	APPLICATION SPEC	SIZE	
	1 PLC	± -			
	2 PLC	± -			
	3 PLC	± -			
MATERIAL		WEIGHT	-	CAGE CODE	
		FINISH	-	DRAWING NO	
		CUSTOMER DRAWING		RESTRICTED TO	
				SCALE	
				SHEET	
				REV	