

COM Express® Basic Module

Performance

conga-B945

Featuring the Intel® Core™2 Duo Processors up to 2.16 GHz


Provides up to 4 GByte Dual Channel DRAM

ACPI Battery Support,
Flat Panel detection ...



Formfactor	COM Express™ Basic, (95 x 125 mm), Type II Connector Layout
CPU	Intel® Core™ 2 Duo T7400, 2.16 GHz, (4M cache, 667 MHz FSB, 65nm), Socket mPGA479M Intel® Core™ 2 Duo L7400 LV, 1.5 GHz, (4M cache, 667 MHz FSB, 65nm) Intel® Core™ 2 Duo U7500 ULV, 1.06 GHz, (2M cache, 533 MHz FSB, 65nm) Intel® Core™ Duo L2400 LV, 1.66 GHz, (2M cache, 667 MHz FSB, 65nm) Intel® Celeron® M440, 1.86 GHz, (1M cache, 533 MHz FSB, 65nm), Socket mPGA479M Intel® Celeron® M423 ULV, 1.06 GHz, (1M cache, 533 MHz FSB, 65nm)
DRAM	2 Sockets, SO-DIMM DDR2 667/PC5300 up to 4 GByte physical memory
Chipset	Graphics & Memory Controller Hub: Intel® 945GME I/O Controller Hub: Intel® 82801GDM (ICH7M-DH)
Ethernet	Gigabit Ethernet, Realtek RTL8111
I/O Interfaces	5x PCI Express™ Lanes, PCI Express Graphic (PEG x16), 2x Serial ATA* (AHCI) supporting RAID 0 and RAID 1, 1x EIDE (UDMA-66/100), 2x Express Card* (uses 2x USB & 2x PCI Express), 8x USB 2.0 (EHCI), PCI Bus 33 MHz Rev. 2.3, LPC Bus, i°C (Fast Mode, 400 kHz, Multi Master)
Sound	AC'97 Rev.2.2 Compatible, Digital High Definition Audio Interface with support for multiple audio codecs
Graphics	Enhanced 256 Bit 3D Video Controller, Intel® Graphics Media Accelerator 950, up to 10.6 GB/sec memory bandwidth, 256-bit graphics core, max. 224 MByte 64 Bit Video RAM (DVMT 3.0), Dynamic Display Modes for flat-panel, wide-screen and Digital TV support, Two independent pipelines for full dual view support
Motion Video Support	High Definition Hardware Motion Compensation to support high definition hi-bitrate MPEG2 media playback, Up and Down Scaling of Video Content, High Definition Content Decode, HDTV (1080i/p) Support
Flat panel Interface	Dual 112 MHz LVDS Transmitter, Supports all 1x18, 2x18, 1x24, 2x24 Bit, VESA- and openLDI-Mappings, Resolutions 640x480 up to 1920x1200, Automatic Panel Detection via EPI, (Embedded Panel Interface, based on VESA EDID™ 1.3)
CRT Interface	400 MHz RAMDAC, Resolutions up to 2048x1536 @ 75 Hz, including 1920x1080 @ >85 Hz (HDTV)
AUX Output	2x SDVO (shared with PEG x16 pins)
TV Out	Onboard TV encoder, supports HDTV (420p, 720p and 1080i), supports component and s-video
congatec Board Controller	Multi Stage Watchdog, Non-volatile User Data Storage, Manufacturing and Board information, Board Statistics, BIOS Setup Data Backup, i°C (Fast Mode, 400 kHz, Multi Master), Power Loss Control
Embedded BIOS Features	OEM Logo, OEM CMOS Defaults, LCD Control, (Auto Detection, Backlight Control), Flash Update, Based on AMIBIOS®
Security	The conga-B945 can be optionally equipped with a discrete "Trusted Platform Module" (TPM). It is capable of calculating efficient hash and RSA algorithms with key lengths up to 2,048 bits and includes a real random number generator. Security sensitive applications such as gaming and e commerce will benefit also with improved authentication, integrity and confidence levels.
Power Management	ACPI 2.0 with Battery support
Operating Systems	Microsoft® Windows 7, Microsoft® Windows XP, Microsoft® Windows® embedded Standard, Microsoft® Windows CE 6.0, Microsoft® Windows Embedded Compact 7, Linux
Power Consumption	Typ. application: 10.5 W @ 12V, (1.66 GHz Core Duo), see manual for full details, CMOS Battery Backup
Temperature	Operating: 0 .. +60°C Storage: -20 .. +80°C
Humidity	Operating: 10 - 90% r. H. non cond. Storage: 5 - 95% r. H. non cond.
Size	95 x 125 mm² (3.74" x 4.92")

Block Diagram conga-B945



Engineering Tools / Accessories for COM Express®

065749	conga-CEVAL
047854	conga-Cdebug
064714	conga-CKIT
011115	conga-LDVI/EPI
500014	conga-HDMI/Display Port adapter
058500	Single DVI-D ADD2 Card
013226	Dual DVI-D ADD2 Card
047250	conga-FPA2
400007	COM-Express-carrierboard-Socket-5
400004	COM-Express-carrierboard-Socket-8

Order Information conga-B945

Article	PN	Description
conga-B945/423	041480	Intel 945GME and Intel® Celeron® M 423 processor 1.06 GHz, 1MB L2 cache and 533MHz FSB
conga-B945/U7500	047894	Intel 945GME chipset and Intel Core2Duo U7500 processor with 1.06GHz, 2MB L2 cache and 533MHz FSB.
conga-B945/L2400	098642	Intel 945GME chipset and Intel CoreDuo L2400 processor with 1.66GHz, 2 MB L2 cache and 667MHz FSB
conga-B945/L7400	013124	Intel 945GME chipset and Intel Core2Duo L7400 processor with 1.5GHz, 2MB L2 cache and 667MHz FSB
conga-B945-socket/440	033884	Intel 945GME and Intel® Celeron® M 440 Processor 1.86 GHz, 1 MB L2 cache and 533MHz FSB
conga-B945-socket/T7400	083447	Intel 945GME and Intel Core2Duo T7400 Processor 2.16 GHz, 4 MB L2 cache and 533MHz FSB.
conga-B945/HSP-B	024175	Heatspreader, Standoff with 2.7mm bore hole
conga-B945/HSP-T	058741	Heatspreader, Standoff with M2.5mm thread
conga-B945/CSA-B	054123	Standard active cooling solution, surface black with 10mm fins, integrated 12V fan 5500rpm, cable length 200mm, w/3 pin, 2.54 pitch connector, bore hole standoffs
conga-B945/CSA-T	069877	Standard active cooling solution, surface black with 10mm fins, integrated 12V fan 5500rpm, cable length 200mm, w/3 pin, 2.54 pitch connector, thread standoffs
conga-B945/CSP-B	087415	Standard passive cooling solution, surface black with 10mm fins, bore hole standoffs
conga-B945/CSP-T	068741	Standard passive cooling solution, surface black with 10mm fins, thread standoffs
conga-B945-socket/HSP-B	042758	Heatspreader, Standoff with 2.7mm bore hole
conga-B945-socket/HSP-T	085744	Heatspreader, Standoff with M2.5mm thread
conga-B945-socket/CSA-B	022417	Standard active cooling solution, surface black with 10mm fins, integrated 12V fan 5500rpm, cable length 200mm, w/3 pin, 2.54 pitch connector, bore hole standoffs
conga-B945-socket/CSA-T	085147	Standard active cooling solution, surface black with 10mm fins, integrated 12V fan 5500rpm, cable length 200mm, w/3 pin, 2.54 pitch connector, thread standoffs
conga-B945-socket/CSP-B	048731	Standard passive cooling solution, surface black with 10mm fins, bore hole standoffs
conga-B945-socket/CSP-T	025879	Standard passive cooling solution, surface black with 10mm fins, thread standoffs
DDR2-SODIMM-667 (0512MB)	057841	512 MByte DDR2 SODIMM memory module
DDR2-SODIMM-667 (1024MB)	087412	1 GByte DDR2 SODIMM memory module
DDR2-SODIMM-667 (2048MB)	068712	2 GByte DDR2 SODIMM memory module

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[congatec:](#)

[conga-BA945/HSP-B](#) [conga-BA945/HSP-T](#) [conga-B945-socket/CSA-B](#) [conga-B945-socket/HSP-T](#) [conga-B945-socket/CSA-T](#) [conga-B945-socket/CSP-B](#) [conga-B945-socket/HSP-B](#) [conga-B945/HSP-B](#) [400004](#) [400007](#)