



V23100V4024A 1 Product Details

[Share](#) | [Print](#) | [Email](#)


V23100V4024A 1

TE Internal Number: 1-1393763-5

Active

Communications/Signal PC Board Relays

[Converted to EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- V23100-V4 / Dry Reed relay DIP & SIL Series
- DC Actuating System
- Input Voltage = 24 VDC
- Contact Arrangement = 1 Form A, SPST-NO, 1 N/O
- Contact - Rated Current = .5 A

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [Reed Relay Datasheet](#) (PDF, English)

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Series](#) = V23100-V4 / Dry Reed relay DIP & SIL
- Termination Type = Through Hole

Electrical Characteristics:

- Actuating System = DC
- Input Voltage (VDC) = 24
- Contact - Rated Current (A) = 0.5
- [Coil Resistance \(\$\Omega\$ \)](#) = 2000
- Coil - Rated Power (mW) = 288
- [Insulation - Special Features](#) = None
- Insulation - Initial Dielectric Between Contacts and Coil (V rms) = 1500

Body Features:

- Polarized = No

Contact Features:

- Mounting Options = PC Board
- Enclosure Type = Ultrasonic Cleanable
- Contact Base Material = Rhodium
- Approx. Dimensions (L x W x H) (mm [in]) = 19.30 x 7.50 x 5.70 [.760 x .295 x .224]
- Option = With Electrostatic Shield
- DIP Package Style = Flat
- Contact Configuration = Bifurcated
- Pin Configuration = DIP

Configuration Features:

- [Contact Arrangement](#) = 1 Form A, SPST-NO, 1 N/O
- [Coil - Magnetic System](#) = Non Polarized, Monostable
- Coil Suppression Diode = Without

Industry Standards:

- Approved Standards = cUL
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Converted to comply with RoHS directive

Other:

- Brand = Axicom

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

[▶](#)

