

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

G

86

E2

REVISED PER ECO-11-004820

11MAR11

RK

HMR

AMP WIRE RANGE

16-14 AWG STRANDED

FILE

E66717

LR7189

Certified

16-14 AWG STRANDED

16-14 AWG STRANDED

1

AMP

16-14

.375 REF

.881 MAX

3

.016±.001

.22 REF

1

MARKED AMP 16-14

2

DESIGNED FOR WIRE INSULATION DIA OF .105-.160.

3

MATES WITH .250±.003 BY .032±.001 THK TAB.

4

BODY: BRASS, TIN PLATED SLEEVE: NYLON, BLUE

5

RATED FOR 15 MAX AMPERE

TE CONNECTIVITY
CUSTOMER SERVICE SYSTEM

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWING
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

FOR APPLICATION
TOOLING INFORMATION

TOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE:
105°C [221°F]
-

VOLTAGE RATING:
300V MAX
-

CIRCULAR MIL AREA:
2,050-5,180
STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± .008

4 PLC ± -

ANGLES ± -

FINISH

MATERIAL

- 4

DWN
JR RUTH
CHK
T MICHELUTTI
APVD
T MICHELUTTI
PRODUCT SPEC
-
APPLICATION SPEC
114-13076
WEIGHT
-

07NOV01
07NOV01
07NOV01

TE Connectivity

RECEPTACLE, 250 SERIES, FASTON,
FULLY INSULATED, WIRE: 16-14 AWG

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-696366

RESTRICTED TO
-

CUSTOMER DRAWING

SCALE
1:1

SHEET
1 OF 1

REV
E2

100

LOOSE PIECE

8-696366-1

1000

LOOSE PIECE

696366-1

QTY

PACKAGE TYPE

PART NO.

1470-19

(3/11)