


BD250, BD250A, BD250B, BD250C PNP SILICON POWER TRANSISTORS

Copyright © 1997, Power Innovations Limited, UK

JUNE 1973 - REVISED MARCH 1997

- Designed for Complementary Use with the BD249 Series
- 125 W at 25°C Case Temperature
- 25 A Continuous Collector Current
- 40 A Peak Collector Current
- Customer-Specified Selections Available



Pin 2 is in electrical contact with the mounting base.

MDTRA4

absolute maximum ratings at 25°C case temperature (unless otherwise noted)

| RATING | | SYMBOL | VALUE | UNIT |
|--|--------|---------------------|-------------|------|
| Collector-emitter voltage ($R_{BE} = 100 \Omega$) | BD250 | V_{CER} | -55 | V |
| | BD250A | | -70 | |
| | BD250B | | -90 | |
| | BD250C | | -115 | |
| Collector-emitter voltage ($I_C = -30 \text{ mA}$) | BD250 | V_{CEO} | -45 | V |
| | BD250A | | -60 | |
| | BD250B | | -80 | |
| | BD250C | | -100 | |
| Emitter-base voltage | | V_{EBO} | -5 | V |
| Continuous collector current | | I_C | -25 | A |
| Peak collector current (see Note 1) | | I_{CM} | -40 | A |
| Continuous base current | | I_B | -5 | A |
| Continuous device dissipation at (or below) 25°C case temperature (see Note 2) | | P_{tot} | 125 | W |
| Continuous device dissipation at (or below) 25°C free air temperature (see Note 3) | | P_{tot} | 3 | W |
| Unclamped inductive load energy (see Note 4) | | $\frac{1}{2}LI_C^2$ | 90 | mJ |
| Operating junction temperature range | | T_j | -65 to +150 | °C |
| Storage temperature range | | T_{stg} | -65 to +150 | °C |
| Lead temperature 3.2 mm from case for 10 seconds | | T_L | 250 | °C |

NOTES: 1. This value applies for $t_p \leq 0.3 \text{ ms}$, duty cycle $\leq 10\%$.
 2. Derate linearly to 150°C case temperature at the rate of 1 W/°C.
 3. Derate linearly to 150°C free air temperature at the rate of 24 mW/°C.
 4. This rating is based on the capability of the transistor to operate safely in a circuit of: $L = 20 \text{ mH}$, $I_{B(on)} = -0.4 \text{ A}$, $R_{BE} = 100 \Omega$, $V_{BE(off)} = 0$, $R_S = 0.1 \Omega$, $V_{CC} = -20 \text{ V}$.

PRODUCT INFORMATION

Information is current as of publication date. Products conform to specifications in accordance with the terms of Power Innovations standard warranty. Production processing does not necessarily include testing of all parameters.



BD250, BD250A, BD250B, BD250C

PNP SILICON POWER TRANSISTORS

JUNE 1973 - REVISED MARCH 1997

electrical characteristics at 25°C case temperature

| PARAMETER | TEST CONDITIONS | | | MIN | TYP | MAX | UNIT |
|--|---|--|-------------------------------------|---------------------------|-----|------------------------------|------|
| $V_{(BR)CEO}$ Collector-emitter breakdown voltage | $I_C = -30 \text{ mA}$ (see Note 5) | $I_B = 0$ | BD250 BD250A BD250B BD250C | -45 -60 -80 -100 | | | V |
| I_{CES} Collector-emitter cut-off current | $V_{CE} = -55 \text{ V}$ $V_{CE} = -70 \text{ V}$ $V_{CE} = -90 \text{ V}$ $V_{CE} = -115 \text{ V}$ | $V_{BE} = 0$ $V_{BE} = 0$ $V_{BE} = 0$ $V_{BE} = 0$ | BD250 BD250A BD250B BD250C | | | -0.7 -0.7 -0.7 -0.7 | mA |
| I_{CEO} Collector cut-off current | $V_{CE} = -30 \text{ V}$ $V_{CE} = -60 \text{ V}$ | $I_B = 0$ $I_B = 0$ | BD250/250A BD250B/250C | | | -1 -1 | mA |
| I_{EBO} Emitter cut-off current | $V_{EB} = -5 \text{ V}$ | $I_C = 0$ | | | | -1 | mA |
| h_{FE} Forward current transfer ratio | $V_{CE} = -4 \text{ V}$ $V_{CE} = -4 \text{ V}$ $V_{CE} = -4 \text{ V}$ | $I_C = -1.5 \text{ A}$ $I_C = -15 \text{ A}$ $I_C = -25 \text{ A}$ | (see Notes 5 and 6) | 25 10 5 | | | |
| $V_{CE(sat)}$ Collector-emitter saturation voltage | $I_B = -1.5 \text{ A}$ $I_B = -5 \text{ A}$ | $I_C = -15 \text{ A}$ $I_C = -25 \text{ A}$ | (see Notes 5 and 6) | | | -1.8 -4 | V |
| V_{BE} Base-emitter voltage | $V_{CE} = -4 \text{ V}$ $V_{CE} = -4 \text{ V}$ | $I_C = -15 \text{ A}$ $I_C = -25 \text{ A}$ | (see Notes 5 and 6) | | | -2 -4 | V |
| h_{fe} Small signal forward current transfer ratio | $V_{CE} = -10 \text{ V}$ | $I_C = -1 \text{ A}$ | $f = 1 \text{ kHz}$ | 25 | | | |
| $ h_{fe} $ Small signal forward current transfer ratio | $V_{CE} = -10 \text{ V}$ | $I_C = -1 \text{ A}$ | $f = 1 \text{ MHz}$ | 3 | | | |

NOTES: 5. These parameters must be measured using pulse techniques, $t_p = 300 \mu\text{s}$, duty cycle $\leq 2\%$.

6. These parameters must be measured using voltage-sensing contacts, separate from the current carrying contacts.

thermal characteristics

| PARAMETER | MIN | TYP | MAX | UNIT |
|---|-----|-----|-----|------|
| $R_{\theta JC}$ Junction to case thermal resistance | | | 1 | °C/W |
| $R_{\theta JA}$ Junction to free air thermal resistance | | | 42 | °C/W |

resistive-load-switching characteristics at 25°C case temperature

| PARAMETER | TEST CONDITIONS [†] | | | MIN | TYP | MAX | UNIT |
|-------------------------|------------------------------|------------------------------|--|-----|-----|-----|---------------|
| t_{on} Turn-on time | $I_C = -5 \text{ A}$ | $I_{B(on)} = -0.5 \text{ A}$ | $I_{B(off)} = 0.5 \text{ A}$ | | 0.2 | | μs |
| t_{off} Turn-off time | $V_{BE(off)} = 5 \text{ V}$ | $R_L = 5 \Omega$ | $t_p = 20 \mu\text{s}$, dc $\leq 2\%$ | | 0.4 | | μs |

[†] Voltage and current values shown are nominal; exact values vary slightly with transistor parameters.

PRODUCT INFORMATION

TYPICAL CHARACTERISTICS

**TYPICAL DC CURRENT GAIN
vs
COLLECTOR CURRENT**




Figure 1.

**COLLECTOR-EMITTER SATURATION VOLTAGE
vs
BASE CURRENT**




Figure 2.

**BASE-EMITTER VOLTAGE
vs
COLLECTOR CURRENT**




Figure 3.

BD250, BD250A, BD250B, BD250C
PNP SILICON POWER TRANSISTORS

JUNE 1973 - REVISED MARCH 1997

MAXIMUM SAFE OPERATING REGIONS




Figure 4.

THERMAL INFORMATION




Figure 5.


PRODUCT INFORMATION

MECHANICAL DATA

SOT-93

3-pin plastic flange-mount package

This single-in-line package consists of a circuit mounted on a lead frame and encapsulated within a plastic compound. The compound will withstand soldering temperature with no deformation, and circuit performance characteristics will remain stable when operated in high humidity conditions. Leads require no additional cleaning or processing when used in soldered assembly.



NOTE A: The centre pin is in electrical contact with the mounting tab.

MDXXAW

BD250, BD250A, BD250B, BD250C

PNP SILICON POWER TRANSISTORS

JUNE 1973 - REVISED MARCH 1997

IMPORTANT NOTICE

Power Innovations Limited (PI) reserves the right to make changes to its products or to discontinue any semiconductor product or service without notice, and advises its customers to verify, before placing orders, that the information being relied on is current.

PI warrants performance of its semiconductor products to the specifications applicable at the time of sale in accordance with PI's standard warranty. Testing and other quality control techniques are utilized to the extent PI deems necessary to support this warranty. Specific testing of all parameters of each device is not necessarily performed, except as mandated by government requirements.

PI accepts no liability for applications assistance, customer product design, software performance, or infringement of patents or services described herein. Nor is any license, either express or implied, granted under any patent right, copyright, design right, or other intellectual property right of PI covering or relating to any combination, machine, or process in which such semiconductor products or services might be or are used.

PI SEMICONDUCTOR PRODUCTS ARE NOT DESIGNED, INTENDED, AUTHORIZED, OR WARRANTED TO BE SUITABLE FOR USE IN LIFE-SUPPORT APPLICATIONS, DEVICES OR SYSTEMS.

Copyright © 1997, Power Innovations Limited