

Current refinements (click  to remove)

Search Tips

 Region  USA

 Product Family  Braided Expandable Sleeving – Flame Retardant Polyethylene Terephthalate

 Text Search: 'SE38PFR-TR0'

Your search criteria matched only one product, shown below.



- Provides continuous abrasion resistance for wires cables and tubing
- Lightweight durable protection
- Highly flexible open weave will not trap heat or humidity
- Rated for use up to 257°F (125°C)
- Allows for use with irregular shapes
- Self extinguishing meets UL VW-1
- Stock colors: Black or gray with white tracer or in white with black tracer to identify flame retardant materials.

Part Number:	SE38PFRTR0
RoHS Compliancy Status:	Compliant
Part Description:	Flame Retardant Braided Expandable Sleeving provides continuous abrasion resistance for wires, cables and tubing. The highly flexible open weave will not trap heat or humidity.
Material:	Flame Retardant Polyethylene Terephthalate
Color:	Black
CSA Certified:	Yes
UL Recognized:	E116868
Flammability Rating:	UL224 VW-1
Length Per Reel (ft.):	200
Length Per Reel (m):	61.0
Nominal Diameter Range (In.):	.188 to .625
Nominal Diameter Range (mm 4.7 to 15.9	
Nominal I.D. (In.):	.38
Nominal I.D. (mm):	9.5
Temperature Range:	-94°F to 257°F (-70°C to 125°C)
Min. Order UOM:	RL
Min. Order Qty.:	1
BOM Qty. (# of Pkgs.)	0
Add to My Catalog	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features.