


Inductive Sensors
BES Q08ZC-POC20B-S49G
8 x 8 x 59
normally-closed
Sn=2mm
shielded



PX0676



Common Data

Mounting in steel	shielded
Rated operating distance Sn	2mm
Assured operating distance Sa	0...1.6mm
Repeatability R	<= 5%
Hysteresis	<= 15%
Function indication	yes
Ambient temperature range	-25...+70°C
Pollution Degree	3
IEC-Code	I1C08BP2
Time delay before availability	<= 10ms

Mechanical Data

Measurements BxHxT or DxT	8 x 8 x 59mm
Housing material	Gd Zn Al
Material of sensing face	PA 12
Degree of protection	IP65IP
Connection	Connector S49
Schock: Halbsinus, 30 gn, 11ms	
Vibration: 55 Hz, 1mm Amplitude, 3 x 30 Minutes	

Electrical Data

Current type	DC
Wiring	3-Wire
switching function	normally-closed
Output signal	PNP
Rated operational voltage	24 DCV
Rated operational current	200mA
Supply voltage	10...30 DCV
Ripple	<= 10%
max. switching frequency	1000Hz
No-load supply current	<= 12/<= 20mA
Off-state current	<= 10µA
Voltage drop	<= 2.5/-V
Short circuit protection	yes
Protected against polarity reversal	yes



Utilization categories
 Insulation class

DC 13
 -

Datasheet number:

Definitions see general catalog.
 If not otherwise noted, ratings according to
 IEC 60947-5-2 (DIN EN60947-5-2)

Balluff GmbH
 P.O.Box 1160
 73761 Neuhausen Germany
 Phone (07158) 173-0 Fax (07158) 5010

Datenblatt by CD-ROM - 10/2004

BALLUFF