




THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO CW INDUSTRIES INCORPORATED AND ITS AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN CW INDUSTRIES PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM CW INDUSTRIES INCORPORATED, SOUTHAMPTON, PENNSYLVANIA USA.

Rating		10A 24VDC		Mounting Hole 	Circuit Diagram 									
Contact Resistance		50m ohm Max.												
Insulation Resistance		DC 500V 100M ohm Min.												
Dielectric Strength		AC 1500V 1 minute												
Operation Temperature		-25°~85°												
Switch Function		3P SPST OFF-ON Lamp Dependent		<table><tr><td>Thickness(mm)</td><td>X(mm)</td><td>Y(mm)</td></tr><tr><td>0.75~1.25</td><td rowspan="3">21.0^{+0.3}₀</td><td>36.6+0.1</td></tr><tr><td>1.25~2.0</td><td>36.8+0.1</td></tr><tr><td>2.0~3.0</td><td>37.0+0.1</td></tr></table>	Thickness(mm)	X(mm)	Y(mm)	0.75~1.25	21.0 ^{+0.3} ₀	36.6+0.1	1.25~2.0	36.8+0.1	2.0~3.0	37.0+0.1
Thickness(mm)	X(mm)	Y(mm)												
0.75~1.25	21.0 ^{+0.3} ₀	36.6+0.1												
1.25~2.0		36.8+0.1												
2.0~3.0		37.0+0.1												
Lamp Type	LED 24VDC w/resistor													

Material:

1. Frame: Nylon-66(94V-2) - Black
Actuator: Nylon-66+33%GF - Black
Lens: PC - Black / Amber
Terminal: Silver plated copper
(excepted lamp terminal)
Printed: None
2. Waterproof: "IP-67".



TOLERANCE: $\pm 0.3\text{mm}$ UNLESS OTHERWISE SPECIFIED.

RoHS Compliant

3	Added Dependent to Function & Lamp Type. 12/19/2011.
2	Changed IP-66 to IP-67. 12/13/10
1	Switch Function OFF-ON was ON-OFF. 8/24/10.

CW INDUSTRIES
Southampton, Pa. 18966
Tel 215.355.7080/www.cwind.com

Date Drawn: 5/20/10

Rev. 3

Unit: mm

Checked By: *G. Gold*

Title: **ROCKER SWITCH**

CW P/N: **GRB292A201BBNA2**