





SYMBOL DEFINITION		MISSING NUMBERS
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL () DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON AN INDIVIDUAL COMPONENT DRAWING.	TOTAL NO. OF SYMBOLS ON DRAWING	7
	LAST NO. USED	10




DWO STATUS		ZONE		REVISION HISTORY		AUTH	DR	APVD	APVD
DATE	STG	REV	N/P	CHG					
29MY02	R	11	-	-	-	CLEARED REV COLUMN: 15405481 - REVISED GRAPHICS: M3571006 WAS PM003571 006, M2965008 WAS PM002965 008, M3571003 WAS PM003571 003; REVISED NOTES	226118	CJP	CJP MB
18JUL03	R	12	-	-	-	ALL PARTS - UPDATED PDM ATTRIBUTES	243602	JVM	JVM AD
25JUN04	R	13	-	-	-	ALL PARTS - UPDATED PDM ATTRIBUTES	256385	JTV	FKV MDM
13JUL05	R	14	-	-	-	15317832 - UPDATED PDM ATTRIBUTES AND ADDED FORD PRINT	270016	JBD	JVM CSD



TYPE 103
SAME AS TYPE 102 EXCEPT AS SHOWN



TYPE 102



NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:

DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION. (SEE MATH MODEL FOR PRECISE DIMENSIONS.) FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.

- THIS PART IS NOT CONTROLLED FOR AUTOMATIC FEEDING.
- MATERIAL RECYCLING CODE >PA6 (GB20+GF10)< PER SAE J1344 TO APPEAR ON PARTS 15317832 AND 15405481. >PA6T/61/66< PER SAE J1344 TO APPEAR ON 15401975. (1.2)X(0.1) RAISED CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE. OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.
- (2.3)X(0.1) DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION FOR EXISTING TOOLING MAY BE "PED".

15405481	04	-	103	M3571006 PA6 GB20+GF10 HS YEL	0.559
15401975	02	-	102	M2965008 PA6T/61/66 HS IM BLU	0.559
15317832	07	AA	102	M3571003 PA6 GB20+GF10 HS GRA	0.559
15317629	05	-	101	M3571009 PA6 GB20+GF10 HS PPL	0.559
PART NO	REV	N/P	STATUS	TYPE	MATERIAL SPEC & COLOR
					REPLACED BY
					VOL

DIMENSIONAL RANGE (MM)		TOLERANCE UNLESS OTHERWISE SPECIFIED		CHART	
FROM	TO	> 0	> 30	> 70	> 100
20	30	20	30	70	100
100	150	100	150	150	200
200	300	200	300	300	400
100	150	±0.2	±0.3	±0.4	±0.5
150	200	±0.4	±0.5	±0.6	±0.8
200	300	±0.5	±0.6	±0.8	±1
300	400	±0.6	±0.8	±1	±1.2
		ANGULAR TOLERANCE 12°			

DWO TYPE		PART DRAWING	
STYLE		SEE CHART	D
VOLUME (CM³)			
UNLESS OTHERWISE SPECIFIED		THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE 2018 DIMENSIONING AND TOLERANCING ADDENDUM - 1997. ALL GEOMETRIC TOLERANCES AND RELATED DATUMS APPLY. IF THE PART IS NOT A MACHINED PART, THE RELATIONSHIP BETWEEN FEATURES IS ESTABLISHED BY ORIENTATION OR LOCATION TOLERANCES. SEPARATE POSITION CALLOUTS MAY BE USED SEPARATELY, REGARDLESS OF DATUM REFERENCE. ALL DIMENSIONS ARE IN MILLIMETERS.	
REFERENCE		THIRD ANGLE PROJECTION	
DO NOT SCALE		USE MATH DATA	

DELPHI	
DELPHI PACKARD ELECTRIC SYSTEMS WARREN, OH	
DR	DATE
APVD1 R. D'ANDREA	25NO96
APVD2 R. D'ANDREA	25NO96
APVD3 ED ARANGO	12DE96
APVD4	
APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001	
MATERIAL SEC. CHART	
DRAWING NAME	
TAXI LOCK CPA	
DRAWING NUMBER	
15317831	
SIZE	SCALE
A0	5:1
FRAME NO	SHEET NO
1	1 OF 1
REV	N/P
1	R 14

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Delphi Connection Systems:](#)

[15317832](#)