

Amplifier Transistor




RoHS
Compliant




Features:

- Collector-Emitter Voltage: $V_{CE0} = 150V$
- Collector Dissipation: $P_C (\text{max}) = 625mW$
- Suffix "C" means Conter Collector
(1. Emitter 2. Collector 3. Base)



TO-92



Absolute Max. Ratings $T_A=25^{\circ}C$ unless otherwise noted

Parameter	Symbol	Value	Units
Collector-Base Voltage	V_{CBO}	160	V
Collector-Emitter Voltage	V_{CEO}	150	V
Emitter-Base Voltage	V_{EBO}	5	V
Collector Current	I_C	600	mA
Collector Dissipation	P_C	625	mW
Junction Temperature	T_J	150	$^{\circ}C$
Storage Temperature	T_{STG}	-55 to +150	$^{\circ}C$

Electrical Characteristics $T_A = 25^{\circ}C$ unless otherwise noted

Parameter	Symbol	Test Condition	Min.	Type	Max.	Units
Collector-Base Breakdown Voltage	BV_{CBO}	$I_C = 100\mu A, I_E = 0$	160			V
*Collector-Emitter Breakdown Voltage	BV_{CEO}	$I_C = 1mA, I_B = 0$	150			V
Emitter-Base Breakdown Voltage	BV_{EBO}	$I_E = 10\mu A, I_C = 0$	5			V
Collector Cut-off Current	I_{CBO}	$V_{CB} = 120V, I_E = 0$			50	nA
Emitter Cut-off Current	I_{EBO}	$V_{EB} = 3V, I_C = 0$			50	nA
*DC Current Gain	h_{FE}	$I_C = 1mA, V_{CE} = 5V$ $I_C = 10mA, V_{CE} = 5V$ $I_C = 50mA, V_{CE} = 5V$	30 60 50		240	
*Collector-Emitter Saturation Voltage	$V_{CE(sat)}$	$I_C = 10mA, I_B = 1mA$ $I_C = 50mA, I_B = 5mA$			0.2 0.5	V V
*Base-Emitter Saturation Voltage	$V_{BE(sat)}$	$I_C = 10mA, I_B = 1mA$ $I_C = 50mA, I_B = 5mA$			1 1	V V
Current Gain Bandwidth Product	f_T	$I_C = 10mA, V_{CE} = 10V,$ $f = 100MHz$	100		400	MHz
Output Capacitance	C_{ob}	$V_{CB} = 10V, I_E=0, f = 1MHz$			6	pF
Noise Figure	N_F	$I_C = 250\mu A, V_{CE} = 5V$ $R_S=1K\Omega$ $f = 10Hz \text{ to } 15.7KHz$			8	dB

* Pulse Test : Pulse Width $\leq 300\mu s$, Duty Cycle $\leq 2\%$

Typical Characteristics




Figure 1. DC current Gain




Figure 2. Base-Emitter Saturation Voltage
Collector-Emitter Saturation Voltage




Figure 3. Base-Emitter On Voltage




Figure 4. Output Capacitance





Figure 5. Current Gain Bandwidth Product

Package Dimensions:



Dimensions : Millimetres

Part Number Table

Description	Part Number
PNP Epitaxial Silicon Transistor	2N5401

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.