



Features

- Low power consumption
- Robust package
- I.C. Compatible
- Standard configuration: Gray face w/ white segments
- Optional black face provides superior color contrast
- RoHS Compliant


RECOMMENDED PCB LAYOUT


ATTENTION
OBSERVE PRECAUTIONS
FOR HANDLING
ELECTROSTATIC
DISCHARGE
SENSITIVE
DEVICES

Package Schematics

Notes:

1. All dimensions are in millimeters (inches), Tolerance is $\pm 0.25(0.01")$ unless otherwise noted.
2. Specifications are subject to change without notice.

Absolute Maximum Ratings ($T_A=25^\circ\text{C}$)		CBD (InGaN)	Unit
Reverse Voltage (Per Chip)	V_R	5	V
Forward Current (D _p)	I_F	30 (30)	mA
Forward Current (Peak) 1/10Duty Cycle 0.1ms Pulse Width (D _p)	i_{fs}	150 (150)	mA
Power Dissipation (Per Chip)	P_D	120	mW
Operating Temperature	T_A	-40 ~ +85	$^\circ\text{C}$
Storage Temperature	T _{stg}	-40 ~ +85	
Electrostatic Discharge Threshold (HBM)		250	V
Lead Solder Temperature [2mm Below Package Base]	260°C For 3-5 Seconds		


Operating Characteristics ($T_A=25^\circ\text{C}$)		CBD (InGaN)	Unit
Forward Voltage (Typ.) (D _p) (I _f =10mA)	V_F	6.0 (3.0)	V
Forward Voltage (Max.) (D _p) (I _f =10mA)	V_F	8 (4.0)	V
Reverse Current (Max.) (Per Chip) ($V_R=5\text{V}$)	I_R	50	uA
Wavelength of Peak Emission CIE127-2007* (Typ.) (I _f =10mA)	λ_P	465*	nm
Wavelength of Dominant Emission CIE127-2007* (Typ.) (I _f =10mA)	λ_D	460*	nm
Spectral Line Full Width At Half-Maximum (Typ.) (I _f =10mA)	$\Delta\lambda$	25	nm
Capacitance (Typ.) (V _F =0V, f=1MHz)	C	100	pF

Part Number	Emitting Color	Emitting Material	Luminous Intensity CIE127-2007* (I _f =10mA) ucd	Wavelength CIE127-2007* nm λ_P	Description
XDCBD25C	Blue	InGaN	21000 *	53990 *	460 *









min. typ.

 Common Cathode, Rt.
Hand Decimal


*Luminous intensity value and wavelength are in accordance with CIE127-2007 standards.



❖ CBD



Wave Soldering Profile for Thru-Hole Products (Pb-Free Components)



Remarks:

If special sorting is required (e.g. binning based on forward voltage, luminous intensity / luminous flux, or wavelength), the typical accuracy of the sorting process is as follows:




1. Wavelength: +/-1nm

2. Luminous Intensity / Luminous Flux: +/-15%

3. Forward Voltage: +/-0.1V

Note: Accuracy may depend on the sorting parameters.

PACKING & LABEL SPECIFICATIONS



TERMS OF USE

1. Data presented in this document reflect statistical figures and should be treated as technical reference only.
2. Contents within this document are subject to improvement and enhancement changes without notice.
3. The product(s) in this document are designed to be operated within the electrical and environmental specifications indicated on the datasheet. User accepts full risk and responsibility when operating the product(s) beyond their intended specifications.
4. The product(s) described in this document are intended for electronic applications in which a person's life is not reliant upon the LED. Please consult with a SunLED representative for special applications where the LED may have a direct impact on a person's life.
5. The contents within this document may not be altered without prior consent by SunLED.
6. Additional technical notes are available at <http://www.SunLEDusa.com/TechnicalNotes.asp>