







- NOTES:
- ELECTRICAL:
CONTACT RESISTANCE: 20 MILLIOHMS MAX, INITIAL
50 MILLIOHMS MAX, AFTER LIFE
INSULATION RESISTANCE: 50 MEGAOHMS MIN. AT 500 VDC
DIELECTRIC WITHSTANDING VOLTAGE: 250 VAC
 - MECHANICAL:
LIFE: 5000 CYCLES
INSERTION FORCE: 0,4 KG TO 1,6 KG
WITHDRAWAL FORCE: 0,4 KG TO 1,4 KG
 - MATERIALS:
HOUSING: PBT +15% GLASS FILLED, BLACK, UL94V0
BUSHING: BRASS, NICKEL PLATED
SPRINGS: COPPER ALLOY, SILVER PLATED
COVER: POLYCARBONATE, CLEAR, UL94V0.
 - THIS PRODUCT IS RoHS COMPLIANT.



SCALE 4:1



P.C. BOARD
(COMPONENT SIDE)

SUPPLIED WITH KNURL NUT.

CUSTOMER DRAWING

PART NO.	SCHEMATIC
35RAPC3BV4	
35RAPC4BV4	
35RAPC2BV4	
35RAPC2AV4	

G	27551	8-4-15	TO	TJK	★ STAR SYMBOL DENOTES CRITICAL DIMENSION	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.
F	27312	6-19-14	TJK	TJK	UNLESS OTHERWISE SPECIFIED	SIZE WIDTH MULT LBS/M TEMPER
E	26658	11-10-10	TO	TJK	1. ALL DIMENSIONS IN INCHES - TWO PLACE DECIMALS ±0.01 - THREE PALCE DECIMALS ±0.005 - FRACTIONAL DIMENSIONS ±1/64 - ANGLES ±1° - ALL DIA. CONCENTRIC WITHIN 0.005 T.I.R.	FINISH MATERIAL SPEC No.
D	ECO #20278	11-5-96	MM	EBR	2. FEATURES ON THE SAME CENTERLINE MUST BE ALIGNED WITHIN ±0.002	FIRST USED ON SCALE 4:1
C	ECO #19567	5-5-95	SG	GHJ	3. REMOVE ALL BURRS	DATE DRAWN BY CHKD APVD 7-Dec-93 LR 12-10-93 12-10-93
B	ECO #19058	6-29-94	LR	EBR	DO NOT SCALE DRAWING	NAME 3.5 MM VERTICAL STEREO JACK, RoHS
A	FIRST DRAWN	12-7-93	LR	EBR		SHEET 1 OF 1
REV	ECO NUMBER	DATE	BY	APVD		PART No. 35RAPC__V4
REVISIONS						REV G