




COIL: @ 25°C

RESISTANCE 3300 OHMS $\pm 10\%$

NOMINAL VOLTAGE 26.5 VDC

MUST OPERATE 14.0 VDC

MUST RELEASE 8.0 VDC MAX. 1.4 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's

SHOCK 75 g's 6 MS. DURATION


TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 4 MS MAX

RELEASE TIME 7.5 MS MAX

CONTACT STABILIZATION TIME 2.0 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 3/15/96 CK3/15/96 JMB

**COMMUNICATIONS
INSTRUMENTS, INC.**

JMSCD-26XP

CUST. QPL

CUST. NO. M39016/16-036P

TYPE JMSD RELAY