



PDB183-GTR - 17 mm Guitar Potentiometer w/Push-Pull Switch

BOURNS®


Product Dimensions

**PDB183-GTR03,
PDB183-GTR04**




Circuit


Single Gang




Dual Gang




Switch



Schematic



PDB183-GTR05



DIMENSIONS: $\frac{\text{MM}}{\text{(INCHES)}}$

Specifications are subject to change without notice.
The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time.
Users should verify actual device performance in their specific applications.

BOURNS®

Technical drawing showing the dimensions of a NUT and a WASHER.

NUT:

- Thread: M3/8" - 32 UNF
- Outer Diameter: 12.7 ± 0.5 ($.472 \pm .020$)
- Height: 2.5 ± 0.2 ($.098 \pm .008$)

WASHER:

- Outer Diameter: 14.0 ± 0.5 ($.157 \pm .020$) DIA.
- Inner Diameter: 9.5 ± 0.2 ($.374 \pm .008$) DIA.

17.0 $\pm$ 0.5
(.669 $\pm$.020)

30 °

FULL CCW

3 PLCS.
1.5 X 2.5
(.059 X .098)

5.0 $\pm$ 0.3
(.197 $\pm$.012)

5.0 $\pm$ 0.3
(.197 $\pm$.012)

Technical drawing of a shaft with the following dimensions and tolerances:



- Overall length: 27.5 ± 0.2 ($1.083 \pm .008$)
- Distance from left end to start of thread: 19.0 ± 0.1 ($.748 \pm .004$)
- Thread specification: $\frac{3}{8}'' \times \frac{0.75}{(.030)}$
- Thread length: $C \frac{0.5}{(.020)} \times 45^\circ$
- End diameter: $\frac{6.0 \pm 0.3}{(.236 \pm .012)}$ DIA.

The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time. Users should verify actual device performance in their specific applications.


PDB183-GTR - 17 mm Guitar Potentiometer w/Push-Pull Switch

BOURNS®

Tapers



Typical Part Marking



DIMENSIONS: $\frac{\text{MM}}{\text{(INCHES)}}$

REV. 04/14

Specifications are subject to change without notice.

The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time. Users should verify actual device performance in their specific applications.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bourns:

[PDB183-GTR21-254A2](#) [PDB183-GTR21-504A2](#) [PDB183-GTR22-254A2](#) [PDB183-GTR22-504A2](#) [PDB183-GTR32-504A2](#) [PDB183-GTR31-504A2](#) [PDB183-GTR01-304B](#) [PDB183-GTR01-504B0](#) [PDB183-GTR01-254A2](#) [PDB183-GTR03-504A2](#) [PDB183-GTR01-103A2](#) [PDB183-GTR01-105A2](#) [PDB183-GTR01-105B0](#) [PDB183-GTR01-304B0](#) [PDB183-GTR01-504A2](#) [PDB183-GTR02-105A2](#) [PDB183-GTR02-254A2](#) [PDB183-GTR02-504A2](#) [PDB183-GTR03-254A2](#) [PDB183-GTR03-254B0](#) [PDB183-GTR03-253A2](#) [PDB183-GTR04-253A2](#) [PDB183-GTR22-304B0](#) [PDB183-GTR31-254A2](#) [PDB183-GTR01-253A2](#) [PDB183-GTR01-104A2](#) [PDB183-GTR32-254A2](#) [PDB183-GTR03-103A2](#) [PDB183-GTR11-254A2](#) [PDB183-GTR11-504A2](#) [PDB183-GTR04-103A2](#) [PDB183-GTR31-105A2](#) [PDB183-GTR02-253A2](#) [PDB183-GTR11-253A2](#)