

# ON Semiconductor

## Is Now



To learn more about onsemi™, please visit our website at  
[www.onsemi.com](http://www.onsemi.com)

onsemi and onsemi. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application, Buyer shall indemnify and hold onsemi and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that onsemi was negligent regarding the design or manufacture of the part. onsemi is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner. Other names and brands may be claimed as the property of others.

# MC14541B

## Programmable Timer

The MC14541B programmable timer consists of a 16-stage binary counter, an integrated oscillator for use with an external capacitor and two resistors, an automatic power-on reset circuit, and output control logic.

Timing is initialized by turning on power, whereupon the power-on reset is enabled and initializes the counter, within the specified  $V_{DD}$  range. With the power already on, an external reset pulse can be applied. Upon release of the initial reset command, the oscillator will oscillate with a frequency determined by the external RC network. The 16-stage counter divides the oscillator frequency ( $f_{osc}$ ) with the  $n^{th}$  stage frequency being  $f_{osc}/2^n$ .

### Features

- Available Outputs  $2^8$ ,  $2^{10}$ ,  $2^{13}$  or  $2^{16}$
- Increments on Positive Edge Clock Transitions
- Built-in Low Power RC Oscillator ( $\pm 2\%$  accuracy over temperature range and  $\pm 20\%$  supply and  $\pm 3\%$  over processing at  $< 10$  kHz)
- Oscillator May Be Bypassed if External Clock Is Available (Apply external clock to Pin 3)
- External Master Reset Totally Independent of Automatic Reset Operation
- Operates as  $2^n$  Frequency Divider or Single Transition Timer
- $Q/\bar{Q}$  Select Provides Output Logic Level Flexibility
- Reset (auto or master) Disables Oscillator During Resetting to Provide No Active Power Dissipation
- Clock Conditioning Circuit Permits Operation with Very Slow Clock Rise and Fall Times
- Automatic Reset Initializes All Counters On Power Up
- Supply Voltage Range = 3.0 Vdc to 18 Vdc with Auto Reset  
Disabled (Pin 5 =  $V_{DD}$ )  
= 8.5 Vdc to 18 Vdc with Auto Reset  
Enabled (Pin 5 =  $V_{SS}$ )
- NLV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q100 Qualified and PPAP Capable
- These Devices are Pb-Free and are RoHS Compliant



ON Semiconductor®


[www.onsemi.com](http://www.onsemi.com)



SOIC-14  
D SUFFIX  
CASE 751A




SOEIAJ-14  
F SUFFIX  
CASE 965




TSSOP-14  
DT SUFFIX  
CASE 948G

### PIN ASSIGNMENT




NC = NO CONNECTION


### MARKING DIAGRAMS



SOIC-14



SOEIAJ-14



TSSOP-14

A = Assembly Location  
WL, L = Wafer Lot  
YY, Y = Year  
WW, W = Work Week  
G or ■ = Pb-Free Package

(Note: Microdot may be in either location)

### ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 2 of this data sheet.

# MC14541B

## MAXIMUM RATINGS (Voltages Referenced to $V_{SS}$ )

| Symbol            | Parameter                                        | Value                  | Unit |
|-------------------|--------------------------------------------------|------------------------|------|
| $V_{DD}$          | DC Supply Voltage Range                          | -0.5 to +18.0          | V    |
| $V_{in}, V_{out}$ | Input or Output Voltage Range, (DC or Transient) | -0.5 to $V_{DD} + 0.5$ | V    |
| $I_{in}$          | Input Current (DC or Transient)                  | $\pm 10$ (per Pin)     | mA   |
| $I_{out}$         | Output Current (DC or Transient)                 | $\pm 45$ (per Pin)     | mA   |
| $P_D$             | Power Dissipation, per Package (Note 1)          | 500                    | mW   |
| $T_A$             | Ambient Temperature Range                        | -55 to +125            | °C   |
| $T_{stg}$         | Storage Temperature Range                        | -65 to +150            | °C   |
| $T_L$             | Lead Temperature, (8-Second Soldering)           | 260                    | °C   |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Temperature Derating: "D/DW" Packages: -7.0 mW/°C From 65°C To 125°C

## ORDERING INFORMATION

| Device          | Package                | Shipping <sup>†</sup> |
|-----------------|------------------------|-----------------------|
| MC14541BDG      | SOIC-14<br>(Pb-Free)   | 55 Units / Rail       |
| NLV14541BDG*    | SOIC-14<br>(Pb-Free)   | 55 Units / Rail       |
| MC14541BDR2G    | SOIC-14<br>(Pb-Free)   | 2500 / Tape & Reel    |
| NLV14541BDR2G*  | SOIC-14<br>(Pb-Free)   | 2500 / Tape & Reel    |
| MC14541BDTR2G   | TSSOP-14<br>(Pb-Free)  | 2500 / Tape & Reel    |
| NLV14541BDTR2G* | TSSOP-14<br>(Pb-Free)  | 2500 / Tape & Reel    |
| MC14541BFELG    | SOEIAJ-14<br>(Pb-Free) | 2000 / Tape & Reel    |

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

\*NLV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q100 Qualified and PPAP Capable.

# MC14541B

## ELECTRICAL CHARACTERISTICS (Voltages Referenced to V<sub>SS</sub>)

| Characteristic                                                                                                                                                      | Symbol           | V <sub>DD</sub><br>Vdc | – 55°C                                                                                                                                                      |                      | 25°C                    |                           |                      | 125°C                   |                      | Unit |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------|------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------|-------------------------|---------------------------|----------------------|-------------------------|----------------------|------|
|                                                                                                                                                                     |                  |                        | Min                                                                                                                                                         | Max                  | Min                     | Typ<br>(Note 2)           | Max                  | Min                     | Max                  |      |
| Output Voltage<br>“0” Level<br>V <sub>in</sub> = V <sub>DD</sub> or 0                                                                                               | V <sub>OL</sub>  | 5.0<br>10<br>15        | –<br>–<br>–                                                                                                                                                 | 0.05<br>0.05<br>0.05 | –<br>–<br>–             | 0<br>0<br>0               | 0.05<br>0.05<br>0.05 | –<br>–<br>–             | 0.05<br>0.05<br>0.05 | Vdc  |
| V <sub>in</sub> = 0 or V <sub>DD</sub><br>“1” Level                                                                                                                 | V <sub>OH</sub>  | 5.0<br>10<br>15        | 4.95<br>9.95<br>14.95                                                                                                                                       | –<br>–<br>–          | 4.95<br>9.95<br>14.95   | 5.0<br>10<br>15           | –<br>–<br>–          | 4.95<br>9.95<br>14.95   | –<br>–<br>–          | Vdc  |
| Input Voltage<br>“0” Level<br>(V <sub>O</sub> = 4.5 or 0.5 Vdc)<br>(V <sub>O</sub> = 9.0 or 1.0 Vdc)<br>(V <sub>O</sub> = 13.5 or 1.5 Vdc)                          | V <sub>IL</sub>  | 5.0<br>10<br>15        | –<br>–<br>–                                                                                                                                                 | 1.5<br>3.0<br>4.0    | –<br>–<br>–             | 2.25<br>4.50<br>6.75      | 1.5<br>3.0<br>4.0    | –<br>–<br>–             | 1.5<br>3.0<br>4.0    | Vdc  |
| V <sub>in</sub> = 0 or V <sub>DD</sub><br>“1” Level<br>(V <sub>O</sub> = 0.5 or 4.5 Vdc)<br>(V <sub>O</sub> = 1.0 or 9.0 Vdc)<br>(V <sub>O</sub> = 1.5 or 13.5 Vdc) | V <sub>IH</sub>  | 5.0<br>10<br>15        | 3.5<br>7.0<br>11                                                                                                                                            | –<br>–<br>–          | 3.5<br>7.0<br>11        | 2.75<br>5.50<br>8.25      | –<br>–<br>–          | 3.5<br>7.0<br>11        | –<br>–<br>–          | Vdc  |
| Output Drive Current<br>(V <sub>OH</sub> = 2.5 Vdc)<br>(V <sub>OH</sub> = 9.5 Vdc)<br>(V <sub>OH</sub> = 13.5 Vdc)<br>Source                                        | I <sub>OH</sub>  | 5.0<br>10<br>15        | –4.19<br>–7.96<br>–16.3                                                                                                                                     | –<br>–<br>–          | –3.38<br>–6.42<br>–13.2 | –6.75<br>–12.83<br>–26.33 | –<br>–<br>–          | –2.37<br>–4.49<br>–9.24 | –<br>–<br>–          | mAdc |
| (V <sub>OL</sub> = 0.4 Vdc)<br>(V <sub>OL</sub> = 0.5 Vdc)<br>(V <sub>OL</sub> = 1.5 Vdc)<br>Sink                                                                   | I <sub>OL</sub>  | 5.0<br>10<br>15        | 1.93<br>4.96<br>19.3                                                                                                                                        | –<br>–<br>–          | 1.56<br>4.0<br>15.6     | 3.12<br>8.0<br>31.2       | –<br>–<br>–          | 1.09<br>2.8<br>10.9     | –<br>–<br>–          | mAdc |
| Input Current                                                                                                                                                       | I <sub>in</sub>  | 15                     | –                                                                                                                                                           | ±0.1                 | –                       | ±0.00001                  | ±0.1                 | –                       | ±1.0                 | μAdc |
| Input Capacitance<br>(V <sub>in</sub> = 0)                                                                                                                          | C <sub>in</sub>  | –                      | –                                                                                                                                                           | –                    | –                       | 5.0                       | 7.5                  | –                       | –                    | pF   |
| Quiescent Current<br>(Pin 5 is High)<br>Auto Reset Disabled                                                                                                         | I <sub>DD</sub>  | 5.0<br>10<br>15        | –<br>–<br>–                                                                                                                                                 | 5.0<br>10<br>20      | –<br>–<br>–             | 0.005<br>0.010<br>0.015   | 5.0<br>10<br>20      | –<br>–<br>–             | 150<br>300<br>600    | μAdc |
| Auto Reset Quiescent Current<br>(Pin 5 is low)                                                                                                                      | I <sub>DDR</sub> | 10<br>15               | –<br>–                                                                                                                                                      | 250<br>500           | –<br>–                  | 30<br>82                  | 250<br>500           | –<br>–                  | 1500<br>2000         | μAdc |
| Supply Current (Notes 3 & 4)<br>(Dynamic plus Quiescent)                                                                                                            | I <sub>D</sub>   | 5.0<br>10<br>15        | I <sub>D</sub> = (0.4 μA/kHz) f + I <sub>DD</sub><br>I <sub>D</sub> = (0.8 μA/kHz) f + I <sub>DD</sub><br>I <sub>D</sub> = (1.2 μA/kHz) f + I <sub>DD</sub> |                      |                         |                           |                      |                         |                      | μAdc |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

2. Data labelled "Typ" is not to be used for design purposes but is intended as an indication of the IC's potential performance.

3. The formulas given are for the typical characteristics only at 25°C.

4. When using the on chip oscillator the total supply current (in μAdc) becomes: I<sub>T</sub> = I<sub>D</sub> + 2 C<sub>tc</sub> V<sub>DD</sub> f × 10<sup>–3</sup> where I<sub>D</sub> is in μA, C<sub>tc</sub> is in pF, V<sub>DD</sub> in Volts DC, and f in kHz. (see Fig. 3) Dissipation during power-on with automatic reset enabled is typically 50 μA @ V<sub>DD</sub> = 10 Vdc.

# MC14541B

## SWITCHING CHARACTERISTICS (Note 5) ( $C_L = 50$ pF, $T_A = 25^\circ\text{C}$ )

| Characteristic                                                                                                                                                                                                                                          | Symbol                  | $V_{DD}$        | Min               | Typ<br>(Note 6)    | Max                | Unit          |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------|-----------------|-------------------|--------------------|--------------------|---------------|
| Output Rise and Fall Time<br>$t_{TLH}, t_{THL} = (1.5 \text{ ns/pF}) C_L + 25 \text{ ns}$<br>$t_{TLH}, t_{THL} = (0.75 \text{ ns/pF}) C_L + 12.5 \text{ ns}$<br>$t_{TLH}, t_{THL} = (0.55 \text{ ns/pF}) C_L + 9.5 \text{ ns}$                          | $t_{TLH},$<br>$t_{THL}$ | 5.0<br>10<br>15 | –<br>–<br>–       | 100<br>50<br>40    | 200<br>100<br>80   | ns            |
| Propagation Delay, Clock to Q ( $2^8$ Output)<br>$t_{PLH}, t_{PHL} = (1.7 \text{ ns/pF}) C_L + 3415 \text{ ns}$<br>$t_{PLH}, t_{PHL} = (0.66 \text{ ns/pF}) C_L + 1217 \text{ ns}$<br>$t_{PLH}, t_{PHL} = (0.5 \text{ ns/pF}) C_L + 875 \text{ ns}$     | $t_{PLH}$<br>$t_{PHL}$  | 5.0<br>10<br>15 | –<br>–<br>–       | 3.5<br>1.25<br>0.9 | 10.5<br>3.8<br>2.9 | $\mu\text{s}$ |
| Propagation Delay, Clock to Q ( $2^{16}$ Output)<br>$t_{PHL}, t_{PLH} = (1.7 \text{ ns/pF}) C_L + 5915 \text{ ns}$<br>$t_{PHL}, t_{PLH} = (0.66 \text{ ns/pF}) C_L + 3467 \text{ ns}$<br>$t_{PHL}, t_{PLH} = (0.5 \text{ ns/pF}) C_L + 2475 \text{ ns}$ | $t_{PHL}$<br>$t_{PLH}$  | 5.0<br>10<br>15 | –<br>–<br>–       | 6.0<br>3.5<br>2.5  | 18<br>10<br>7.5    | $\mu\text{s}$ |
| Clock Pulse Width                                                                                                                                                                                                                                       | $t_{WH(cl)}$            | 5.0<br>10<br>15 | 900<br>300<br>225 | 300<br>100<br>85   | –<br>–<br>–        | ns            |
| Clock Pulse Frequency (50% Duty Cycle)                                                                                                                                                                                                                  | $f_{cl}$                | 5.0<br>10<br>15 | –<br>–<br>–       | 1.5<br>4.0<br>6.0  | 0.75<br>2.0<br>3.0 | MHz           |
| MR Pulse Width                                                                                                                                                                                                                                          | $t_{WH(R)}$             | 5.0<br>10<br>15 | 900<br>300<br>225 | 300<br>100<br>85   | –<br>–<br>–        | ns            |
| Master Reset Removal Time                                                                                                                                                                                                                               | $t_{rem}$               | 5.0<br>10<br>15 | 420<br>200<br>200 | 210<br>100<br>100  | –<br>–<br>–        | ns            |

5. The formulas given are for the typical characteristics only at  $25^\circ\text{C}$ .

6. Data labelled "Typ" is not to be used for design purposes but is intended as an indication of the IC's potential performance.




Figure 1. Power Dissipation Test Circuit and Waveform






Figure 2. Switching Time Test Circuit and Waveforms

### EXPANDED BLOCK DIAGRAM



| A | B | Number of Counter Stages<br>n | Count<br>2 <sup>n</sup> |
|---|---|-------------------------------|-------------------------|
| 0 | 0 | 13                            | 8192                    |
| 0 | 1 | 10                            | 1024                    |
| 1 | 0 | 8                             | 256                     |
| 1 | 1 | 16                            | 65536                   |

| Pin                 |    | State                            |                                   |
|---------------------|----|----------------------------------|-----------------------------------|
|                     |    | 0                                | 1                                 |
| Auto Reset,         | 5  | Auto Reset Operating             | Auto Reset Disabled               |
| Master Reset,       | 6  | Timer Operational                | Master Reset On                   |
| Q/ $\overline{Q}$ , | 9  | Output Initially Low After Reset | Output Initially High After Reset |
| Mode,               | 10 | Single Cycle Mode                | Recycle Mode                      |



5

## TYPICAL RC OSCILLATOR CHARACTERISTICS





Figure 4. RC Oscillator Stability

Figure 5. RC Oscillator Frequency as a Function of  $R_{tc}$  and  $C_{tc}$ 

## OPERATING CHARACTERISTICS

With Auto Reset pin set to a “0” the counter circuit is initialized by turning on power. Or with power already on, the counter circuit is reset when the Master Reset pin is set to a “1”. Both types of reset will result in synchronously resetting all counter stages independent of counter state. Auto Reset pin when set to a “1” provides a low power operation.

The RC oscillator as shown in Figure 3 will oscillate with a frequency determined by the external RC network i.e.,

$$f = \frac{1}{2.3 R_{tc} C_{tc}} \quad \text{if } (1 \text{ kHz} \leq f \leq 100 \text{ kHz})$$

and  $R_S \approx 2 R_{tc}$  where  $R_S \geq 10 \text{ k}\Omega$


The time select inputs (A and B) provide a two-bit address to output any one of four counter stages ( $2^8$ ,  $2^{10}$ ,  $2^{13}$  and  $2^{16}$ ). The  $2^n$  counts as shown in the Frequency Selection Table represents the Q output of the  $N^{\text{th}}$  stage of the counter. When A is “1”,  $2^{16}$  is selected for both states of B. However,

when B is “0”, normal counting is interrupted and the 9th counter stage receives its clock directly from the oscillator (i.e., effectively outputting  $2^8$ ).

The Q/Q select output control pin provides for a choice of output level. When the counter is in a reset condition and Q/Q select pin is set to a “0” the Q output is a “0”, correspondingly when Q/Q select pin is set to a “1” the Q output is a “1”.

When the mode control pin is set to a “1”, the selected count is continually transmitted to the output. But, with mode pin “0” and after a reset condition the  $R_S$  flip-flop (see Expanded Block Diagram) resets, counting commences, and after  $2^{n-1}$  counts the  $R_S$  flip-flop sets which causes the output to change state. Hence, after another  $2^{n-1}$  counts the output will not change. Thus, a Master Reset pulse must be applied or a change in the mode pin level is required to reset the single cycle operation.

## DIGITAL TIMER APPLICATION



When Master Reset (MR) receives a positive pulse, the internal counters and latch are reset. The Q output goes high and remains high until the selected (via A and B) number of clock pulses are counted, the Q output then goes low and remains low until another input pulse is received.


This “one shot” is fully retriggerable and as accurate as the input frequency. An external clock can be used (pin 3 is the clock input, pins 1 and 2 are outputs) if additional accuracy is needed.

Notice that a setup time equal to the desired pulse width output is required immediately following initial power up, during which time Q output will be high.

# MC14541B

## PACKAGE DIMENSIONS

SOIC-14 NB  
CASE 751A-03  
ISSUE L




### NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. DIMENSION b DOES NOT INCLUDE DAMBAR PROTRUSION. ALLOWABLE PROTRUSION SHALL BE 0.13 TOTAL IN EXCESS OF AT MAXIMUM MATERIAL CONDITION.
4. DIMENSIONS D AND E DO NOT INCLUDE MOLD PROTRUSIONS.
5. MAXIMUM MOLD PROTRUSION 0.15 PER SIDE.

| DIM | MILLIMETERS |      | INCHES    |       |
|-----|-------------|------|-----------|-------|
|     | MIN         | MAX  | MIN       | MAX   |
| A   | 1.35        | 1.75 | 0.054     | 0.068 |
| A1  | 0.10        | 0.25 | 0.004     | 0.010 |
| A3  | 0.19        | 0.25 | 0.008     | 0.010 |
| b   | 0.35        | 0.49 | 0.014     | 0.019 |
| D   | 8.55        | 8.75 | 0.337     | 0.344 |
| E   | 3.80        | 4.00 | 0.150     | 0.157 |
| e   | 1.27 BSC    |      | 0.050 BSC |       |
| H   | 5.80        | 6.20 | 0.228     | 0.244 |
| h   | 0.25        | 0.50 | 0.010     | 0.019 |
| L   | 0.40        | 1.25 | 0.016     | 0.049 |
| M   | 0°          | 7°   | 0°        | 7°    |

### SOLDERING FOOTPRINT\*




DIMENSIONS: MILLIMETERS

\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

# MC14541B

## PACKAGE DIMENSIONS

TSSOP-14  
CASE 948G  
ISSUE C




### NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: MILLIMETER.
3. DIMENSION A DOES NOT INCLUDE MOLD FLASH, PROTRUSIONS OR GATE BURRS. MOLD FLASH OR GATE BURRS SHALL NOT EXCEED 0.15 (0.006) PER SIDE.
4. DIMENSION B DOES NOT INCLUDE INTERLEAD FLASH OR PROTRUSION. INTERLEAD FLASH OR PROTRUSION SHALL NOT EXCEED 0.25 (0.010) PER SIDE.
5. DIMENSION K DOES NOT INCLUDE DAMBAR PROTRUSION. ALLOWABLE DAMBAR PROTRUSION SHALL BE 0.08 (0.003) TOTAL IN EXCESS OF THE K DIMENSION AT MAXIMUM MATERIAL CONDITION.
6. TERMINAL NUMBERS ARE SHOWN FOR REFERENCE ONLY.
7. DIMENSION A AND B ARE TO BE DETERMINED AT DATUM PLANE -W-.

| DIM | MILLIMETERS |      | INCHES |       |
|-----|-------------|------|--------|-------|
|     | MIN         | MAX  | MIN    | MAX   |
| A   | 4.90        | 5.10 | 0.193  | 0.200 |
| B   | 4.30        | 4.50 | 0.169  | 0.177 |
| C   | ---         | 1.20 | ---    | 0.047 |
| D   | 0.05        | 0.15 | 0.002  | 0.006 |
| F   | 0.50        | 0.75 | 0.020  | 0.030 |
| G   | 0.65        | BSC  | 0.026  | BSC   |
| H   | 0.50        | 0.60 | 0.020  | 0.024 |
| J   | 0.09        | 0.20 | 0.004  | 0.008 |
| J1  | 0.09        | 0.16 | 0.004  | 0.006 |
| K   | 0.19        | 0.30 | 0.007  | 0.012 |
| K1  | 0.19        | 0.25 | 0.007  | 0.010 |
| L   | 6.40        | BSC  | 0.252  | BSC   |
| M   | 0°          | 8°   | 0°     | 8°    |

### SOLDERING FOOTPRINT\*





\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.


# MC14541B

## PACKAGE DIMENSIONS

SOEIAJ-14  
CASE 965  
ISSUE B



DETAIL P



### NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: MILLIMETER.
3. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH OR PROTRUSIONS AND ARE MEASURED AT THE PARTING LINE. MOLD FLASH OR PROTRUSIONS SHALL NOT EXCEED 0.15 (0.006) PER SIDE.
4. TERMINAL NUMBERS ARE SHOWN FOR REFERENCE ONLY.
5. THE LEAD WIDTH DIMENSION (b) DOES NOT INCLUDE DAMBAR PROTRUSION. ALLOWABLE DAMBAR PROTRUSION SHALL BE 0.08 (0.003) TOTAL IN EXCESS OF THE LEAD WIDTH DIMENSION AT MAXIMUM MATERIAL CONDITION. DAMBAR CANNOT BE LOCATED ON THE LOWER RADIUS OR THE FOOT. MINIMUM SPACE BETWEEN PROTRUSIONS AND ADJACENT LEAD TO BE 0.46 (0.018).

| DIM            | MILLIMETERS |       | INCHES    |       |
|----------------|-------------|-------|-----------|-------|
|                | MIN         | MAX   | MIN       | MAX   |
| A              | ---         | 2.05  | ---       | 0.081 |
| A <sub>1</sub> | 0.05        | 0.20  | 0.002     | 0.008 |
| b              | 0.35        | 0.50  | 0.014     | 0.020 |
| c              | 0.10        | 0.20  | 0.004     | 0.008 |
| D              | 9.90        | 10.50 | 0.390     | 0.413 |
| E              | 5.10        | 5.45  | 0.201     | 0.215 |
| e              | 1.27 BSC    |       | 0.050 BSC |       |
| H <sub>E</sub> | 7.40        | 8.20  | 0.291     | 0.323 |
| L              | 0.50        | 0.85  | 0.020     | 0.033 |
| L <sub>E</sub> | 1.10        | 1.50  | 0.043     | 0.059 |
| M              | 0 °         | 10 °  | 0 °       | 10 °  |
| Q <sub>1</sub> | 0.70        | 0.90  | 0.028     | 0.035 |
| Z              | ---         | 1.42  | ---       | 0.056 |

ON Semiconductor and  are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marketing.pdf](http://www.onsemi.com/site/pdf/Patent-Marketing.pdf). ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

### PUBLICATION ORDERING INFORMATION

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor  
19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA  
Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada  
Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada  
Email: [orderlit@onsemi.com](mailto:orderlit@onsemi.com)

N. American Technical Support: 800-282-9855 Toll Free  
USA/Canada  
Europe, Middle East and Africa Technical Support:  
Phone: 421 33 790 2910

ON Semiconductor Website: [www.onsemi.com](http://www.onsemi.com)

Order Literature: <http://www.onsemi.com/orderlit>

For additional information, please contact your local Sales Representative