

FEATURES

- 2 Form C contact
- High sensitivity-200 mW nominal operating power
- High breakdown voltage
1500 V FCC surge between open contacts
- DIP-2C type matching 16 pin IC socket
- Sealed construction

SPECIFICATIONS

Contact

Arrangement		2 Form C
Initial contact resistance, max. (By voltage drop 6 V DC 1 A)		50 mΩ
Contact material		Gold-clad silver
Rating (resistive)	Max. switching power	60 W, 62.5 VA
	Max. switching voltage	220 V DC, 250 V AC
	Max. switching current	2 A
	Max. carrying current	3 A
Expected life (min. operations)	Mechanical	1×10 ⁸
	Electrical	1 A 30 V DC
		5×10 ⁵
2 A 30 V DC		1×10 ⁵

Coil (polarized) (at 20°C 68°F)

Single side stable	Minimum operating power	Approx. 98 mW (147 mW: 48 V)
	Nominal operating power	Approx. 200 mW (300 mW: 48 V)
2 coil latching	Minimum set and reset power	Approx. 88 mW (177 mW: 48 V)
	Nominal set and reset power	Approx. 180 mW (360 mW: 48 V)

Remarks

* Specifications will vary with foreign standards certification ratings.

*1 Measurement at same location as "Initial breakdown voltage" section

*2 Detection current: 10mA

*3 Excluding contact bounce time

*4 Half-wave pulse of sine wave: 11ms, detection time: 10μs

*5 Half-wave pulse of sine wave: 6ms


*6 Detection time: 10μs

*7 Refer to 6. Conditions for operation, transport and storage mentioned in AMBIENT ENVIRONMENT

Characteristics (at 20°C 68°F)

Initial insulation resistance* ¹	Min. 100 MΩ (at 500 V DC)
Initial breakdown voltage* ²	Between open contacts
	1,000 Vrms
	Between contact sets
Between contact and coil	1,000 Vrms
FCC surge voltage between contacts and coil	1,500 V
Operate time* ³ (at nominal voltage)	Approx. 4 ms
Release time* ³ (at nominal voltage)	Approx. 3 ms
Set time* ³ (latching) (at nominal voltage)	Approx. 3 ms
Reset time* ³ (latching) (at nominal voltage)	Approx. 3 ms
Temperature rise	Max. 65°C with nominal voltage across coil and at nominal switching capacity
Shock resistance	Functional* ⁴ Min. 490 m/s ² {50 G}
	Destuctive* ⁵ Min. 980 m/s ² {100 G}
Vibration resistance	Functional* ⁶ 10 to 55 Hz at double amplitude of 3.3 mm
	Destuctive 10 to 55 Hz at double amplitude of 5 mm
Conditions for operation, transport and storage* ⁷ (Not freezing and condens- ing at low temperature)	Ambient temp. -40°C to +70°C -40°F to +158°F
Humidity	5 to 85% R.H.
Unit weight	Approx. 4 g .14 oz

FCC (Federal Communication Commission) requests following standard as Breakdown Voltage specification.



TYPICAL APPLICATIONS

- Telecommunication equipment
- Office equipment
- Computer peripherals
- Security alarm systems
- Medical equipment

ORDERING INFORMATION

Ex DS2Y-S	L2	DC12 V	R
Operating function		Coil voltage	Polarity
Nil: Single side stable L2: 2 coil latching		DC 1.5, 3, 5, 6, 9, 12, 24, 48 V	Nil: Standard polarity R: Reverse polarity

(Notes) 1. Standard packing: Carton: 50 pcs. Case: 500 pcs.
2. 1 coil latching type available.

TYPES AND COIL DATA (at 20°C 68°F)

Single side stable

Nominal voltage, V DC	Part No.	Pick-up voltage, V DC (max.)	Drop-out voltage, V DC (min.)	Nominal operating current mA ($\pm 10\%$)	Coil resistance, Ω ($\pm 10\%$)	Nominal operating power mW	Maximum allowable voltage, V DC (at 50°C 122°F)
1.5	DS2Y-S-DC1.5V	1.05	0.15	132.7	11.3	200	3
3	DS2Y-S-DC3V	2.10	0.3	66.7	45	200	6
5	DS2Y-S-DC5V	3.5	0.5	40	125	200	10
6	DS2Y-S-DC6V	4.2	0.6	33.3	180	200	12
9	DS2Y-S-DC9V	6.3	0.9	22.2	405	200	18
12	DS2Y-S-DC12V	8.4	1.2	16.7	720	200	24
24	DS2Y-S-DC24V	16.8	2.4	8.3	2,880	200	48
48	DS2Y-S-DC48V	33.6	4.8	6.3	7,680	300	86

(Note) Standard packing: Carton: 50 pcs. Case: 500 pcs.

2 coil latching


Nominal voltage, V DC	Part No.	Reset set, V DC (max.)	Nominal operating current mA ($\pm 10\%$)		Coil resistance, Ω ($\pm 10\%$)		Nominal operating power mW		Maximum allowable voltage, V DC (at 50°C 122°F)
			Set	Reset	Set	Reset	Set	Reset	
1.5	DS2Y-SL2-DC1.5V	1.05	120	120	12.5	12.5	180	180	3
3	DS2Y-SL2-DC3V	2.1	60	60	50	50	180	180	6
5	DS2Y-SL2-DC5V	3.5	36	36	139	139	180	180	10
6	DS2Y-SL2-DC6V	4.2	30	30	200	200	180	180	12
9	DS2Y-SL2-DC9V	6.3	20	20	450	450	180	180	18
12	DS2Y-SL2-DC12V	8.4	15	15	800	800	180	180	24
24	DS2Y-SL2-DC24V	16.8	7.5	7.5	3,200	3,200	180	180	48
48	DS2Y-SL2-DC48V	33.6	7.5	7.5	6,400	6,400	360	360	72

(Note) Standard packing: Carton: 50 pcs. Case: 500 pcs.

DIMENSIONS


mm inch

Single side stable



General tolerance: $\pm 0.3 \pm 0.012$


PC board pattern (Copper-side view)



matching 16 pin IC socket


Tolerance: $\pm 0.1 \pm 0.004$

Schematic (Bottom view) (Deenergized position)




*A polarity bar shows the relay direction.

2 coil latching



General tolerance: $\pm 0.3 \pm 0.012$


PC board pattern (Copper-side view)



matching 16 pin IC socket

Tolerance: $\pm 0.1 \pm 0.004$

Schematic (Bottom view) (Reset position)



*A polarity bar shows the relay direction.

Diagram shows the "reset" position when terminals 2 and 15 are energized. Energize terminals 1 and 16 to transfer contacts.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panasonic:](#)

[DS2Y-S-DC5V-R](#)