





Screw Connection Dual Level

- **Plastic Body:** Polyamide 66.6 VO
- **Internal Bus:** Silver plated copper
- **Clamp:** Hardened steel, electro-plated with zinc yellow chromated
- **Screws:** Steel, zinc plated and yellow chromated
- **Marking:** 4 slots on both sides
- **Tracking Resistance:**
IEC 112: CTI > 600
VDE 0303: KB > 600

6204110 D 4-2/6 LED



6204130 D 4-2/6 LED



Screw Connection Triple Level

- **Plastic Body:** Polyamide 66.6 VO
- **Internal Bus:** Silver-plated copper
- **Clamp:** Nickel-plated brass
- **Screws:** Zinc plated and yellow-chromated steel
- **Tracking Resistance:**
IEC 112: CTI > 600
VDE 0303: KB > 600

Dimensions

Stripping Length

Connecting Capacity

Number of Connectable Conductors

Approvals

Wire Range

Voltage Rating

Current Rating

Tightening Torque

Gauges

ACCESSORIES

Available Colors

End Plate Qty. pk. 25

Jumpers 2 pole / Blue
3 pole / Blue
4 pole / Blue
12-Pole / Blue
2 pole / Red
3 pole / Red
4 pole / Red
12-Pole / Red

End Bracket Qty. pk. 50

Dimensions

72 mm (L) x 55 mm (H) x
6 mm (W)

Opening

4 x 3.3 mm

Stripping Length

10 mm

Screw Thread

M 3

Rating

3, 4 K / 12-24V

Connecting Capacity

Solid conductors mm² 0.5-6
Stranded conductors
mm² 0.5-4

Conductors with Ferrules

DIN 46288 / 1 mm² 0.5-4

Number of Connectable Conductors

4 x 1.5 mm²

Approvals



Wire Range

24-10 AWG 24-10 AWG 4 mm²

Voltage Rating

Current Rating

Tightening Torque

Max 0.6 Nm

Gauges

A4

ACCESSORIES

End Plate Qty. pk. 10

Cover Qty. pk. 100

End Bracket Qty. pk. 100

Cat. No.

6800014 – 72 mm (L) x
55 mm (H) x 1.5 mm (W)

6800080 – 36 mm (L) x
14 mm (H) x 6 mm (W)

6804150 – 58 mm (L) x
36 mm (H) x 9 mm (W)

Max 0.6 Nm

A4


Cat. No.

6800014 – 72 mm (L) x
55 mm (H) x 1.5 mm (W)

6800080 – 36 mm (L) x
14 mm (H) x 6 mm (W)

6804150 – 58 mm (L) x
36 mm (H) x 9 mm (W)

6302000
T 2.5/5.3
Feed Through



78.5 mm (L) x 47.5 mm (H) x
 5.3 mm (W)

7 mm

Solid conductors mm² 0.5-4
 Stranded conductors
 mm² 0.5-2.5

2 x 1.5 mm²



26-14 AWG 26-14 AWG 2.5 mm²

300V 300V 250V

10A 10A 24A

Max. 0.5 Nm

A2

Cat. No.


6302000 – Gray

6800015 – 55.4 mm (L) x
 50 mm (H) x 1.5 mm (W)

6800192 – 100 pieces
6800193 – 100 pieces
6800194 – 100 pieces
6800200 – 10 pieces
6800202 – 100 pieces
6800203 – 100 pieces
6800204 – 100 pieces
6800300 – 10 pieces

6804150 – 58 mm (L) x
 36 mm (H) x 9 mm (W)

6302100
T 2.5/5.3



62 mm (L) x 47.5 mm (H) x
 5.3 mm (W)

7 mm

Solid conductors mm² 0.5-4
 Stranded conductors
 mm² 0.5-2.5

2 x 1.5 mm²



26-14 AWG 26-14 AWG 2.5 mm²

300V 300V 250V

10A 10A 24A

Max. 0.5 Nm

A2

Cat. No.


6302100 – Gray

6800016 – 55.4 mm (L) x
 50 mm (H) x 1.5 mm (W)

6800192 – 100 pieces
6800193 – 100 pieces
6800194 – 100 pieces
6800200 – 10 pieces
6800202 – 100 pieces
6800203 – 100 pieces
6800204 – 100 pieces
6800300 – 10 pieces

6804150 – 58 mm (L) x
 36 mm (H) x 9 mm (W)

6302110
T 2.5/5.3
*PNP LED
 Sensor*



62 mm (L) x 47.5 mm (H) x
 5.3 mm (W)

7 mm

Solid conductors mm² 0.5-4
 Stranded conductors
 mm² 0.5-2.5

2 x 1.5 mm²



26-14 AWG 26-14 AWG 2.5 mm²

Max. 0.5 Nm

A2

Cat. No.


6302110 – Gray

6800016 – 55.4 mm (L) x
 50 mm (H) x 1.5 mm (W)

6800192 – 100 pieces
6800193 – 100 pieces
6800194 – 100 pieces
6800200 – 10 pieces
6800202 – 100 pieces
6800203 – 100 pieces
6800204 – 100 pieces
6800300 – 10 pieces

6804150 – 58 mm (L) x
 36 mm (H) x 9 mm (W)

6302120
T 2.5/5.3
*NPN LED
 Sensor*



62 mm (L) x 42.5 mm (H) x
 5.3 mm (W)

7 mm

Solid conductors mm² 0.5-4
 Stranded conductors
 mm² 0.5-2.5

2 x 1.5 mm²



26-14 AWG 26-14 AWG 2.5 mm²

Max 0.5 Nm

A2

Cat. No.

6302120 – Gray

6800016 – 55.4 mm (L) x
 50 mm (H) x 1.5 mm (W)

6800192 – 100 pieces
6800193 – 100 pieces
6800194 – 100 pieces
6800200 – 10 pieces
6800202 – 100 pieces
6800203 – 100 pieces
6800204 – 100 pieces
6800300 – 10 pieces

6804150 – 58 mm (L) x
 36 mm (H) x 9 mm (W)