

TO-92

Pin Definition:

1. Emitter
2. Base
3. Collector

PRODUCT SUMMARY

BV_{CBO}	-500V
BV_{CEO}	-500V
I_C	-150mA
V_{CE(SAT)}	-0.5V @ I _C / I _B = -50mA / -10mA

Features

- Low Saturation Voltages
- Excellent gain characteristics specified up to -50mA

Structure

- Epitaxial Planar Type
- PNP Silicon Transistor

Ordering Information

Part No.	Package	Packing
TSA894CT B0	TO-92	1Kpcs / Bulk
TSA894CT A3	TO-92	2Kpcs / Ammo

Absolute Maximum Rating (Ta = 25°C unless otherwise noted)

Parameter	Symbol	Limit	Unit
Collector-Base Voltage	V _{CBO}	-500	V
Collector-Emitter Voltage	V _{CEO}	-500	V
Emitter-Base Voltage	V _{EBO}	-5	V
Collector Current	DC	-150	mA
	Pulse	-500	
Total Power Dissipation	P _{tot}	1	W
Operating Junction Temperature	T _J	+150	°C
Operating Junction and Storage Temperature Range	T _{STG}	- 55 to +150	°C

Electrical Specifications (Ta = 25°C unless otherwise noted)

Parameter	Conditions	Symbol	Min	Typ	Max	Unit
Collector-Base Breakdown Voltage	I _C = -100uA, I _E = 0	BV _{CBO}	-500	--	--	V
Collector-Emitter Breakdown Voltage	I _C = -10mA, I _B = 0	BV _{CEO}	-500	--	--	V
Emitter-Base Breakdown Voltage	I _E = -100uA, I _C = 0	BV _{EBO}	-5	--	--	V
Collector Cutoff Current	V _{CB} = 120V, I _E = 0	I _{CBO}	--	--	-100	nA
Emitter Cutoff Current	V _{EB} = 6V, I _C = 0	I _{EBO}	--	--	-100	nA
Collector-Emitter Saturation Voltage	I _C = -20mA, I _B = -2mA	V _{CE(SAT)} 1	--	--	-0.2	V
	I _C = -50mA, I _B = -10mA	V _{CE(SAT)} 2	--	--	-0.5	
Base-Emitter Saturation Voltage	I _C = -50mA, I _B = -10mA	V _{BE(SAT)}	--	--	-0.9	V
Base-Emitter on Voltage	V _{CE} = -10V, I _C = -50mA	V _{BE(ON)}	--	--	-0.9	V
DC Current Transfer Ratio	V _{CE} = -10V, I _C = -1mA	h _{FE} 1	150	--	300	
	V _{CE} = -10V, I _C = -50mA	h _{FE} 2	80	--	300	
	V _{CE} = -10V, I _C = -100mA	h _{FE} 3	--	15	--	
Transition Frequency	V _{CE} = 10V, I _C = -100mA	f _T	--	50	--	MHz
Output Capacitance	V _{CB} = 20V, f = 1MHz	Cob	--	--	8	pF
Turn On Time	V _{CE} = -100V, I _C = -50mA	Ton	--	110	--	nS
Turn Off Time	I _{B1} = -5mA, I _{B2} = -10mA	Toff	--	1500	--	nS

Electrical Characteristics Curve ($T_a = 25^\circ\text{C}$, unless otherwise noted)

Figure 1. Static Characteristics




Figure 2. DC Current Gain




Figure 3. $V_{ce(sat)}$ v.s. $V_{be(sat)}$




Figure 4. Power Derating







Figure 5. Safety Operation Area




TO-92 Mechanical Drawing



DIM	TO-92 DIMENSION			
	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	4.30	4.70	0.169	0.185
B	4.30	4.70	0.169	0.185
C	12.70	15.49	0.500	0.609
D	0.39	0.49	0.015	0.019
E	1.18	1.28	0.046	0.050
F	3.00	3.70	0.130	0.146
G	1.27	1.31	0.050	0.051
H	0.33	0.43	0.013	0.017

Marking Diagram



Y = Year Code

M = Month Code

(**A**=Jan, **B**=Feb, **C**=Mar, **D**=Apr, **E**=May, **F**=Jun, **G**=Jul, **H**=Aug, **I**=Sep, **J**=Oct, **K**=Nov, **L**=Dec)

L = Lot Code

TSA894

PNP Silicon Planar High Voltage Transistor

Not Recommended

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.