

# Other Analog Circuits

---

## In Brief . . .

Other analog circuits are provided for special applications with both bipolar and CMOS technologies. These circuits range from the industry standard analog timing circuits and multipliers to specialized CMOS smoke detectors. These products provide key functions in a wide range of applications, including data transmission, commercial smoke detectors, and various industrial controls.

|  | Page   |
|--|--------|
| Timing Circuits . . . . .                  | 4.10-2 |
| Singles . . . . .                          | 4.10-2 |
| Duals . . . . .                            | 4.10-2 |
| Multipliers . . . . .                      | 4.10-2 |
| Linear Four-Quadrant Multipliers . . . . . | 4.10-2 |
| Smoke Detectors (CMOS) . . . . .           | 4.10-3 |
| Package Overview . . . . .                 | 4.10-4 |

# Timing Circuits

These highly stable timers are capable of producing accurate time delays or oscillation. In the time delay mode of operation, the time is precisely controlled by one external resistor and capacitor. For a stable operation as an oscillator, the free-running frequency and the duty cycle are both accurately controlled with two external resistors and one capacitor. The output structure can source or sink up to 200 mA or drive TTL circuits. Timing intervals from microseconds through hours can be obtained. Additional terminals are provided for triggering or resetting if desired.


## Singles

### MC1455P1, D

$T_A = 0^\circ$  to  $+70^\circ\text{C}$ , Case 626, 751

### MC1455BP1, D

$T_A = -40^\circ$  to  $+85^\circ\text{C}$ , Case 626, 751



## Duals

### MC3456P

$T_A = 0^\circ$  to  $+70^\circ\text{C}$ , Case 646

### NE556N, D


$T_A = 0^\circ$  to  $+70^\circ\text{C}$ , Case 646, 751A

# Multipliers

## Linear Four-Quadrant Multipliers

Multipliers are designed for use where the output voltage is a linear product of two input voltages. Typical applications include: multiply, divide, square, root-mean-square, phase detector, frequency doubler, balanced modulator/demodulator, electronic gain control.

Multiplier Transfer Characteristics



### MC1494P

$T_A = 0^\circ$  to  $+70^\circ\text{C}$ , Case 648

This device has all the necessary internal regulation and references. The single-ended output is referenced to ground.

### MC1495D, P

$T_A = 0^\circ$  to  $+70^\circ\text{C}$ , Case 751A, 646

Maximum versatility is assured by allowing the user to select the level shift method.

### MC1495BP

$T_A = -40^\circ$  to  $+125^\circ\text{C}$ , Case 646

Linearity and offset are actually tested over temperature. This is an improved specification over previous versions.

# Smoke Detectors (CMOS)

These smoke detector ICs require a minimum number of external components. When smoke is sensed, or a low battery voltage is detected, an alarm is sounded via an external


piezoelectric transducer. All devices are designed to comply with UL specifications.

**Table 1. Smoke Detectors (CMOS)**


| Function  | Recommended Power Source | Unique Feature  | Low Battery Detector | Piezoelectric Horn Driver | Complies with UL217 and UL268 | Device Number | Suffix/Package |
|---|--------------------------|---|----------------------|---------------------------|-------------------------------|---------------|----------------|
| Ionization-Type Smoke Detector                      | Battery                  | High Input Impedance FET Comparator                   | ✓                    | ✓                         | ✓                             | MC14467-1     | P1/646         |
|   | Line                     |   | —                    | —                         | ✓                             | MC14578       | P/648          |
| Ionization-Type Smoke Detector with Interconnect    | Battery                  |   | ✓                    | ✓                         | ✓                             | MC14468       |                |
|   | Line                     |   | —                    | ✓                         | ✓                             | MC14470       |                |
| Photoelectric-Type Smoke Detector with Interconnect | Battery                  | Photo Amplifier                                       | ✓                    | ✓                         | ✓                             | MC145010      | P/648, DW/751G |
|   | Line                     |   | (1)                  | ✓                         | ✓                             | MC145011      |                |
|   | Battery                  | Photo Amplifier, Temporal Pattern                     | ✓                    | ✓                         | ✓                             | MC145012      | P/646, DW/751G |
|   | Line                     |   | (1)                  | ✓                         | ✓                             | MC145013      |                |
| Ionization-Type Smoke Detector                      | Battery                  | High Input Impedance FET Comparator, Temporal Pattern | ✓                    | ✓                         | ✓                             | MC145017      | P/648          |
| Ionization-Type Smoke Detector with Interconnect    | Battery                  |   | ✓                    | ✓                         | ✓                             | MC145018      |                |

(1) Low-supply detector.


# Other Analog Circuits Package Overview



CASE 626  
P1 SUFFIX



CASE 646  
N, P, P1 SUFFIX




CASE 648  
P SUFFIX



CASE 751  
D SUFFIX



CASE 751A  
D SUFFIX



CASE 751G  
DW SUFFIX